



PRESSURE TRANSDUCERS WITH AMP. PA-20



FEATURES

- Ultra-small size pressure transducer with Amp.
- 2 types of pressure ports are available
- Meet EMC standards

INTERNAL STRUCTURE (Universal joint)



Part name	Material
① Pressure Port	SUS 304
② Housing	PC (Polycarbonate)
③ Sensor module	PPS (Polyphenylene sulphide)
④ "O" ring	Fluoro-rubber
⑤ Cable	Vynyl chloride
⑥ Gasket	POM (Polyoxymethylene)

MODEL NUMBER DESIGNATION

PA-20-102V-U-3M

Series name

Rated pressure range

102V : 0 ~ -100 kPa (Gauge - Vacuum)
302R : -100 ~ 300 kPa (Gauge - Compound)

Cable length

Blank : 1.5 m
3M : 3 m

Pressure port

U : Universal joint (M5 male screw)
M : 2-M5 female screw

LIST OF MODEL NUMBERS

Pressure port	Cable length	Rated pressure range [kPa]	
		0 ~ - 100	- 100 ~ 300
Universal joint	1.5 m	PA-20-102V-U	PA-20-302R-U
	3 m	PA-20-102V-U-3M	PA-20-302R-U-3M
2-M5 female screw	1.5 m	PA-20-102V-M	PA-20-302R-M
	3 m	PA-20-102V-M-3M	PA-20-302R-M-3M

※ Verify the above model numbers when placing orders.

PA-20

PRESSURE TRANSDUCERS WITH AMP.

STANDARD SPECIFICATIONS

● Unless otherwise specified, the specs are defined at an ambient temperature of 25±5 °C and excitation voltage of 24 VDC.

Item		Model number	PA-20		
			102V	302R	
General specifications	Pressure reference		Gauge		
	Rated pressure range	kPa	0 ~ −100	−100 ~ 300	
	Maximum pressure	kPa	200	600	
	Operating temp. range	°C	−10 ~ 60		
	Compensated temp. range	°C	0 ~ 50		
	Operating humidity	%RH	35 ~ 85 (No condensation)		
	Storage temp.	°C	−20 ~ 70		
	Pressure medium		Non-corrosive gases		
	Insulation resistance	MΩ minimum	100		
	Dielectric strength		500 VAC, 60 s		
	Net weight (Without cable)		g	Approx. 5 (PA-20- * * * * -U) Approx. 8 (PA-20- * * * * -M)	
Power	Supply voltage	VDC	10.8~30 (Including ripple percentage)		
	Consumption current	mA maximum	20		
Analog output	Output voltage		V	1 ~ 5	
	Output current		mA maximum	1 (Load resistance : 5 kΩ minimum)	
	Linearity/Hysteresis		%F.S.	± 0.5	
	Thermal error (Reference temp.: 25 °C)	ZERO %F.S.	± 2		
		SPAN %F.S.	± 2		
	Response		ms	Approx. 1	

ENVIRONMENTAL CHARACTERISTICS

Test item	Test conditions	permissible change
Vibration	10 ~ 55 Hz, 1.5 mm, 3 directions for 2 hours each	Analog output : ± 2 %F.S. maximum after test
Shock	1000 m/s ² , 3 directions for 3 times each	
Pressure cycling	0 ~ Rated pressure, 10 ⁶ cycles	
Moisture resistance	40 °C, 90 ~ 95 %RH, 240 h.	

- **Universal joint type**

- **Universal joint type**



Technical drawing of the 1/2" NPT female connector. The drawing includes a side view showing a total length of 10.0 with a tolerance of +0.3/-0.3, and a front view showing a 5mm wide base with two 3.5mm diameter holes. A table indicates the wire color options: Brown, Blue, and Black.

Wire color
Brown
Blue
Black