

4

3


2

1

LOC	DIST	REVISIONS				
CE	16	P	LTR	DESCRIPTION	DATE	APVD
			C	ECR-13-014889	22SEP2013	HZ RZ

- 1

MAXIMUM CONNECTOR INSERTION LOSS IS 0.2dB PLUS CABLE ATTENUATION OF 0.7dB/km AT 1310nm. (SEE TABLE)
2. MINIMUM RETURN LOSS: 55 dB
3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.



0.21	20.00±0.30 [787.0±12.0]	2-6374107-0
0.21	10.00±0.15 [393.70±6.00]	1-6374107-0
0.20	0.413±.032 [10.50±0.80]	6374107-8
0.20	1.35±.05 [53.15±2.00]	6374107-7
0.20	2.15±.05 [84.65±2.00]	6374107-6
0.20	5.00±0.08 [196.90±3.00]	6374107-5
0.20	4.00±0.08 [157.50±3.00]	6374107-4
0.20	3.00±0.05 [118.10±2.00]	6374107-3
0.20	2.00±0.05 [78.70±2.00]	6374107-2
0.20	1.00±0.05 [39.40±2.00]	6374107-1
MAX IL (dB) 1	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KATHY HE	27SEP05	TE TE Connectivity				
DIMENSIONS: METERS INCHES		CHK RICHARD ZHAO	27SEP05	NAME CABLE ASSY, FIBER OPTIC, 900 BUFFER, SM LC TO LC, OPTIMATE —				
		APVD J.DUNCAN	27SEP05					
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		WEIGHT —						
MATERIAL —	FINISH —			SIZE A3	CAGE CODE 00779	DRAWING NO C-6374107	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE NTS	SHEET 1 OF 1	REV C