

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION			DATE	DWN
HB	—	C	PN. OBSOLETE	ECO-12-004810	24-APR-12	BL,L	BH,Y	







Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm

**NOTE**  
④1.LOT NO. SYSTEM AS FOLLOWING:  
  
WEEK      YEAR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FU BO
DIMENSIONS: mm		CHK XN.ZHANG
		APVD CH.HSU
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES		PRODUCT SPEC —
MATERIAL —		APPLICATION SPEC —
FINISH —		WEIGHT —
CUSTOMER DRAWING		

	UV RESIN	UV SEAL	14
	EPOXY RESIN	SEAL	13
CLASS 155 F	MW79	MAGNETIC WIRE	12
	HCP	COIL TERMINAL	11
UL94 V-0	PET	BOBBIN	10
UL94 V-0	NYLON	CASE	9
	Ag ALLOY	STATIONARY CONTACT	8
	Ag ALLOY	MOVABLE CONTACT	7
	Cu ALLOY	MOVABLE SPRING	6
	Cu ALLOY	NC TERMINAL	5
	Cu ALLOY	NO TERMINAL	4
	Ni PLATED	STEEL	3
	Cu PLATED	STEEL	2
	Ni PLATED	STEEL	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION

**TE** TE Connectivity

ORWH-H3F,000 CUSTOMER DRAWING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=1721956	—
SCALE	3:1	1 OF 1	REV C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[ORWH-SS-112H3F,000](#)