

Heavy-Duty Computer Power Cord, 15A, 14AWG (IEC-320-C14 to IEC-320-C15), 10-ft.

MODEL NUMBER: **P018-010**



Description

Tripp Lite's C14-to-C15 power cords allow connection from high voltage network hardware utilizing C15 type connectors to PDU's and UPS systems with C14 type inputs. Heavy-duty 14AWG wire supports voltages up to 250V. Molded ends ensure a lifetime of use.

Features

- Heavy-duty power cord supports up to 250V
- Flexible 14AWG wire for easy routing
- Use with Cisco, HP and other hardware that uses C15 type power connections
- UL Listed

Specifications

MODEL TEXT	
What Does This Product Do?	Connect network hardware with C15 power connections such as servers to PDUs and UPS systems with C14 type inputs.
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3
PHYSICAL	
Shipping Dimensions (hwd / in.)	14.17 x 11.8 x 0.5
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27

Highlights

- 10-ft. heavy-duty power cord, C14-to-C15
- 100~250V, 15A, 14AWG, SJT
- UL Listed

Package Includes

- 10-ft. C14 to C15 Power Cord

Shipping Weight (lbs.)	1.04
Shipping Weight (kg)	0.47
Color	Black
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C15
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>