

4-1825136-4 Product Details



4-1825136-4

TE Internal Number: 4-1825136-4

Active

[View 3D PDF](#)

Toggle Switches

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- A Series
- Single Pole - Double Throw Configuration (Pole-Throw)
- Current Rating = 0.4 VA A
- Mount Style = Through-Hole
- Termination Type = Printed Circuit

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information	
Product Drawings: • GEMINI A SERIES TOGGLE SWITCH, SINGLE POLE, 2 POSITI... (PDF, English) Catalog Pages/Data Sheets: • SWITCHES_CORE_PROGRAM_CATALOG (PDF, English) • GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5 (PDF, English) Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: (CAD Format & Compression Information) • 2D Drawing (DXF, Version A) • 3D Model (IGES, Version A) • 3D Model (STEP, Version A) List all Documents	Additional Information: • Product Line Information Additional Product Images: • Product Photo Related Products: • Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Configuration (Pole-Throw) = Single Pole - Double Throw • Termination Type = Printed Circuit Electrical Characteristics: • Current Rating (A) = 0.4 VA Termination Related Features: • Seal Type = Terminal Seal (epoxy) Body Related Features: • Series = A • Mount Style = Through-Hole Contact Related Features: • Contact Plating = Gold	Housing Related Features: • Toggle Actuation = Vertical • Toggle Style = Baton Long • Toggle Length (mm [in]) = 10.40 [0.410] • Process Sealed = No • Bushing Style = Threaded • Bushing Type = 1/4-40 Configuration Related Features: • Operating Function = On On Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant

- Other:**
- Brand = Alcoswitch

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

>

Follow Us On:



Visit Us On:

