

MOS FET Relays


G3VM-81HR

High-capacity MOS FET Relay Allowing Switching of a 1.25-A Continuous Load Current with a 80-V Load Voltage, 6-pin SOP Package.

- Continuous load current of 1,250 mA.
- Dielectric strength of 1,500 Vrms between I/O.
- RoHS Compliant.

■ Application Examples

- Broadband systems
- Measurement devices
- Data loggers
- Amusement machines



Note: The actual product is marked differently from the image shown here.


■ List of Models

Contact form	Terminals	Load voltage (peak value)	Model	Number per stick	Number per tape
SPST-NO	Surface-mounting terminals	80 VAC	G3VM-81HR	75	---
			G3VM-81HR(TR)	---	2,500


■ Dimensions

Note: All units are in millimeters unless otherwise indicated.

G3VM-81HR




Note: The actual product is marked differently from the image shown here.



Weight: 0.13 g


■ Terminal Arrangement/Internal Connections (Top View)

G3VM-81HR



■ Actual Mounting Pad Dimensions (Recommended Value, Top View)

G3VM-81HR



Absolute Maximum Ratings (Ta = 25°C)


Item		Symbol	Rating	Unit	Measurement conditions
Input	LED forward current	I _F	50	mA	
	Repetitive peak LED forward current	I _{FP}	1	A	100 μs pulses, 100 pps
	LED forward current reduction rate	Δ I _F /°C	−0.5	mA/°C	T _a ≥ 25°C
	LED reverse voltage	V _R	5	V	
	Connection temperature	T _j	125	°C	
Output	Load voltage (AC peak/DC)	V _{OFF}	80	V	
	Continuous load current	I _O	1,250	mA	
	ON current reduction rate	Δ I _{ON} /°C	−12.5	mA/°C	T _a ≥ 25°C
	Connection temperature	T _j	125	°C	
Dielectric strength between input and output (See note 1.)		V _{I-O}	1,500	V _{rms}	AC for 1 min
Operating temperature		T _a	−20 to +85	°C	With no icing or condensation
Storage temperature		T _{stg}	−40 to +125	°C	With no icing or condensation
Soldering temperature (10 s)		---	260	°C	10 s

Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

Electrical Characteristics (Ta = 25°C)

Item	Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions
Input	LED forward voltage	V_F	1.0	1.15	1.3	V
	Reverse current	I_R	---	---	10	μA
	Capacity between terminals	C_T	---	15	---	pF
	Trigger LED forward current	I_{FT}	---	2	5	mA
Output	Maximum resistance with output ON	R_{ON}	---	0.11	0.15	Ω
	Current leakage when the relay is open	I_{LEAK}	---	1.2	1.5	nA
	Capacity between terminals	C_{OFF}	---	460	1,000	pF
Capacity between I/O terminals		C_{I-O}	---	0.8	---	pF
Insulation resistance		R_{I-O}	1,000	---	---	M Ω
Turn-ON time		t_{ON}	---	2.0	3.0	ms
Turn-OFF time		t_{OFF}	---	0.7	1.0	ms

Note: 2. Turn-ON and Turn-OFF Times




Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.


Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	V_{DD}	---	---	64	V
Operating LED forward current	I_F	5	---	30	mA
Continuous load current (AC peak/DC)	I_O	---	---	1,250	mA
Operating temperature	T_a	25	---	60	°C

■ Engineering Data


**LED forward current vs.
Ambient temperature**
 $I_F - T_a$




**Continuous load current vs.
Ambient temperature**
 $I_O - T_a$




**LED forward current vs.
LED forward voltage**
 $I_F - V_F$




**Continuous load current vs.
On-state voltage**
 $I_O - V_{ON}$




**On-state resistance vs.
Ambient temperature**
 $R_{ON} - T_a$




**Trigger LED forward current vs.
Ambient temperature**
 $I_{FT} - T_a$




**Turn ON, Turn OFF time vs.
LED forward current**
 $t_{ON}, t_{OFF} - I_F$



**Turn ON, Turn OFF time vs.
Ambient temperature**
 $t_{ON}, t_{OFF} - T_a$



**Current leakage vs.
Ambient temperature**
 $I_{LEAK} - T_a$



All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON[®]

**OMRON ELECTRONIC
COMPONENTS LLC**

55 E. Commerce Drive, Suite B
Schaumburg, IL 60173

847-882-2288

OMRON ON-LINE

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Cat. No. X302-E-1

12/10

Specifications subject to change without notice

Printed in USA