

323197

© 1955 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS			
SYM	DESCRIPTION	DATE	APPD
A	REDRAWN	5/27/65	FRW
B	REV. PER P-8347	6/10/77	REB.
C	REV G-4680	5-5-88	TMS/JT

METALLIC BAND:
STEEL QQ-S-698
(ASTM A109)

FOR .298 MAX.
INSULATION DIA.

RED INSULATION

DIMPLED
SURFACE

$\frac{7}{32}$ MAX. WASKERR.

.406

$\pm .003$
.197 DIA.
(FOR #10 STUD)

$\frac{13}{64}$ MAX.

AMP INFO

LOC. PART NO.

61410

UNLESS
OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON

FRACTIONS	DECIMALS	ANGLES
$\pm \frac{1}{64}$	$\pm .008$	$\pm 5^\circ$

MATERIAL **COPPER**
(QQ-C-576)

HEAT TREAT

H

FINISH **TIN PLATED**
(MIL-T-10727) TYPE I

TONGUE MATERIAL THICKNESS .040

SIGNATURE

DATE

DR. *L.E. Conley*

5/24/65

CHK. *R. Wolfe*

7/2/65

DSGN. *FRW*

APPD. *FRW*

5/27/65

AMP

AMP INCORPORATED
HARRISBURG, PENNSYLVANIA

WIRE TERMINAL
AMPLI-BOND
RING TONGUE
WIRE SIZE : 8

DSGN APPD

CODE IDENT NO

SIZE

NUMBER

00779

A

323197

OTHER APPD

SCALE

2:1

WT

CALC

ACTUAL

SHEET

OF 1

CUSTOMER DRAWING