





Technical drawing of a mechanical part showing dimensions and tolerances. The drawing includes the following specifications:

- Top horizontal dimension: 6.35 ± 0.05 [$.250 \pm .002$]
- Top right horizontal dimension: 1.27 ± 0.05 [$.050 \pm .002$] TYP
- Top right vertical dimension: POSITION NO.
- Top right circular feature dimension: $\varnothing 0.889 \pm 0.076$ [$\varnothing .035 \pm .003$]
- Top right circular feature label: 6 PLACES
- Left vertical dimension: 8.89 ± 0.05 [$.350 \pm .002$]
- Right vertical dimension: 6.35 ± 0.05 [$.250 \pm .002$]
- Bottom left horizontal dimension: 4.445 ± 0.05 [$.175 \pm .002$]
- Bottom right horizontal dimension: 10.16 ± 0.05 [$.400 \pm .002$]
- Bottom right circular feature dimension: $\varnothing 3.251 \pm 0.076$ [$\varnothing .128 \pm .003$]
- Bottom right circular feature label: 2 HOLES

Technical drawing of a mechanical part with dimensions:

- Top horizontal dimension: 1.40 [.055]
- Right vertical dimension (total): 15.88 [.625]
- Right vertical dimension (middle section): 13.34 [.525]
- Right vertical dimension (bottom section): 10.16 [.400] NOMINAL



SUPERSEDED BY 520250-9
SUPERSEDED BY 520250-3
SUPERSEDED BY 520250-2

2.16-2.67 [.085-.105] 3.30-4.32 [.130-.170]		BLACK	4		1-520250-1
		BLACK	4		
		BLACK	4		
		PEBBLE GRAY	4		520250-9
		BLACK	4		520250-8
		BLACK	6		520250-7
		PEBBLE GRAY	4		520250-4
		BLACK	6		520250-3
		BLACK	4		520250-2
		BLACK	2		520250-1

THIS DRAWING IS A CONTROLLED DOCUMENT.									
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWG. T. WOOTEN 05-APR-94 CHK. C. WHITT 06-APR-94 APPV. J. TONEY 13-APR-94		AMP TYCO Electronics Harrisburg, PA 17105-3608			
		0 PLOC a= 2 PLOC a= 2 PLOC a= 4 PLOC a= 4 PLOC a= FINISH		NAME MODULAR JACK ASSEMBLY, 6 POSITION, SIDE ENTRY, FLANGELESS, WITH PANEL STOPS		SIZE CASE CODE DRAWING NO. RESTRICTED TO A1 00779 C-520250 -			
MATERIAL:				WEIGHT - CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 2 REV 2			

27-FEB-02 15:45:35 anp36051 /hone/anp36051/ednmod