




Foil Type Polyester Film Capacitor

series (Standard type)


- Inductive construction, using a dielectric of polyester film together with aluminum foil.
- Coated with epoxy resin for superior heat resistance, humidity resistance and solvent resistance.
- Suited for use in commercial and industrial applications.
- Available for automatic insertion systems.
- Compliant to the RoHS directive (2011/65/EU).




Specifications

Item	Performance Characteristics
Category Temperature Range	-40 to +85°C
Rated Voltage	50, 100VDC
Rated Capacitance Range	0.001 to 0.47μF
Capacitance Tolerance	±5% (J), ±10% (K)
Dielectric Loss Tangent	0.8% or less (at 1kHz 20°C)
Insulation Resistance	30000 MΩ or more
Withstand Voltage	Between Terminals : Rated Voltage × 250%, 1 to 5 secs. Between Terminals and Coverage : Rated Voltage × 200%, 1 to 5 secs.
Encapsulation	Epoxy resin

Drawing



Type numbering system (Example : 50V 0.047μF)



Dimensions

Unit : mm

V (Code) Cap. (μF)		50VDC (1H)							100VDC (2A)					
		T	W	H	d	P	F		T	W	H	d	P	F
0.001	102	2.5	5.0	8.5	0.5	3.5 ± 0.75	5.0		2.8	5.5	11.5	0.5	3.5 ^{+1.0} _{-1.2}	5.0
0.0015	152	2.5	5.0	8.5	0.5	3.5 ± 0.75	5.0		2.8	5.5	12.0	0.5	3.5 ^{+1.0} _{-1.2}	5.0
0.0022	222	3.0	5.5	8.5	0.5	3.5 ± 0.75	5.0		2.8	5.5	12.0	0.5	3.5 ^{+1.0} _{-1.2}	5.0
0.0033	332	3.0	5.5	8.5	0.5	3.5 ± 0.75	5.0		2.8	5.5	12.0	0.5	3.5 ^{+1.0} _{-1.2}	5.0
0.0047	472	3.0	6.0	8.5	0.5	3.5 ± 0.75	5.0		3.0	6.0	12.0	0.5	3.5 ^{+1.0} _{-1.2}	5.0
0.0068	682	3.5	6.0	8.5	0.5	3.5 ± 0.75	5.0		3.0	6.0	12.0	0.5	5.0 ± 1.0	5.0
0.01	103	3.5	6.0	8.5	0.5	3.5 ± 0.75	5.0		3.0	6.5	12.0	0.5	5.0 ± 1.0	5.0
0.015	153	3.5	6.0	10.0	0.5	3.5 ± 0.75	5.0		3.0	6.5	13.0	0.5	5.0 ± 1.0	5.0
0.022	223	3.5	6.5	10.5	0.5	3.5 ± 0.75	5.0		3.5	7.0	13.0	0.5	5.0 ± 1.0	5.0
0.033	333	4.0	7.0	10.5	0.5	3.5 ± 0.75	5.0		3.5	7.5	13.0	0.5	5.0 ± 1.0	5.0
0.047	473	4.5	7.5	11.0	0.5	5.0 ± 1.0	5.0		4.5	8.5	14.0	0.5	5.0 ± 1.0	5.0
0.068	683	5.0	8.0	11.0	0.5	5.0 ± 1.0	5.0		4.5	9.5	14.0	0.5	7.5 ^{+1.0} _{-1.2}	7.5
0.1	104	5.5	9.0	12.0	0.5	5.0 ± 1.0	5.0		5.5	11.0	14.0	0.5	7.5 ^{+1.0} _{-1.2}	7.5
0.15	154	6.5	10.0	13.5	0.5	5.0 ± 1.0	5.0		6.0	12.5	15.5	0.5	10.0 ^{+1.0} _{-1.2}	7.5
0.22	224	7.0	11.0	13.5	0.5	7.5 ^{+1.0} _{-1.2}	7.5		7.0	14.0	15.5	0.5	10.0 ^{+1.0} _{-1.2}	7.5
0.33	334	8.0	12.5	16.0	0.6	7.5 ^{+1.0} _{-1.2}	7.5		8.0	14.5	18.5	0.6	10.0 ^{+1.0} _{-1.2}	7.5
0.47	474	9.5	14.0	16.5	0.6	7.5 ^{+1.0} _{-1.2}	7.5		9.5	16.5	18.5	0.6	10.0 ^{+1.0} _{-1.2}	7.5

F : lead pitch for cut / formed lead wires.