

Description

- High Density, high current/low voltage applications
- Foil technology that adds higher reliability factor over the traditional magnet wire used for higher frequency circuit designs
- Current range from 78.0 to 33.8 Amps
- Inductance range from 0.50uH to 6.52uH

Applications

- Next generation microprocessors
- Energy storage applications
- DC-DC converters
- Computers

Environmental Data

- Storage temperature range: -40°C to +125°C
- Operating ambient temperature range: -40°C to +85°C
- Infrared reflow temperature: +260°C for 10 seconds maximum



Packaging




- Supplied in bulk packaging, 24 parts per tray

Part Number	Rated Inductance μH	OCL (1) nominal $\pm 20\%$ μH	I _{rms} (2) Amperes (Typ.)	I _{sat} (3) Amperes (Typ.)	DCR (m Ω) max. @ 20°C	Volts (4) μSec (V μS) (ref.)
HC3-R50	0.50	0.50	78.00	120	0.42	17.33
HC3-1R0	1.0	1.05	78.00	78	0.42	17.33
HC3-2R2	2.2	2.05	55.50	60	0.70	26.01
HC3-3R3	3.3	3.63	42.45	46	1.20	34.65
HC3-4R7	4.7	4.98	33.80	38	2.17	43.30
HC3-5R6	5.6	5.68	33.80	34.5	2.17	43.30
HC3-6R0	6.0	6.52	33.80	30.0	2.17	43.30

- 1) Test Parameters: 300kHz, 0.25 Vrms
- 2) DC current for approximately ΔT of 40°C without core loss
De-rating is necessary for AC currents. PCB layout, trace thickness and width, air flow and proximity of other heat generating components will affect temperature rise. It is recommended that the temperature of the part not exceed 125°C under worst case conditions verified in the end application.
- 3) Peak current for approximately 30% rolloff (@20°C)
- 4) Applied Volt-Time product (V- μS) across the inductor. This value represents the applied V- μS at 300kHz necessary to generate a core loss equal to 10% of the total losses for a 40°C temperature rise.

Part number definition:
First 3 characters = Product code and size.
Last 3 characters = Inductance in uH. R = Decimal point. If no R is present, third character = # of zeros.
wwllly = (Date Code)
R = Revision Level

Mechanical Diagrams




SCHEMATIC



Part Number	Height max
HC3-R50	18.0
HC3-1R0	17.5
HC3-2R2	17.5
HC3-3R3	17.5
HC3-4R7	17.5
HC3-5R6	17.5
HC3-6R0	17.5

Rolloff



Core Loss

Irms DERATING WITH CORE LOSS for HC3 % Applied Volt-u Seconds

