




Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.



- Technical data
- 1.Nominal voltage: 300V/10A
PITCH:3.5mm
 - 2.Connection capacity:
AWG 26-16
 - 3.Insulation Withstanding Voltage:
AC 1600V/MIN
 - 4.Insulation Resistance:
1000MΩ or more at DC500V
 - 5.Tightening torque:
2.0kgf.cm (0.2N.m)
 - 6.Screw thread: M2
 - 7.Stripping length: 5-6mm
 - 8.Operating temperature range:-40°C ~ 115°C
Soldering temperature:250±10°C/5s
 - 9.Undimensioned Tolerances:


Dim.L=Px3.5 Dim.B=(P-1)x3.5 P= number of poles(2-24P)		
0-30mm	±0.10	±0.15
over 30mm-60mm	±0.15	±0.20
over 60mm-90mm	±0.20	±0.25
over 90mm	±0.25	±0.30

- 10.Safety approval:
- 11.RoHS Compliance

Part No.: OSTTEXX0161

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	2: Red
...	3: Orange
...	4: Yellow
24 24 Poles	5: Green
	6: Blue (Standard)
	8: Grey

Nonstandard colors
Mins could apply



SIGN	DESCRIPTION	CHK.	DATE
------	-------------	------	------

4	WIRE GUARD	Stainless steel			P			
3	SCREW	STEEL		M2.0, Zn Plated	P			
2	CAGE	BRASS		M2.0, Tin PLATED	P			
1	BODY	PA66 UL94V-0		ALL COLOR	1			
ITEM	NAME OF PART	MATERIAL			NOTES	Q'TY		
DWG.	WF. Zhang	DATE	2015.11.23	UNITS:	MM	SHEET:	1 OF 1	Tolerance
CHK.		DATE		SCALE:	NONE 3:1 (:)	REV.:	A	X. ±0.50
APP.		DATE		TITLE:	OSTTE 3.50mm Series Interlock stackable type			X.X ±0.30
				PART NO.	OSTTExX0161			X° ±1°
				DWG NO.	OSTTExX0161.dwg			
ON-SHORE TECHNOLOGY, INC.								