




PRODUCT NUMBER	DIM "J"	DIM "K"
76316-XXX	SEE NEXT SHEET	
76316-XXXC	SEE NEXT SHEET	



NOTES:

- 1 MATERIAL HOUSING: THERMOPLASTIC POLYESTER 30 % GLASS FILLED, COLOUR BLUE, FLAME RETARDANT PER UL 94-V0
- 2 MATERIAL BOX: BRASS ASTM B36 C26000-H02
- 3 MATERIAL SPRING: BERYLLIUM COPPER ASTM B 194 C 17200-TF 00
- 4 PLATING: SEE NEXT SHEET TIN PLATED
- 5 A LETTER "C" AT THE END OF PART NUMBER TO INDICATE PACKAGING IN SHORT TUBES (550mm).

All rights reserved. Reproduction or use in this drawing is by the
 property of BERG ELECTRONICS.
 Copyright BERG ELECTRONICS.

BERG
 ELECTRONICS

All rights reserved. Reproduction or use in this drawing is by the
 property of BERG ELECTRONICS.
 Copyright BERG ELECTRONICS.

mat'l code SEE NOTES				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS	
lir	ecn no	dr	date	linear		projection		title	
B	F80325	DLE	98.05.07					V. C. C.	
				angles		mm		DOUBLE ROW 100x.100	
		dr	DLE	98.05.07	scale		product family		code
		enr	AESCHBACHER	98.05.07	5:1		BERGCON		213
		chr	AESCHBACHER	98.05.07			size dwg no		sheet
		appd	NIZZI	98.05.07			A3 76316		1 of 2
sheet index	revision	B	B						
	sheet	1	2						

All rights reserved. Reproduction of this drawing is prohibited without the written permission of BERG ELECTRONICS.

BERG
ELECTRONICS

All rights reserved. Reproduction of this drawing is prohibited without the written permission of BERG ELECTRONICS.

PRODUCT NUMBER	NBR OF POS	DIM "J"	DIM "K"
76316-X02(C)	2x02	(2.54)	(5.08)
76316-X03(C)	2x03	(5.08)	(7.62)
76316-X04(C)	2x04	(7.62)	(10.16)
76316-X05(C)	2x05	(10.16)	(12.70)
76316-X06(C)	2x06	(12.70)	(15.24)
76316-X07(C)	2x07	(15.24)	(17.78)
76316-X08(C)	2x08	(17.78)	(20.32)
76316-X09(C)	2x09	(20.32)	(22.86)
76316-X10(C)	2x10	(22.86)	(25.40)
76316-X11(C)	2x11	(25.40)	(27.94)
76316-X12(C)	2x12	(27.94)	(30.48)
76316-X13(C)	2x13	(30.48)	(33.02)
76316-X14(C)	2x14	(33.02)	(35.56)
76316-X15(C)	2x15	(35.56)	(38.10)
76316-X16(C)	2x16	(38.10)	(40.64)
76316-X17(C)	2x17	(40.64)	(43.18)
76316-X18(C)	2x18	(43.18)	(45.72)
76316-X19(C)	2x19	(45.72)	(48.26)
76316-X20(C)	2x20	(48.26)	(50.80)
76316-X21(C)	2x21	(50.80)	(53.34)
76316-X22(C)	2x22	(53.34)	(55.88)
76316-X23(C)	2x23	(55.88)	(58.42)
76316-X24(C)	2x24	(58.42)	(60.96)
76316-X25(C)	2x25	(60.96)	(63.50)

PRODUCT NUMBER	NBR OF POS	DIM "J"	DIM "K"
76316-X26(C)	2x26	(63.50)	(66.04)
76316-X27(C)	2x27	(66.04)	(68.58)
76316-X28(C)	2x28	(68.58)	(71.12)
76316-X29(C)	2x29	(71.12)	(73.66)
76316-X30(C)	2x30	(73.66)	(76.20)
76316-X31(C)	2x31	(76.20)	(78.74)
76316-X32(C)	2x32	(78.74)	(81.28)
76316-X33(C)	2x33	(81.28)	(83.82)
76316-X34(C)	2x34	(83.82)	(86.36)
76316-X35(C)	2x35	(86.36)	(88.90)
76316-X36(C)	2x36	(88.90)	(91.44)
76316-X37(C)	2x37	(91.44)	(93.98)
76316-X38(C)	2x38	(93.98)	(96.52)
76316-X39(C)	2x39	(96.52)	(99.06)
76316-X40(C)	2x40	(99.06)	(101.60)
76316-X41(C)	2x41	(101.60)	(104.14)
76316-X42(C)	2x42	(104.14)	(106.68)
76316-X43(C)	2x43	(106.68)	(109.22)
76316-X44(C)	2x44	(109.22)	(111.76)
76316-X45(C)	2x45	(111.76)	(114.30)
76316-X46(C)	2x46	(114.30)	(116.84)
76316-X47(C)	2x47	(116.84)	(119.38)
76316-X48(C)	2x48	(119.38)	(121.92)
76316-X49(C)	2x49	(121.92)	(124.46)
76316-X50(C)	2x50	(124.46)	(127.00)

76316-9XX(C)	5µm Sn/Pb	1.25µm Sn/Pb
PLATING CODE X	PLATING THICKNESS IN CONTACT AREA	PRE-PLTEAD FLASH THICKNESS

mat'l. code SEE TABLE				tolerances unless otherwise specified			CUSTOMER COPY		BERG ELECTRONICS		
lir	ecm no	dr	date	linear			projection 	title V. C. C.			
B	F80325	DLE	98.05.07					DOUBLE ROW .100x.100			
				angles			mm ←→	product family BERGCON		code	
				dr	DLE	98.05.07		size		213	
				engr	AESCHBACHER	98.05.07		dwg no		sheet	
				chr	AESCHBACHER	98.05.07		A3		2 of 2	
				appd	P. NIZZI	98.05.07	scale N/A		76316		
sheet index	revision sheet										