




HZ0603C651R-10

**UNCONTROLLED
DOCUMENT**

PHYSICAL DIMENSIONS:

A	1.60 [.063]	+ 0.15	-.006]
B	0.80 [.031]	+ 0.15	-.006]
C	0.80 [.031]	+ 0.15	-.006]
D	0.36 [.014]	+ 0.15	-.006]




ELECTRICAL CHARACTERISTICS:			
Z @ 100MHz (Ω)	DCR (Ω)	Rated Current	
Nominal	650		
Minimum	488		
Maximum	813	0.60	300 mA

NOTES: UNLESS OTHERWISE SPECIFIED


1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 7" REELS, 4000 PCS/REEL.
2. TERMINATION FINISH IS 100% TIN.
3. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
4. OPERATING TEMP. RANGE: -40°C~+125°C (INCLUDING SELF-HEATING)

LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762 (.030) to this dimension)

RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved. Laird				
C	ADD OPERATING TEMPERATURE UPDATE LAIRD LOGO AND REFLOW CURVE	08/05/13	QU	PROJECT/PART NUMBER: HZ0603C651R-10		REV C	PART TYPE: CO-FIRE	DRAWN BY: TMB
B	UPDATE COPMANY LOGO AND ADD ROHS	02/27/05	JRK	DATE: 04/03/04	SCALE: —	SHEET: 2 of 2		
A	ORIGINAL DRAFT	04/03/04	TMB	CAD HZ0603C651R-10-C	TOOL # —			
REV	DESCRIPTION	DATE	INT					