







LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		E	REVISED PER ECR-12-013486	10JAN13	KH KR

SUGGESTED MATING TAB



- CONTINUOUS STRIP ON REELS.
- ACCEPTS #22-#18 SINGLE WIRE SIZES, WIRE CRIMP IS 2.03 [0.080], F TYPE.
- FITS INSULATION RANGE 2.29-3.30 [0.090-0.130] DIA, INSULATION CRIMP IS 3.94 [0.155] F TYPE.



SECTION C-C

SECTION D-D

SECTION A-A

SECTION B-B
ROTATED 90° CW

TIN		1217113-2	
-		1217113-1	
FINISH		PART NO.	
		TE Connectivity	
NAME			
RECEPTACLE, POSITIVE-LOCK, MARK III, 4.75 [.187] SERIES			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=1217113	-
		SCALE	SHEET
		6:1	1 OF 1
		REV	E

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	JR RUTH	9/17/98
			CHK	MS FEHER	9/17/98
			APVD	E HOWARD	9/17/98
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		0 PLC	±	—	—
		1 PLC	±	—	—
		2 PLC	±	0.25 [.010]	—
		3 PLC	±	—	APPLICATION SPEC
		4 PLC	±	—	—
MATERIAL		FINISH		WEIGHT	
BRASS		SEE TABLE		—	
				CUSTOMER DRAWING	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm [INCHES]			
		0 PLC	± -
		1 PLC	± -
		2 PLC	± 0.25 [0.010]
		3 PLC	± -
		4 PLC	± -
		ANGLES	± -
		FINISH	SEE TABLE
MATERIAL			
BRASS			