




PRODUCT NUMBER

95278-YXX-XXLF

- RoHS COMPATIBLE, NOTE 6.
- TOTAL NB OF POSITIONS 04 TO 50
- PACKAGING OPTIONS, NOTE 3.
- PIN STYLE SEE SHEET 2
- PLATING SEE SHEET 2

NOTES:

1. HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK
2. PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PACKAGING OPTIONS:
 - = POLY BAGS
 - B = TUBE + CAP
 - A = TAPE & REEL WITH CAP, SEE TA840 FOR PRODUCT AVAILABILITY.
 - TR = CUSTOM TAPE & REEL WITH CAP, SEE TA840 ONLY FOR P/N 95278-102TR04LF AND P/N 95278-101TR10LF
4. 9N MIN RETENTION IN EITHER DIRECTION
5. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS $N \times 2.54 = 20.32\text{mm}$
6. RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, $2\mu\text{m}$ MINIMUM MATTE TIN OVER $1.27\mu\text{m}$ MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDES IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code				surface	tolerance	projection	product family		
				ISO 1302	ISO 406 ISO 1101		BERGSTIK		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
N	F08-0148	RTR	08.03.31	angles	x.x ±0.3	mm	UNSHR.HEADER		
P	F08-0253	LMU	08.12.10	linear	x.xx ±0.13				
R	F10-0008	LMU	10.03.09		x.xxx ±0.05	scale 5:1	DR SMT		
S	B-18789	LMU	14.09.11	dr	D.LE	FCJ	dwg no	sheet 1 of 2	size
T	B-18983	LMU	14.10.03	enrg	JM.C		95278		A3
U	B-20276	LMU	15.02.16	chr	JM.C		CUSTOMER Drawing		
V	B-20561	AMA	15.03.26	appd	JF.N				
sheet	revision	V	T						
index	sheet	1	2						

PIN	STYLE	MATING
01		5.9
02		8
03		9.9
04		11.4
05		9.2
06		10.4
07		5.3
09		17.00
10		8.10
11		8.50
12		3.05
13		14.35
14		4.00

PLATING


1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

4 = 2µm TIN MIN FULL PLATED

5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

– 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS



mat'l. code				surface	tolerance	projection	product family			
				ISO 1302	ISO 406	ISO 1101	BERGSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title			
N	F08-0253	LMU	08.12.10	angles	linear		UNSHR.HEADER			
P	B-18789	LMU	14.09.11				DR SMT			
R	B-18983	LMU	14.10.03			scale N/A				
S	B-20276	LMU	15.02.16	dr	D.LE	01.01.24	dwg no		sheet 2 of -	size
T	B-20561	AMA	15.03.26	enr	JM.C	01.01.24	95278			A3
				chr	JM.C	01.01.24	type		CUSTOMER	Drawing
				appd	JF.N	01.01.24				
sheet index	revision	sheet								