




Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite de FCI NV.
All rights strictly reserved. Reproduction or issue to third parties in any form without written authority from the proprietor.
Property of FCI NV.
© FCI NV.



Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite de FCI B.V. est formellement interdite.
All rights strictly reserved. Reproduction or issue to third parties in any form without written authority from the proprietor, FCI B.V., is expressly prohibited.





PRODUCT NR:	ROW#	CONFIGURATION						DIM A	PCB THICKNESS
		1	2	3	4	5	6		
85867-X20LF	D	-	-	-	-	-	-	2.90	1.60
	C	-	-	-	-	-	-		
	B	-	-	X	X	X	X		
	A	X	X	X	X	X	X		
85867-X21LF	D	X	-	X	X	-	-	2.90	1.60
	C	X	-	-	-	-	-		
	B	-	-	-	-	X	-		
	A	X	X	-	-	X	-		
85867-X22LF	D	-	X	-	X	-	-	2.90	1.60
	C	X	-	-	-	X	-		
	B	-	X	-	X	-	X		
	A	X	-	-	-	X	-		
85867-X23LF	D	X	-	X	-	X	-	2.90	1.60
	C	X	-	X	-	-	X		
	B	-	X	-	X	-	X		
	A	-	X	-	X	-	X		




PRODUCT NR:	ROW#	CONFIGURATION						DIM A	PCB THICKNESS
		1	2	3	4	5	6		
85867-X24LF	D	X	X	X	X	X	-	2.90	1.60
	C	X	X	X	X	X	-		
	B	X	X	X	X	X	-		
	A	-	-	X	X	X	-		
85867-X25LF	D	X	X	-	X	-	X	2.90	1.60
	C	X	X	-	X	-	X		
	B	X	X	-	X	-	X		
	A	X	X	-	X	-	X		
85867-X26LF	D	X	-	X	X	X	X	2.90	1.60
	C	X	-	X	X	X	X		
	B	X	-	X	X	X	X		
	A	X	-	X	X	X	X		
85867-X27LF	D	X	-	X	-	X	X	2.90	1.60
	C	X	-	X	-	-	X		
	B	-	X	-	X	-	X		
	A	-	X	-	X	-	X		

"-" POSITION NOT LOADED
"X" POSITION LOADED




PRODUCT AFTER PC BOARD APPLICATION.



- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 PLATING SOLDER TAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn FOR LEAD FREE.
 - 4 INDICATED HOLES ARE UNPLATED.
 - 5 PRODUCT MARKING: PARTNUMBER & BATCH ID.
 - 6 SET BACK FOR PRESS BLOCK.
 - 7 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
 - 8 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - 9 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL



RECOMMENDED HOLE PATTERN, COMPONENT SIDE.

mat'l. code SEE NOTES		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
litr	ecnr	no	date	linear	projection	title	www.fciconnect.com
v				angles	mm	4R RA RCP SG 12mm PRESS PEG	
dr	VISSCHERS IB	980514		engr	M LOMAN	980514	product family METRAL(tm)
chr	M LOMAN	980514		appo	H COOLMANS	980514	code 213
sheet	revision	sheet		scale	5:1	A2	85867
Index							sheet 2 of 2

All rights strictly reserved. Reproduction or issue to third parties in any form without written authority from the proprietor.
Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite du propriétaire.
Property of FCI b.v.
© FCI b.v.



1	2	3	4	5	6	7	8
PRODUCT NR:	CONFIGURATION	DIM A	PCB THICKNESS	PRODUCT NR:	CONFIGURATION	DIM A	PCB THICKNESS
85867-X28LF	ROW# 1 2 3 4 5 6 D X - X - X - C - X - X - X - B X - X - X - A - X - X - X -	2.90	1.60	85867-X29LF	ROW# 1 2 3 4 5 6 D - X - X - X - C - X - X - X - B - X - X - X - A - X - X - X -	2.90	1.60
				85867-X201LF	ROW# 1 2 3 4 5 6 D X X X X X X C X X X X X X B - - - - - A X X X X X X	2.90	1.60

"-" POSITION NOT LOADED
"X" POSITION LOADED

nat'l. code SEE NOTES		tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnection.com	
ltr	ec	n	o	d	r	date	
v							
linear				projection		title	
angles						4R RA RCP SG	
dr		VISSCHERS IB 980514		product family		code	
engr		M LOMAN 980514		size		213	
chr		M LOMAN 980514		dwg no		sheet	
appdr		CODJLMANS 980514		scale		3 of-	
sheet		revision		A2		85867	
index		sheet		5:1			

Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite de FCI S.A. est formellement interdite. © FCI S.A.

All rights strictly reserved. Reproduction or issue in third parties in any form without written authority from the proprietor. Property of FCI S.A. © FCI S.A.

