

TURCK

Level Sensors - Capacitive



Housing Style	Part Number	ID Number	Features	Embeddable Range (mm)	Nonembed. Range (mm)	Output
5.5 mm - Embeddable, Potted-In Cable 	BC 5-QF5.5-AN6X2/S250	S2620120	No Potentiometer	5	5	3-Wire DC NPN
	BC10-QF5.5-AN6X2	S2620121		10	10	
	BC10-QF5.5-AN6X2/S250	S2620119	No Potentiometer	10	10	
	BC10-QF5.5-RN6X2			10	10	
	BC10-QF5.5-RN6X2/S250		No Potentiometer	10	10	3-Wire DC PNP
	BC 5-QF5.5-AP6X2/S250	S2620116	No Potentiometer	5	5	
	BC 5-QF5.5-RP6X2/S250		No Potentiometer	5	5	
	BC10-QF5.5-AP6X2	S2620117		10	10	
	BC10-QF5.5-AP6X2/S250	S2620115	No Potentiometer	10	10	
	BC10-QF5.5-RP6X2		Normally Closed	10	10	
	BC10-QF5.5-RP6X2/S250		No Potentiometer	10	10	
	BC 5-QF5.5-Y1X/S250	S2030000	No Potentiometer	5	5	2-Wire DC NAMUR
5.5 mm - Embeddable, Potted-In Cable, w/Potentiometer Cover 	BC10-QF5.5-AN6X2/S932	S2620137	Covered Pot.	10	10	3-Wire DC NPN
	BC10-QF5.5-RN6X2/S932	S2620140	Covered Pot.	10	10	
	BC10-QF5.5-AP6X2/S932	S2620109	Covered Pot.	10	10	3-Wire DC PNP
	BC10-QF5.5-RP6X2/S932	S2620141	Covered Pot.	10	10	
8 mm - Embeddable, Potted-In Cable 	BC 5-Q08-AN6X2/S250	S2620100	No Potentiometer	5	5	3-Wire DC NPN
	BC 5-Q08-AP6X2/S250	S2620000	No Potentiometer	5	5	3-Wire DC PNP
8 mm - Embeddable, <i>picofast</i>® Connector 	BC 5-Q08-AN6X2-V1131/S250	S2621100	No Potentiometer	5	5	3-Wire DC NPN
	BC 5-Q08-AP6X2-V1131/S250	S2621000	No Potentiometer	5	5	3-Wire DC PNP

"/S250" designates without potentiometer.

"/S932" designates Covered potentiometer.

Level Sensors - Capacitive

Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection Class	Housing Material	Face/ Front Cap	Power LED	Output LED	Mating Cord, Cable Length/ Jacket	Wiring Diagram #	Wiring Diagrams
10-30 VDC	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	1	Diagram 1
	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	1	
	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	1	
	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	5	
	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	5	
10-30 VDC	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	2	Diagram 2
	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	6	
	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	2	
	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	2	
	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	6	
5-30 VDC	100	Remote	-25 to +70	IP67	PP	PP	N/A	YE	2M/TPU	5	Diagram 3
10-30 VDC	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	1	Diagram 4
	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	5	
10-30 VDC	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	2	Diagram 5
	100	≤200	-25 to +70	IP67	PP	PP	GN	YE	2M/TPU	6	
10-30 VDC	100	≤200	-25 to +70	IP67	Zinc	PA 12	GN	YE	2M/TPU	1	Diagram 6
10-30 VDC	100	≤200	-25 to +70	IP67	Zinc	PA 12	GN	YE	2M/TPU	2	
10-30 VDC	100	≤200	-25 to +70	IP67	Zinc	PA 12	GN	YE	PKG 3Z-*	3	
10-30 VDC	100	≤200	-25 to +70	IP67	Zinc	PA 12	GN	YE	PKG 3Z-*	4	
10-30 VDC	100	≤200	-25 to +70	IP67	Zinc	PA 12	GN	YE	PKG 3Z-*	4	

* Length in meters.