

Frequency Mixer

ZX05-C24

Level 7 (LO Power +7 dBm) 300 to 2400 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

Coaxial Connections

LO	1
RF	2
IF	3

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.74	.90	.54	.50	.04	.16	.29
18.80	22.86	13.72	12.70	1.02	4.06	7.37


H	J	K	L	M	N	wt
.37	--	.122	.496	.106	.122	grams
9.40	--	3.10	12.60	2.69	3.10	20.0

Features

- rugged construction
- small size
- low conversion loss
- high L-R isolation
- protected by US Patents 6,790,049 & 7,027,795

Applications

- cellular
- PCS
- instrumentation
- satellite communication



CASE STYLE: FL905

Connectors	Model	Price	Qty.
SMA	ZX05-C24-S	\$37.95 ea.	(1-24)

Electrical Specifications (T_{AMB}=25°C)

FREQUENCY (MHz)		CONVERSION LOSS (dB)		LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)	
LO/RF	IF	Mid-Band m							
f _L -f _U		$\overline{X}$	σ	Total Range Max.	Typ.	Min.	Typ.	Min.	Typ.
300-2400	DC-700	6.1	0.1	8.9	40	25	25	15	10

1 dB COMP.: +1 dBm typ.
m= mid band [2f_L to f_U/2]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm
300.10	330.11	5.68	51.87	22.71	2.06	11.84
407.79	437.80	5.25	41.41	23.57	1.67	3.88
515.49	545.50	6.06	40.47	26.07	3.26	2.16
677.02	707.03	5.89	42.94	25.56	3.01	2.01
784.72	814.73	5.84	40.24	25.84	3.01	2.70
892.41	922.42	6.34	40.63	27.58	3.33	3.30
1000.10	1030.11	6.20	40.86	24.68	2.91	3.30
1107.79	1137.80	6.30	41.49	25.50	2.85	3.64
1215.49	1245.50	6.30	42.28	28.67	2.80	4.25
1323.18	1353.19	6.52	42.85	31.25	2.63	4.29
1430.87	1460.88	5.50	42.88	31.79	1.90	3.30
1538.56	1568.57	5.12	39.85	29.89	1.21	2.08
1646.25	1676.26	4.99	35.18	30.66	1.28	1.95
1753.95	1783.96	5.24	35.73	27.45	1.34	1.73
1861.64	1891.65	5.46	32.74	25.30	1.75	1.89
1969.33	1999.34	5.85	32.38	24.75	2.29	2.21
2077.02	2107.03	6.40	32.49	29.12	2.96	2.39
2184.72	2214.73	6.71	31.71	25.37	3.22	2.63
2292.41	2322.42	6.43	33.89	24.61	2.63	2.96
2400.10	2370.09	6.47	34.51	25.21	2.41	3.22

Electrical Schematic

