

GLASS PASSIVATED SUPER FAST RECTIFIER

VOLTAGE RANGE 50 to 400 Volts CURRENT 16 Amperes

FEATURES


- * Low switching noise
- * Low forward voltage drop
- * Low thermal resistance
- * High current capability
- * Super fast switching speed
- * High reliability
- * Good for switching mode circuit

MECHANICAL DATA


- * Case: TO-220 molded plastic
- * Epoxy: Device has UL flammability classification 94V-O
- * Lead: MIL-STD-202E method 208C guaranteed
- * Mounting position: Any
- * Weight: 2.24 grams

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25 °C ambient temperature unless otherwise specified.
Single phase, half wave, 60 Hz, resistive or inductive load.
For capacitive load, derate current by 20%.



TO-220



MAXIMUM RATINGS (At $T_A = 25^\circ\text{C}$ unless otherwise noted)

RATINGS	SYMBOL	SF161C	SF162C	SF163C	SF164C	SF165C	SF166C	UNITS
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	150	200	300	400	Volts
Maximum RMS Voltage	V_{RMS}	35	70	105	140	210	280	Volts
Maximum DC Blocking Voltage	V_{DC}	50	100	150	200	300	400	Volts
Maximum Average Forward Rectified Current at $T_C = 125^{\circ}C$	I_O	16.0						Amps
Peak Forward Surge Current 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)	I_{FSM}	150						Amps
Typical Thermal Resistance	$R_{\theta JC}$	3						$^{\circ}C/W$
Typical Junction Capacitance (Note 2)	C_j	50				30		pF
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to + 150						$^{\circ}C$

ELECTRICAL CHARACTERISTICS (At $T_A = 25^\circ\text{C}$ unless otherwise noted)

CHARACTERISTICS		SYMBOL	SF161C	SF162C	SF163C	SF164C	SF165C	SF166C	UNITS
Maximum Instantaneous Forward Voltage at 8.0A DC		V _F	1.0				1.35		Volts
Maximum DC Reverse Current	@T _C = 25°C	I _R	10						uAmps
at Rated DC Blocking Voltage	@T _C = 100°C		500						
Maximum Reverse Recovery Time (Note 1)		t _{rr}	35				50		nSec

NOTES : 1. Test Conditions: $I_F = 0.5A$, $I_R = -1.0A$, $IRR = -0.25A$
2. Measured at 1 MHz and applied reverse voltage of 4.0 volts.
3. Suffix "A" =Common Anode.

RATING AND CHARACTERISTIC CURVES (SF161C THRU SF166C)

