





PRODUCT NO.
78208-XYHLF

LEAD FREE OPTION
NOTE 6, 7 & 8
NO. OF POSITIONS
SEE TABLE
PIN PLATING
BASE P/N



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADER			
ltr ecn no dr date				tolerances unless otherwise specified						title			
L ELX-N-011912 JZ 05/31/12				angles		linear		XX±.01/XX±0.3		INCH/MM		FRICITION LATCH HEADER	
M ELX-N-21463 MZ 07/22/15				0±.2°				XXX±.005/XXX±0.13		scale 3:1		SINGLE ROW, R/A	
								XXX±.0020/XXX±0.051					
G M05-0134 ERE 06/15/05				enr		M.CLOUSER		11/26/90				dwg no sheet1 of 3 size	
H M06-0256 MHT 9/07/06				dgr		C.TREXLER		11/26/90				78208 A	
J M08-0023 MHT 1/28/08				chr		C.TREXLER		11/26/90					
K M08-0291 MHT 10/08/08				appd		C.TREXLER		11/26/90					
sheet index		revision sheet		M M M								type Product Customer Drawing	
				1 2 3									

PRODUCT NO.	NO.OF POS.	DIM K	DIM L	TAIL LENGTH DIM M
78208-X03	1 X 3	.300/7.62	.200/5.08	.120/3.05
-X04	1 X 4	.400/10.16	.300/7.62	
-X05	1 X 5	.500/12.70	.400/10.16	
-X06	1 X 6	.600/15.24	.500/12.70	
-X07	1 X 7	.700/17.78	.600/15.24	
-X08	1 X 8	.800/20.32	.700/17.78	
-X09	1 X 9	.900/22.86	.800/20.32	
-X10	1 X 10	1.000/25.40	.900/22.86	
-X11	1 X 11	1.100/27.94	1.000/25.40	
-X12	1 X 12	1.200/30.48	1.100/27.94	
-X13	1 X 13	1.300/33.02	1.200/30.48	
-X14	1 X 14	1.400/35.56	1.300/33.02	
78208-X15	1 X 15	1.500/38.10	1.400/35.56	.120/3.05
78208-X43	1 X 3	.300/7.62	.200/5.08	.190/4.83

PIN PLATING CODES

-1YY	30u"/.76u (SEE NOTE 9) 50u"/1.27u Ni
-2YY	15u"/.38u (SEE NOTE 9) 50u"/1.27u Ni
-3YY	50u"/1.27u (SEE NOTE 9) 50u"/1.27u Ni
-4YY	100u"/2.54u MIN Sn 50u"/1.27u Ni (SEE NOTE 10)
-4YYHLF	
-5YY	15u"/.38u (SEE NOTE 9) 50u"/1.27u Ni
-6YY	30u"/.76u (SEE NOTE 9) 50u"/1.27u Ni
-7YY	30u"/.76u (SEE NOTE 9) OVER 50u"/1.27u Ni
-8YY	15u"/.38u (SEE NOTE 9) OVER 50u"/1.27u Ni

NOTES:

1. MOLDING MAT'L: GLASS REINFORCED PCT OR MINRAL FILLED LCP, COLOR: BLACK
FLAME RETARDANT PER UL-94V-0
MAXIMUM OPERATING TEMPERATURE 130° C.

2. PIN MATERIAL: 3/4 HD PHOS. BRZ.

3. NO SLOTS ON 1 X 5 POSITION OR SMALLER PRODUCT. THE CENTER KEY SLOT WILL BE ON ALL HEADERS REGARDLESS OF SIZE.

4. TWO NON-CRITICAL SIDES OF PIN TIP NOT PLATED, BOTH ENDS.

5. COMPANY LOGO MAY APPEAR IN THIS AREA.

6. ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION, NOT AVAILABLE FOR -5YY, -5YYH, -6YY & -6YYH.

7. PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.

8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

9. PLATING OPTIONS:

PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON CONTACT OR TAIL, OPTIONALLY (78~295u"/2~7.5u) TIN ON TAIL.

10. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection ⊕	product family HEADER
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM	title
M					angles linear		FRICION LATCH HEADER SINGLE ROW, R/A
					0±2"	scale 3:1	
			dr	M.CLOUSER	11/26/90	FCI	dwg no
			enr	C.TREXLER	11/26/90		sheet2 of 3
			chr	C.TREXLER	11/26/90		size
			appd	C.TREXLER	11/26/90		A3
sheet index	revision sheet						type Product Customer Drawing

1		2		3		4		5		6	
PRODUCT NO.	NO.OF POS.	DIM K	DIM L	TAIL LENGTH DIM M	POLARIZATION PIN POSITION						
78208-X77	1 X 10	1.000/25.40	.900/22.86	.120/3.05	2/3/5/6/8/9						
78208-X78	1 X 4	1.000/25.40	.900/22.86	.120/3.05	2/3						

FCI

FCIconnect.com

Copyright FCI

mat'l. code		surface		tolerance		projection		product family	
		ISO 1302		ISO 406				HEADER	
				ISO 1101					
ltr		ecn	no	dr	date	tolerances unless otherwise specified		title	
M								FRICION LATCH HEADER	
						linear		INCH/MM	
						0±2°		scale 3:1	
						dr		M.CLOUSER 11/26/90	
						enr		C.TREXLER 11/26/90	
						chr		C.TREXLER 11/26/90	
						appd		C.TREXLER 11/26/90	
sheet		revision						dwg no	
index		sheet						sheet3 of 3	
								size	
								A3	
								type	
								Product Customer Drawing	