








PRODUCT NO.
SEE TABLE



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX ±.01				
P	V11058	JM	6/12/91		.XXX ±.005	projection	title QUICKIE P.C.B. CONNECTOR 10,14,26,30,34, & 50 POS.		
R	V50805	LSS	7/5/95		.XXXX ±.0020				
S	N05-0123	ZC	5/9/05		0' ±2"	INCH/MM	product family size dwg no		
T	N07-0199	WG	08/27/07	dr	J.MUSTARD 6/12/91	scale			
				enr	M.SMYK 6/12/91	2.5:1	A 65495		
				chr	W.FUNK 6/12/91				
				appd	M.SMYK 6/12/91		sheet index		
							revision sheet		
							T T 1 2		



	1	2								3		4
	NO. OF POS.	DIM "A"	DIM "B"	DIM "C" REF	SEE NOTE							
65495-017(LF)	10	. 450/11. 43	. 700/17. 78	. 100/2. 54	1							
-018(LF)					2							
-019(LF)					1							
-020(LF)					2							
-021(LF)	26	1. 250/31. 75	1. 500/38. 10	. 100/2. 54	1							
-022(LF)					2							
-023(LF)					1							
-024(LF)					2							
-025(LF)	34	1. 650/41. 91	1. 900/48. 26	. 100/2. 54	1							
-026(LF)					2							
-027(LF)					1							
-028(LF)					2							
-029(LF)	50	2. 450/62. 23	2. 700/68. 58	. 100/2. 54	1							
-030(LF)					2							
-031(LF)					1							
-032(LF)					2							
-033(LF)	14	. 650/16. 51	. 900/22. 86	. 100/2. 54	1							
-034(LF)					2							
-035(LF)					1							
-036(LF)					2							
-037(LF)	30	1. 450/36. 83	1. 700/43. 18	. 100/2. 54	1							
-038(LF)					2							
-039(LF)					1							
65495-040(LF)					2							

NOTES:

- ① 50u"/1.27uM MIN. Ni UNDERPLATE OVER ENTIRE TERMINAL. AND Au FLASH ON SOLDER TAIL ONLY.
- ② 65495-***: 150u"/3.81uM MIN. TIN/LEAD 93/7 OVER ENTIRE TERMINAL. 50u"/1.27uM MIN. Ni UNDERPLATE.
65495-***LF: 150u"/3.81uM MIN. MATTE TIN OVER ENTIRE TERMINAL. 50u"/1.27uM MIN. Ni UNDERPLATE.
- ③ SEE TA 247 FOR MORE INFORMATION.
- 4. PATTERN SHOWN FOR CENTER TEN CONTACTS IS TYPICAL FOR ALL CONNECTOR LENGTHS, EXCEPT 14 & 30 POSITIONS.
- 5. SUB-ASSEMBLY & COVER PACKED SEPARATELY.
- 6. THE HOUSING OF XXXXX-XYLF WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER PROCESS.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX ±.01/.0±.3	projection	title		
T					.XXX ±.005/.00±.13		QUICKIE P.C.B CONNECTOR		
					.XXX ±.0020/.000±.051		10,14,26,30,34,& 50 POS.		
				angles	0° ±2°		product family		
				dr	J.MUSTARD 6/11/91	INCH/MM	size		code
				enr	M.SMYK 6/11/91		dwg no		—
				chr	W.FUNK 6/11/91	scale	A		sheet
				appd	M.SMYK 6/11/91	1:1	65495		2 of
sheet index	revision sheet	T	2						