


	10	9	8	7	6	5	4	3	2	1	
F	MATERIAL NUMBER LOOSE PC.	ENGINEERING NUMBER LOOSE PC.	MATERIAL NUMBER ON TAPE	ENGINEERING NUMBER ON TAPE	STUD SIZE	STUD HOLE SIZE "S" ±.005/.13	"D"	"H"	"L"		F
	191640028	SB-227-06	191640948	SB-227-06T	#06	Ø.146/3.71	.37/9.4	.990/25.15	1.42/36.1		
	191640029	SB-227-08	191640949	SB-227-08T	#08	Ø.173/4.39	.40/10.2	.990/25.15	1.42/36.1		
	191640030	SB-227-10	191640950	SB-227-10T	#10	Ø.198/5.03	.40/10.2	.990/25.15	1.42/36.1		



- NOTES:
1. TERMINAL MATERIAL: COPPER ALLOY .031/0.79 THK.
 2. FINISH: ELECTRO TIN PLATE.
 3. INSULATION MATERIAL: PERMA-SEAL SHRINKABLE TUBING WITH HOT-MELT ADHESIVE INNER LINER. COLOR: BLUE.
 4. MWD = MAXIMUM WIRE INSULATION DIAMETER.

PROPOSED EC NO:	2005/06/28 2005/07/21 2005/07/21 2005/07/21	DRWN: SHADECK CHKD: ROSS APPR: JPAWLICK	DESCRIPTION	REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
								DRAWN BY	DATE	TITLE			
								4 PLACES ± --- ± ---	BE	02/09/03	PERMA-SEAL TERMINAL SPADE TERMINAL 16-14 AWG TAPE MOUNTED		
								3 PLACES ± --- ± ---	CHECKED BY	DATE			
								2 PLACES ± --- ± ---	HB	02/09/03			
		1 PLACE ± --- ± ---	APPROVED BY	DATE	 MOLEX INCORPORATED								
		ANGULAR ± .5 °	RD	02/09/03									
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.					
				SEE CHART		SD-19164-027		1 OF 1					
				SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								