

Ceramic

# Low Pass Filter

DC to 2600 MHz

NEW!

LFCN-2600



CASE STYLE: FV1206  
PRICE: \$1.99 ea. QTY (10-49)

## Maximum Ratings

|                            |                   |
|----------------------------|-------------------|
| Operating Temperature      | -55°C to 100°C    |
| Storage Temperature        | -55°C to 100°C    |
| RF Power Input*            | 10W max. at 25°C  |
| DC Current Input to Output | 0.5A max. at 25°C |


\*Passband rating, derate linearly to 3.5W at 100°C ambient.

## Pin Connections

|        |     |
|--------|-----|
| RF IN  | 1** |
| RF OUT | 3** |
| GROUND | 2,4 |

\*\*RF IN & RF OUT can be interchanged

## Outline Drawing



TOLERANCE UNLESS OTHERWISE STATED

2 PLACE DECIMALS: ±.01  
3 PLACE DECIMALS: ±.005


## Outline Dimensions (inch/mm)

| A    | B    | C    | D    | E    | F    | G    |
|------|------|------|------|------|------|------|
| .126 | .063 | .037 | .020 | .032 | .009 | .169 |
| 3.20 | 1.60 | 0.94 | 0.51 | 0.81 | 0.23 | 4.29 |

| H    | J    | K    | L    | M    | N    | P    | wt    |
|------|------|------|------|------|------|------|-------|
| .087 | .024 | .122 | .024 | .087 | .012 | .071 | grams |
| 2.21 | 0.61 | 3.10 | 0.61 | 2.21 | 0.30 | 1.80 | .020  |

Demo Board MCL P/N: TB-270  
Suggested PCB Layout (PL-137)



NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350 WITH DIELECTRIC THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

■ DENOTES PCB COPPER LAYOUT  
■ DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

## Features

- excellent power handling, 10W
- small size
- 7 sections
- temperature stable
- patent pending


## Applications

- harmonic rejection
- VHF/UHF transmitters/receivers
- lab use


## Low Pass Filter Electrical Specifications (T<sub>AMB</sub>=25°C)

| MODEL NO. | PASSBAND (MHz)<br>(loss < 1 dB)<br>Max. | fco, MHz<br>Nom.<br>(loss 3 dB)<br>Typ. | STOP BAND (MHz)<br>(loss, dB) |            |               | VSWR (:1)        |                  | NO. OF SECTIONS |
|-----------|-----------------------------------------|-----------------------------------------|-------------------------------|------------|---------------|------------------|------------------|-----------------|
|           |                                         |                                         | f 20<br>Min.                  | 30<br>Typ. | fr 20<br>Typ. | Stopband<br>Typ. | Passband<br>Typ. |                 |
| LFCN-2600 | DC-2600                                 | 3125                                    | 3750                          | 3900-6600  | 8400          | 20               | 1.2              | 7               |

## typical frequency response





## schematic



## Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|-----------------|---------------------|-----------|
| 100.00          | 0.10                | 1.02      |
| 1300.00         | 0.39                | 1.09      |
| 2100.00         | 0.61                | 1.15      |
| 2600.00         | 0.94                | 1.37      |
| 3000.00         | 1.97                | 1.98      |
| 3125.00         | 3.02                | 2.60      |
| 3300.00         | 6.03                | 4.66      |
| 3750.00         | 22.35               | 17.93     |
| 3900.00         | 28.99               | 22.29     |
| 4000.00         | 33.27               | 24.83     |
| 5000.00         | 32.82               | 36.97     |
| 6600.00         | 32.00               | 27.59     |
| 8000.00         | 22.00               | 21.73     |
| 8400.00         | 20.08               | 19.54     |
| 9000.00         | 17.02               | 16.41     |



**Mini-Circuits®**

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

REV. OR  
M93409  
LFCN-2600  
EDR-6783/5  
RVN/AD/CP  
040817