


MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

**SWITCH-TOGGLE
FLUSH KEY**

CATALOG LISTING
**4TP201 SERIES
CHART 1**

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH


5	CATALOG LISTING	3 CIRCUIT MADE WITH BUTTON DEPRESSED ON			ELECTRICAL DATA
		LUG SIDE (1-2, 4-5, 7-8, 10-11)	CENTER (1-2, 4-5, 7-8, 10-11)	OPPOSITE LUG (2-3, 5-6, 8-9, 11-12)	
FAA-PMA	(B)	ON	OFF	ON	L191 15A 125, 250, 277 VAC 1/2HP 125 VAC 1HP 250, 277 VAC 5A 125 VAC "L" UL CE
	(D)	OFF	NONE	ON	
	4TP201-3	ON	NONE	ON	
	4TP201-21	NONE	OFF	ON	
	4TP201-31	NONE	ON	ON	
	4TP201-4	MOM OFF	NONE	ON	L192 10A 125, 250, 277 VAC 1/4HP 125 VAC, 1/2HP 250, 277 VAC 3A 125 VAC "L" UL CE
	(B)	MOM ON	OFF	ON	
	4TP201-6	MOM ON	NONE	OFF	
	4TP201-7	MOM ON	OFF	MOM ON	
	4TP201-8	MOM ON	NONE	ON	
	4TP201-51	NONE	ON	MOM ON	
	4TP201-61	MOM ON	OFF	NONE	



NOTES

- 1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
- 2 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
- 3 APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS
- 4 SCREWS FURNISHED UNASSEMBLED
- 5 FAA-PMA MUST BE MARKED ON SWITCH

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ±.030

TWO PLACE (.00) ±.015

THREE PLACE (.000) ±.005

ANGLES ±

WEIGHT .22 LB EST