



TL3365 SERIES TACT SWITCH



APPLICATIONS / MARKETS




Audio / Visual



Computer Peripherals




Consumer Electronics



Instrumentation



Telecommunication



Medical Equipment

RoHS

SPECIFICATIONS

Electrical Rating: 50mA @ 12VDC
Electrical Life: 100,000 Cycles
Mechanical Life: 100,000 Cycles
Contact Resistance: 100mΩ Max. Initial
Insulation Resistance: 100M Ω at 100VDC
Dielectric Strength: 250VAC for 1 min.
Operating Temperature: -20°C to 70°C
Storage Temperature: -30°C to 80°C
Operating Force: 180 gf
Travel: 0.2mm
Contact Arrangement: SPST

FEATURES & BENEFITS

- Ultraminiature
- Surface mount

PART NUMBER CONFIGURATOR

Series



TL

Model



3365

Actuator
Option



A - 2.25mm

Actuation
Force



F180 - 180 gf

Contact
Material



Q - Silver

Termination



Q - Gullwing

Specifications subject to change without notice



E-SWITCH®

www.e-switch.com

800.867.2717

2

TL3365 SERIES TACT SWITCH

BODY DIMENSIONS

