





mat'l. code				surface				tolerance				projection				product family							
				ISO 1302 ✓				ISO 406 ISO 1101								QUICKIE							
ltr		ecn		nodr		date		tolerances unless otherwise specified												title			
H		N05-0123		ZC		5/9/05		angles		linear		.XX±.01/.XX±0.3		INCH/MM		HEADER, QUICKIE, SLIM LINE							
J		N07-0151		WG		8/02/07						.XXX±.005/.XXX±0.13				VERTICAL, 4-WALL							
K		ELX-N-012098		J.Z		2012-07-04		±2'				.XXX±.0020/.XXX±0.051		scale 2:1									
								dr		M. CLOUSER		7/11/90				dwg no		sheet 1 of 10		size			
								engr		M. SMYK		7/11/90				88880		A3					
								chr		M. SMYK		8/21/91											
								appd		M. SMYK		8/21/91				type		Product Customer Drawing					
sheet		revision		K		K		K		K		K		K		K		K		K		K	
index		sheet		1		2		3		4		5		6		7		8		9		10	

PRODUCT NUMBER
SEE TABLE

HEADER STYLE



RECOMMENDED BOARD LAYOUT

NOTES:

1. SAME POSITION TOLERANCE APPLIES TO BOTH ENDS OF PINS.
2. MOLDING MATERIAL: GLASS-FILLED POLYESTER, FLAME RETARDANT PER UL 94 V-0, COLOR: BLACK.
3. 1° MAX. DRAFT PERMISSIBLE ON ALL SURFACES.
4. 3 LBS./1.36 KG MIN. TERMINAL PULL-OUT FORCE.
5. TERMINAL MATERIAL: PHOSPHORUS BRONZE.
6. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
7. SEE 68751 FOR LATCHES.
8. PART NUMBERS WITH "R" FOLLOWING THE PART NUMBER (EXAMPLE 66506-326 R) HAS RETENTION. (ONLY PARTS WITH .105, .120, AND .150 ROUND OR SQUARE TAILS CAN HAVE RETENTION.) LOCATION IS MANUFACTURERS OPTION.
FOR CONNECTORS:
RETENTIVE LEG APPLICABLE TO TAIL LENGTHS .125/3.18 MAX.
5LB/2.3KG MAX INSERTION FORCE AND .25LB/1KG MIN RETENTION FORCE
PER RETENTIVE PIN USING .062/1.57 THICK CIRCUIT BOARD AND RECOMMENDED HOLE PATTERN. RETENTIVE LOCATION AT THE DISCRETION OF THE MANUFACTURER. RETENTION PIN MAY BE SHIFTED TO NEXT POSITION.
9. PART NUMBERS WITH "T" FOLLOWING PART NUMBER (EXAMPLE 66506-068 T IS PACKED IN TUBES.) (CALL PRODUCT MANAGER FOR AVAILABILITY.)
10. MAY BE ORDERED WITH "G" PACK PACKAGING BY ADDING "G" TO DASH NUMBER.
11. UNDER PLATING: 50 μ "/1.27 μ m Ni.
12. ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION & PART NUMBERS WITH "LF" SUFFIX ADDED IN THE TABLE ARE LEAD FREE.
13. IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
14. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
15. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."
16. PLATING OPTIONS:
PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON CONTACT OR TAIL, OPTIONALLY TIN ON TAIL.

mat'l. code		surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family QUICKIE
l	tr	ec	n	dr	date
K					
		angles	linear	tolerances unless otherwise specified	
				X.XX ± .01 / X.XX ± .03	
				.XXX ± .005 / .XXX ± .013	
		±2°		.XXXX ± .0020 / .XXXX ± .0051	
		dr	M. CLOUSER	7/11/90	
		engr	M. SMYK	7/11/90	
		chr	M. SMYK	8/21/91	
		appd	M. SMYK	8/21/91	
sheet	revision				
index	sheet				



FCIconnect.com

Copyright FCI

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-001	2 X 5	B	. 400/10. 16	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	NOTE 2
-002				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-003				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-004				. 105/2. 67	150u"/3. 81u TIN	
-005				. 150/3. 81	150u"/3. 81u TIN	
-006	2 X 5	B	. 400/10. 16	. 675/17. 15	150u"/3. 81u TIN	
-007	2 X 10	D	. 900/22. 86	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-008				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-009				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-010				. 105/2. 67	150u"/3. 81u TIN	
-011				. 150/3. 81	150u"/3. 81u TIN	
-012	2 X 10		. 900/22. 86	. 675/17. 15	150u"/3. 81u TIN	
-013	2 X 13		1. 200/30. 48	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-014				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-015				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-016				. 105/2. 67	150u"/3. 81u TIN	
-017				. 150/3. 81	150u"/3. 81u TIN	
-018	2 X 13		1. 200/30. 48	. 675/17. 15	150u"/3. 81u TIN	
-019	2 X 17		1. 600/40. 64	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-020				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-021				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-022				. 105/2. 67	150u"/3. 81u TIN	
-023				. 150/3. 81	150u"/3. 81u TIN	
-024	2 X 17		1. 600/40. 64	. 675/17. 15	150u"/3. 81u TIN	
-025	2 X 20		1. 900/48. 26	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-026				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-027				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-028				. 105/2. 67	150u"/3. 81u TIN	
-029				. 150/3. 81	150u"/3. 81u TIN	
-030	2 X 20		1. 900/48. 26	. 675/17. 15	150u"/3. 81u TIN	
-031	2 X 25		2. 400/60. 96	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-032				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-033				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-034				. 105/2. 67	150u"/3. 81u TIN	
88880-035	2 X 25	D	2. 400/60. 96	. 150/3. 81	150u"/3. 81u TIN	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr ecn nchr date		tolerances unless otherwise specified		angles linear ±2'		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
						scale 1:1		dwg no 88880	
				dr M. CLOUSER 7/11/90				sheet 5 of 10 size A3	
				engr M. SMYK 7/11/90					
				chr M. SMYK 8/21/91					
				appd M. SMYK 8/21/91				type Product Customer Drawing	
sheet index		revision sheet							



FCIconnect.com

Copyright FCI

D

PRODUCT NO.	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-036	2 X 25	D	2. 400/60. 96	. 675/17. 15	150u" /3. 81u TIN	NOTE 2
-037	2 X 7	C	. 600/15. 24	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-038				. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-039				. 675/17. 15	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-040				. 105/2. 67	150u" /3. 81u TIN	
-041				. 150/3. 81	150u" /3. 81u TIN	
-042	2 X 7	C	. 600/15. 24	. 675/17. 15	150u" /3. 81u TIN	
-043	2 X 8	D	. 700/17. 78	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-044				. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-045				. 675/17. 15	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-046				. 105/2. 67	150u" /3. 81u TIN	
-047				. 150/3. 81	150u" /3. 81u TIN	
-048	2 X 8	D	. 700/17. 78	. 675/17. 15	150u" /3. 81u TIN	
-049	2 X 5	B	. 400/10. 16	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-050	2 X 10	D	. 900/22. 86			
-051	2 X 13		1. 200/30. 48			
-052	2 X 17		1. 600/40. 64			
-053	2 X 20		1. 900/48. 26			
-054	2 X 25	D	2. 400/60. 96			
-055	2 X 7	C	. 600/15. 24			
-056	2 X 8	D	. 700/17. 78	. 150/3. 81		
-057	2 X 30		2. 900/73. 66	. 105/2. 67		
-058				. 150/3. 81		
-059				. 675/17. 15	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-060				. 105/2. 67	150u" /3. 81u TIN	
-061				. 150/3. 81	150u" /3. 81u TIN	
-062				. 675/17. 15	150u" /3. 81u TIN	
-063				. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-064				. 150/3. 81		
-065	2 X 30	D	2. 900/73. 66	. 675/17. 15		
-066	2 X 5	B	. 400/10. 16	. 105/2. 67		
-067	2 X 5	B	. 400/10. 16	. 675/17. 15		
-068	2 X 7	C	. 600/15. 24	. 105/2. 67		
-069	2 X 7	C	. 600/15. 24	. 675/17. 15		
88880-070	2 X 8	D	. 700/17. 78	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		linear		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
K		angles		±2"		scale 1:1		dwg no 88880	
		dir		M. CLOUSER		7/11/90		shee# of 10 size A3	
		engr		M. SMYK		7/11/90			
		chr		M. SMYK		8/21/91			
		appd		M. SMYK		8/21/91		type Product Customer Drawing	
sheet index		revision sheet							

1

2 3

4

5

6

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING		PLASTIC MATERIAL
88880-071	2 X 8	D	. 700/17. 78	. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni		NOTE 2
-072	2 X 10		. 900/22. 86	. 105/2. 67			
-073	2 X 10		. 900/22. 86	. 675/17. 15			
-074	2 X 13		1. 200/30. 48	. 105/2. 67			
-075	2 X 13		1. 200/30. 48	. 675/17. 15			
-076	2 X 17		1. 600/40. 64	. 105/2. 67			
-077	2 X 17		1. 600/40. 64	. 675/17. 15			
-078	2 X 20		1. 900/48. 26	. 105/2. 67			
-079	2 X 20		1. 900/48. 26	. 675/17. 15			
-080	2 X 25		2. 400/60. 96	. 105/2. 67			
-081	2 X 25	D	2. 400/60. 96	. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni		
-082	2 X 5	B	. 400/10. 16	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni		
-083	2 X 5	B	. 400/10. 16	. 150/3. 81			
-084	2 X 5	B	. 400/10. 16	. 675/17. 15			
-085	2 X 7	C	. 600/15. 24	. 105/2. 67			
-086	2 X 7	C	. 600/15. 24	. 150/3. 81			
-087	2 X 7	C	. 600/15. 24	. 675/17. 15			
-088	2 X 8	D	. 700/17. 78	. 105/2. 67			
-089	2 X 8		. 700/17. 78	. 150/3. 81			
-090	2 X 8		. 700/17. 78	. 675/17. 15			
-091	2 X 10		. 900/22. 86	. 105/2. 67			
-092	2 X 10		. 900/22. 86	. 150/3. 81			
-093	2 X 10		. 900/22. 86	. 675/17. 15			
-094	2 X 13		1. 200/30. 48	. 105/2. 67			
-095	2 X 13		1. 200/30. 48	. 150/3. 81			
-096	2 X 13		1. 200/30. 48	. 675/17. 15			
-097	2 X 17		1. 600/40. 64	. 105/2. 67			
-098	2 X 17		1. 600/40. 64	. 150/3. 81			
-099	2 X 17		1. 600/40. 64	. 675/17. 15			
-100	2 X 20		1. 900/48. 26	. 105/2. 67			
-101	2 X 20		1. 900/48. 26	. 150/3. 81			
-102	2 X 20		1. 900/48. 26	. 675/17. 15			
-103	2 X 25		2. 400/60. 96	. 105/2. 67			
-104	2 X 25		2. 400/60. 96	. 150/3. 81			
88880-105	2 X 25	D	2. 400/60. 96	. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni		NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection ⊕ ↖		product family QUICKIE	
ltr ecn nodr		date		tolerances unless otherwise specified		INCH/MM		title	
K				angles	linear			HEADER, QUICKIE, SLIM LINE	
								VERTICAL, 4-WALL	
				±2°		scale 1:1		dwg no	
				dir	M. CLOUSER	7/11/90	shee 5 of 10 size		
				engr	M. SMYK	7/11/90	88880 A3		
				chr	M. SMYK	8/21/91	type Product Customer Drawing		
				appd	M. SMYK	8/21/91			
sheet index	revision sheet								

1				2		3								4		5		6	
PRODUCT NO.		SIZE	STYLE	DIM C	DIM J	PIN PLATING				PLASTIC MATERIAL									
NOTE 8 & 9																			
88880-106		2 X 30	D	2. 900/73. 66	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni				NOTE 2									
-107		2 X 30	D	2. 900/73. 66	. 150/3. 81	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-108		2 X 30	D	2. 900/73. 66	. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-109		2 X 5	B	. 400/10. 16	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-110					. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-111					. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-112					. 105/2. 67	150u"/3. 81u TIN													
-113					. 150/3. 81	150u"/3. 81u TIN													
-114					. 675/17. 15	150u"/3. 81u TIN													
-115					. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-116					. 150/3. 81	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-117					. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-118					. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-119					. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
88880-120		2 X 5	B	. 400/10. 16	. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni				NOTE 2									
88880-121		DISCONTINUED																	
THRU																			
88880-216																			
88880-217		2 X 12	D	1. 100/27. 94	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni				NOTE 2									
-218						30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-219						30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-220					. 105/2. 67	150u"/3. 81u TIN													
-221					. 150/3. 81	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-222						30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-223						30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-224					. 150/3. 81	150u"/3. 81u TIN													
-225					. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-226						30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-227						30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-228		2 X 12		1. 100/27. 94	. 675/17. 15	150u"/3. 81u TIN													
-229		2 X 15		1. 400/35. 56	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-230						30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-231						30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni													
-232					. 105/2. 67	150u"/3. 81u TIN													
88880-233		2 X 15	D	1. 400/35. 56	. 150/3. 81	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni				NOTE 2									

FCI

FCIconnect.com

Copyright FCI

mat'l. code

surface

ISO 1302

tolerance

ISO 406

ISO 1101

projection

product family

QUICKIE

title

HEADER, QUICKIE, SLIM LINE

VERTICAL, 4-WALL

scale 1:1

dwg no

88880

sheet 6 of 10

size

A3

type

Product Customer Drawing

sheet index

revision

sheet

dr

M. CLOUSER

7/11/90

engr

M. SMYK

7/11/90

chr

M. SMYK

8/21/91

appd

M. SMYK

8/21/91

4

PDS: Rev :K

STATUS

Released

Printed: Jul 10, 2012



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-234	2 X 15	D	1. 400/35. 56	. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	NOTE 2
-235				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-236				. 150/3. 81	150u"/3. 81u TIN	
-237				. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-238					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-239					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-240	2 X 15		1. 400/35. 56	. 675/17. 15	150u"/3. 81u TIN	
-241	2 X 22		2. 100/53. 34	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-242					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-243					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-244				. 105/2. 67	150u"/3. 81u TIN	
-245				. 150/3. 81	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-246					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-247					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-248				. 150/3. 81	150u"/3. 81u TIN	
-249				. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-250					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-251					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-252	2 X 22					
88880-253	2 X 17	D	1. 600/40. 64	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	NOTE 2
88880-254	UNAVAILABLE					
THRU						
88880-279	UNAVAILABLE					
88880-280	2 X 10	D	. 900/22. 86	. 105/2. 67	150u"/3. 81u TIN	NOTE 2
88880-281	UNAVAILABLE					
THRU						
88880-306						

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection ⊕		product family QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		linear		INCH/MM		title	
K		angles		XXX-01/XXX-03				HEADER, QUICKIE, SLIM LINE	
		±2"		XXX-005/XXX-013				VERTICAL, 4-WALL	
				XXX-0020/XXX-0051		scale 1:1		dwg no	
		dr		M. CLOUSER 7/11/90		FCI		shee 7 of 10 size	
		engr		M. SMYK 7/11/90				88880 A3	
		chr		M. SMYK 8/21/91					
		appd		M. SMYK 8/21/91				type Product Customer Drawing	
sheet index		revision sheet							



Copyright FCI

A

B

C

D

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-307	2 X 5	B	. 400/10. 16	. 097/2. 46	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2
-308	2 X 5	B	. 400/10. 16			
-309	2 X 7	C	. 600/15. 24			
-310	2 X 8	D	. 700/17. 78			
-311	2 X 10		. 900/22. 86			
-312	2 X 12		1. 100/27. 94			
-313	2 X 13		1. 200/30. 48			
-314	2 X 15		1. 400/35. 56			
-315	2 X 17		1. 600/40. 64			
-316	2 X 20		1. 900/48. 26			
-317	2 X 22		2. 100/53. 34			
-318	2 X 25		2. 400/60. 96			
-319	2 X 30		2. 900/73. 66	. 097/2. 46		
-320	2 X 8		. 700/17. 78	. 105/2. 67		
-321	2 X 25		2. 400/60. 96		30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-322	2 X 8		. 700/17. 78		50u" /1. 27u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-323	2 X 17		1. 600/40. 64	. 105/2. 67	50u" /1. 27u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-324	2 X 25		2. 400/60. 96	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-325	2 X 25		2. 400/60. 96	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-326	2 X 10		. 900/22. 86	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-327	2 X 17		1. 600/40. 64	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-328	2 X 25		2. 400/60. 96	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-329	2 X 13		1. 200/30. 48	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-330	2 X 25		2. 400/60. 96		15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-331	2 X 30		2. 900/73. 66		15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-332	2 X 17		1. 600/40. 64		15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-333	2 X 20		1. 900/48. 26	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-334	2 X 10		. 900/22. 86	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-335	2 X 20		1. 900/48. 26	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-336	2 X 22	D	2. 100/53. 34	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-337	2 X 12	D	1. 100/27. 94	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-338	2 X 5	B	. 400/10. 16	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-339	2 X 4	B	. 300/7. 62	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
88880-340	2 X 10	D	. 900/22. 86	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		linear		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
K		angles		±2°		scale 1:1		dwg no 88880	
		dr M. CLOUSER		7/11/90				shee 8 of 10 size A3	
		engr M. SMYK		7/11/90					
		chr M. SMYK		8/21/91					
		appd M. SMYK		8/21/91				type Product Customer Drawing	
sheet index		revision sheet							

A

B

C

D

1

2 3

4

5

6

PRODUCT NO.	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
NOTE 8 & 9						
88880-341	2 X 17	D	1.600/40.64	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-342	2 X 10	D	.900/22.86	.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-343	2 X 17	D	1.600/40.64	.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-344	U N A S S I G N E D					
-345	2 X 20	D	1.900/48.26	.120/3.05	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-346	U N A S S I G N E D					
-347	U N A S S I G N E D					
-348	2 X 5	B	.400/10.16	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-349	2 X 7	C	.600/15.24			
-350	2 X 8	D	.700/17.78			
-351	2 X 10		.900/22.86			
-352	2 X 13		1.200/30.48			
-353	2 X 17		1.600/40.64			
-354	2 X 20		1.900/48.26			
-355	2 X 22		2.100/53.34			
-356	2 X 25		2.400/60.96			
-357	2 X 30		2.900/73.66	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-358	2 X 10		.900/22.86	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-359	2 X 17		1.600/40.64	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-360	2 X 12	D	1.100/27.94	.295/7.49	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-361	U N A S S I G N E D					
-362	2 X 5	B	.400/10.16	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-363	2 X 8	D	.700/17.78			
-364	2 X 10	D	.900/22.86			
-365	2 X 15	D	1.400/35.56			
-366	2 X 17	D	1.600/40.64	.105/2.67		
-367	2 X 5	B	.400/10.16	.150/3.81		
-368	2 X 17	D	1.600/40.64	.150/3.81		
88880-369	2 X 25	D	2.400/60.96	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2

mat'l. code				surface / tolerance ISO 1302 ✓ / ISO 406 ISO 1101		projection		product family QUICKIE	
l t r e c n n o d r				date		tolerances unless otherwise specified		title	
K						angles		linear	
						±2°		X.XX ± .01 / X.XX ± .03	
								X.XX ± .005 / X.XX ± .013	
								X.XX ± .0020 / X.XX ± .0051	
						scale 1:1		INCH/MM	
						FCI		dwg no	
								shee 9 of 10	
								size	
								88880	
								A3	
								type Product Customer Drawing	
sheet				revision					
index				sheet					



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL	POLARIZED PIN
88880-404	2 X 20	D	1.900/48.26	.120/3.05	15μ/0.38μm MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2	20
↑ -410	2 X 25	↑	2.400/60.96	↑	↑	↑	-
↑ -418	2 X 10	↑	.900/22.86	↑	↑	↑	14
↑ -423	2 X 25	↓	2.400/60.96	↑	↑	↑	25
↑ -426	2 X 17	D	1.600/40.64	↓	↑	↑	3
88880-427	2 X 5	B	.400/10.16	.120/3.05	15μ/0.38μm MIN (NOTE 16) OVER 50u"/1.27u Ni	↑	1
88880-428	2 X 5	B	.400/10.16	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2	10

mat'l. code			surface	tolerance	projection	product family		
			ISO 1302 ✓	ISO 406 ISO 1101		QUICKIE		
l	tr	ec	n	d		title		
K					INCH/MM	HEADER, QUICKIE, SLIM LINE		
						VERTICAL, 4-WALL		
					scale 1:1	dwg no		
						88880		
						sheet 10 of 10		
						A3		
						type Product Customer Drawing		
sheet	revision							
index	sheet							