


HBL5266C




Black and white nylon.

Product Specifications

Device Type	Plug
Body Style	Straight
Standard	NEMA
Amperage	15A
Voltage	125V
Poles and Wires	2 Pole, 3 Wire Grounding
Hospital Grade ?	No
Plug/Connector Grade	Insulgrip
Color	 Black
NEMA No.	5-15P
Horsepower	0.5
Cord Dia.	.230"-.720" (5.8-18.3)
Description	Straight Blade Plug
Type	2 Pole, 3 Wire, Grounding
Rating	15A,125V
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280
IP Suitability	IP20
Housing Material	Nylon-Black
Blade Holder Material	Nylon-Natural
Retainer Material	Polycarbonate-Clear
Cord Clamp Material	Nylon-Natural
Contact Blades Material	.060" (1.5) Brass
Ground Contact Blade Material	.040" (1.0) Copper Alloy
Terminal Screw Material	#8-32 Brass /Ni plated for neutral
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)
Wire Clamps Material	.062" (1.8) Steel-nickel finish
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal	

Accommodation	#18-#10 AWG copper stranded conductor
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 HB or better.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).



NEMA 5-15P
15A 125V
 UL CSA
 0.5 HP

NEMA Configuration

Hubbell Incorporated (Delaware)
 185 Plains Road
 Milford, CT 06460-2420
 Ph: (203) 882-4800
 Fax: (800) 255-1031

