


Specifications



Type : Nickel-Metal Hydride Battery		Size : 5/4AAA
Capacity ¹⁾	Typical	850mAh
	Minimum	760mAh
Nominal Voltage		1.2V
Charging Current x Time	Fast Charge ²⁾	850 mA x about 1.1h
Ambient Temp.	Charge Condition	Fast Charge ²⁾
	0°C - 40°C	
	Discharge Condition	
	0°C - 50°C	
	Storage Condition	Less than 30days
		-20°C - 50°C
		Less than 90days
		-20°C - 40°C
		Less than 1year
		-20°C - 30°C
Internal Impedance ³⁾ (after discharge to E.V.=1.0V)		Approx. 30mΩ(at 1000Hz)
Weight ⁴⁾		Approx. 15 g
Size ⁴⁾ : (Diameter) x (Height)		10.5(D) x 50.0(H) mm

1) Single cell capacity under the following condition.

Charge : 85mA×16h, Discharge : 170mA(E.V.=1.0V) at 20°C


2) Use recommended charging system.

3) After a few charge and discharge cycles under the above 1) condition.

4) With tube.

Typical Characteristics

Charge



Discharge

