

Surface Mount Power Voltage-Regulating Diodes



DO-214AC (SMA)

FEATURES

- Low profile package
- Ideal for automated placement
- Low Zener impedance
- Low regulation factor
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

MECHANICAL DATA

Case: DO-214AC (SMA)

Molding compound meets UL 94 V-0 flammability rating
Base P/N-E3 - RoHS-compliant and commercial grade

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: Color band denotes cathode end

PRIMARY CHARACTERISTICS

V_Z	5.6 V to 68 V
P_{tot} at $T_L = 75\text{ °C}$	1500 mW
P_{tot} at $T_A = 25\text{ °C}$	500 mW
T_J max.	150 °C
V_Z specification	Pulse current
Int. construction	Single

TYPICAL APPLICATIONS

For general purpose regulation and protection applications.

MAXIMUM RATINGS ($T_A = 25\text{ °C}$ unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
Maximum steady state power dissipation at $T_L = 75\text{ °C}$ (fig. 1) ⁽¹⁾	P_{tot}	1500	mW
Maximum steady state power dissipation at $T_A = 25\text{ °C}$ (fig. 1) ⁽²⁾	P_{tot}	500	mW
Maximum instantaneous forward voltage at 200 mA for all types ⁽³⁾	V_F	1.5	V
Operating junction and storage temperature range	T_J, T_{STG}	- 65 to + 150	°C

Notes


⁽¹⁾ Mounted on PCB with 5.0 mm x 5.0 mm copper pads attached to each terminal

⁽²⁾ Mounted on minimum recommended pad layout

⁽³⁾ Pulse test: 300 μ s pulse width, 1 % duty cycle

**ELECTRICAL CHARACTERISTICS**

SYMBOL	PARAMETER
V_Z	Reverse Zener voltage at I_{ZT}
I_{ZT}	Reverse current
Z_{ZT}	Maximum Zener impedance at I_{ZT}
I_{ZK}	Reverse current
Z_{ZK}	Maximum Zener impedance at I_{ZK}
I_R	Reverse leakage current at V_R
V_R	Reverse voltage
I_F	Forward current
V_F	Forward voltage at I_F
I_{ZM}	Maximum DC Zener current



Zener Voltage Regulator

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PART NUMBER	DEVICE MARKING CODE	ZENER VOLTAGE RANGE			TEST CURRENT		MAXIMUM ZENER IMPEDANCE		REVERSE LEAKAGE CURRENT		MAXIMUM ZENER CURRENT
		V_Z AT I_{ZT}			I_{ZT}	I_{ZK}	Z_{ZT} AT I_{ZT}	Z_{ZK} AT I_{ZK}	I_R AT V_R		I_{ZM}
		V			mA		Ω		μA	V	mA
		MIN.	NOM.	MAX.			MAX.	MAX.	MAX.		MAX.
SMAZ5919B	19B	5.32	5.6	5.88	66.9	1.0	5.0	700	200	3.0	268
SMAZ5920B	20B	5.89	6.2	6.51	60.5	1.0	2.0	700	200	4.0	242
SMAZ5921B	21B	6.46	6.8	7.14	55.1	1.0	2.5	400	200	5.2	221
SMAZ5923B	23B	7.79	8.2	8.61	45.7	0.5	5.0	700	10	6.5	183
SMAZ5924B	24B	8.64	9.1	9.56	41.2	0.5	5.0	700	10	7.0	165
SMAZ5925B	25B	9.5	10	10.5	37.5	0.25	5.0	700	10	8.0	150
SMAZ5926B	26B	10.5	11	11.6	34.1	0.25	5.5	550	5	8.4	136
SMAZ5927B	27B	11.4	12	12.6	31.2	0.25	6.5	550	1	9.1	125
SMAZ5928B	28B	12.4	13	13.7	28.8	0.25	7.0	550	1	9.9	115
SMAZ5929B	29B	14.3	15	15.8	25.0	0.25	9.0	600	1	11.4	100
SMAZ5930B	30B	15.2	16	16.8	23.4	0.25	10	600	1	12.2	94
SMAZ5931B	31B	17.1	18	18.9	20.8	0.25	12	650	1	13.7	83
SMAZ5932B	32B	19.0	20	21.0	18.7	0.25	14	650	1	15.2	75
SMAZ5933B	33B	20.9	22	23.1	17.0	0.25	17.5	650	1	16.7	68
SMAZ5934B	34B	22.8	24	25.2	15.6	0.25	19	700	1	18.2	62
SMAZ5935B	35B	25.7	27	28.4	13.9	0.25	23	700	1	20.6	56
SMAZ5936B	36B	28.5	30	31.5	12.5	0.25	28	750	1	22.8	50
SMAZ5937B	37B	31.4	33	34.7	11.4	0.25	33	800	1	25.1	45
SMAZ5938B	38B	34.2	36	37.8	10.4	0.25	38	850	1	27.4	42
SMAZ5939B	39B	37.1	39	41.0	9.6	0.25	45	900	1	29.7	38
SMAZ5940B	40B	40.9	43	45.2	8.7	0.25	53	950	1	32.7	35
SMAZ5941B	41B	44.65	47	49.35	8.0	0.25	67	1000	1	35.8	32
SMAZ5942B	42B	48.45	51	53.55	7.3	0.25	70	1100	1	38.8	29
SMAZ5943B	43B	53.2	56	58.8	6.7	0.25	86	1300	1	42.6	27
SMAZ5944B	44B	58.9	62	65.1	6.0	0.25	100	1500	1	47.1	24
SMAZ5945B	45B	64.6	68	71.4	5.5	0.25	120	1700	1	51.7	22

**THERMAL CHARACTERISTICS** ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Typical thermal resistance, junction to lead ⁽¹⁾	$R_{\theta JL}$	50	$^{\circ}\text{C/W}$
Typical thermal resistance, junction to ambient ⁽²⁾	$R_{\theta JA}$	250	$^{\circ}\text{C/W}$

Note

(1) Mounted on minimum recommended pad layout

ORDERING INFORMATION (Example)

PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
SMAZ5925B-M3/61	0.064	61	1800	7" diameter plastic tape and reel
SMAZ5925B-M3/5A	0.064	5A	7500	13" diameter plastic tape and reel


RATINGS AND CHARACTERISTICS CURVES ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

Fig. 1 - Steady State Power During




Fig. 3 - Typical Zener Voltage




Fig. 2 - Typical Zener Voltage




Fig. 4 - Typical Temperature Coefficients




Fig. 5 - Typical Temperature Coefficients




Fig. 7 - Typical Zener Impedance






Fig. 6 - Typical Junction Capacitance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

DO-214AC (SMA)

Mounting Pad Layout




Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.