



3.3V CMOS 16-BIT BUS TRANSCEIVER WITH 3-STATE OUTPUTS AND 5 VOLT TOLERANT I/O

IDT74LVCR162245A

FEATURES:

- Typical $t_{sk(0)}$ (Output Skew) < 250ps
- ESD > 2000V per MIL-STD-883, Method 3015; > 200V using machine model ($C = 200\text{pF}$, $R = 0$)
- 0.635mm pitch SSOP, 0.50mm pitch TSSOP and 0.40mm pitch TVSOP packages
- Extended commercial range of -40°C to $+85^{\circ}\text{C}$
- $V_{CC} = 3.3\text{V} \pm 0.3\text{V}$, Normal Range
- $V_{CC} = 2.7\text{V}$ to 3.6V , Extended Range
- CMOS power levels ($0.4\mu\text{W}$ typ. static)
- All inputs, outputs and I/O are 5 Volt tolerant
- Supports hot insertion

Drive Features for LVCR162245A:

- Balanced Output Drivers: $\pm 12\text{ mA}$
- Low switching noise

APPLICATIONS:

- 5V and 3.3V mixed voltage systems
- Data communication and telecommunication systems


DESCRIPTION:

This 16-bit bus transceiver is built using advanced dual metal CMOS technology. This high-speed, low power transceiver is ideal for asynchronous communication between two busses (A and B). The Direction and Output Enable controls are designed to operate this device as either two independent 8-bit transceivers or one 16-bit transceiver. The direction control pin (DIR) controls the direction of data flow. The output enable pin (OE) overrides the direction control and disables both ports. All inputs are designed with hysteresis for improved noise margin.

All pins can be driven from either 3.3V or 5V devices. This feature allows the use of this device as a translator in a mixed 3.3V/5V supply system.

The LVCR162245A has series resistors in the device output structure which will significantly reduce line noise when used with light loads. The driver has been designed to drive $\pm 12\text{mA}$ at the designated threshold levels.


FUNCTIONAL BLOCK DIAGRAM



EXTENDED COMMERCIAL TEMPERATURE RANGE

APRIL 1999

PIN CONFIGURATION

SSOP/ TSSOP/ TVSOP
TOP VIEW

ABSOLUTE MAXIMUM RATINGS (1)

| Symbol | Description | Max. | Unit |
|------------------|--|---------------|------|
| VTERM(2) | Terminal Voltage with Respect to GND | - 0.5 to +6.5 | V |
| VTERM(3) | Terminal Voltage with Respect to GND | - 0.5 to +6.5 | V |
| TSTG | Storage Temperature | - 65 to +150 | °C |
| I _{OUT} | DC Output Current | - 50 to +50 | mA |
| I _{IK} | Continuous Clamp Current, V _I < 0 or V _O < 0 | - 50 | mA |
| I _{CC} | Continuous Current through each V _{CC} or GND | ± 100 | mA |
| I _{SS} | | | |

LVC Link

NOTES:

1. Stresses greater than those listed under ABSOLUTE MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.
2. V_{CC} terminals.
3. All terminals except V_{CC}.

CAPACITANCE (T_A = +25°C, f = 1.0MHz)

| Symbol | Parameter ⁽¹⁾ | Conditions | Typ. | Max. | Unit |
|------------------|--------------------------|-----------------------|------|------|------|
| C _{IN} | Input Capacitance | V _{IN} = 0V | 4.5 | 6 | pF |
| C _{OUT} | Output Capacitance | V _{OUT} = 0V | 6.5 | 8 | pF |
| C _{I/O} | I/O Port Capacitance | V _{IN} = 0V | 6.5 | 8 | pF |

LVC Link

NOTE:

1. As applicable to the device type.

PIN DESCRIPTION

| Pin Names | Description |
|------------------|----------------------------------|
| x _{OE} | Output Enable Input (Active LOW) |
| x _{DIR} | Direction Control Input |
| x _{Ax} | Side A Inputs or 3-State Outputs |
| x _{Bx} | Side B Inputs or 3-State Outputs |

FUNCTION TABLE (each 8-bit section)⁽¹⁾

| Inputs | | Outputs |
|-----------------|------------------|---------------------|
| x _{OE} | x _{DIR} | |
| L | L | Bus B Data to Bus A |
| L | H | Bus A Data to Bus B |
| H | X | Isolation |

NOTE:

1. H = HIGH Voltage Level
L = LOW Voltage Level
X = Don't Care

DC ELECTRICAL CHARACTERISTICS OVER OPERATING RANGE

Following Conditions Apply Unless Otherwise Specified:

Operating Condition: $T_A = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$

| Symbol | Parameter | Test Conditions | | Min. | Typ. ⁽¹⁾ | Max. | Unit |
|--|--|---|--|------|---------------------|----------|---------------|
| V _{IH} | Input HIGH Voltage Level | V _{CC} = 2.3V to 2.7V | | 1.7 | — | — | V |
| | | V _{CC} = 2.7V to 3.6V | | 2 | — | — | |
| V _{IL} | Input LOW Voltage Level | V _{CC} = 2.3V to 2.7V | | — | — | 0.7 | V |
| | | V _{CC} = 2.7V to 3.6V | | — | — | 0.8 | |
| I _{IH} I _{IL} | Input Leakage Current | V _{CC} = 3.6V | V _I = 0 to 5.5V | — | — | ± 5 | μA |
| I _{OZH} I _{OZL} | High Impedance Output Current (3-State Output pins) | V _{CC} = 3.6V | V _O = 0 to 5.5V | — | — | ± 10 | μA |
| I _{OFF} | Input/Output Power Off Leakage | V _{CC} = 0V, V _{IN} or V _O \leq 5.5V | | — | — | ± 50 | μA |
| V _{IK} | Clamp Diode Voltage | V _{CC} = 2.3V, I _{IN} = -18mA | | — | -0.7 | -1.2 | V |
| V _H | Input Hysteresis | V _{CC} = 3.3V | | — | 100 | — | mV |
| I _{ICL} I _{ICCH} I _{ICCZ} | Quiescent Power Supply Current | V _{CC} = 3.6V | V _{IN} = GND or V _{CC} | — | — | 10 | μA |
| | | 3.6 \leq V _{IN} \leq 5.5V ⁽²⁾ | | — | — | 10 | |
| ΔI_{CC} | Quiescent Power Supply Current Variation | One input at V _{CC} - 0.6V other inputs at V _{CC} or GND | | — | — | 500 | μA |

NOTES:

1. Typical values are at V_{CC} = 3.3V, $+25^{\circ}\text{C}$ ambient.
2. This applies in the disabled state only.

OUTPUT DRIVE CHARACTERISTICS

| Symbol | Parameter | Test Conditions ⁽¹⁾ | | Min. | Max. | Unit |
|-----------------|---------------------|--------------------------------|-----------------------------------|-----------------------|------|------|
| V _{OH} | Output HIGH Voltage | V _{CC} = 2.3V to 3.6V | I _{OH} = -0.1mA | V _{CC} - 0.2 | — | V |
| | | V _{CC} = 2.3V | I _{OH} = -4mA | 1.9 | — | |
| | | | I _{OH} = -6mA | 1.7 | — | |
| | | V _{CC} = 2.7V | I _{OH} = -4mA | 2.2 | — | |
| | | | I _{OH} = -8mA | 2 | — | |
| | | V _{CC} = 3.0V | I _{OH} = -6mA | 2.4 | — | |
| | | | I _{OH} = -12mA | 2 | — | |
| V _{OL} | Output LOW Voltage | V _{CC} = 2.3V to 3.6V | I _{OL} = 0.1mA | — | 0.2 | V |
| | | V _{CC} = 2.3V | I _{OL} = 4mA | — | 0.4 | |
| | | | I _{OL} = 6mA | — | 0.55 | |
| | | V _{CC} = 2.7V | I _{OL} = 4mA | — | 0.4 | |
| | | | I _{OL} = 8mA | — | 0.6 | |
| | | V _{CC} = 3.0V | I _{OL} = 6mA | — | 0.55 | |
| | | | I _{OL} = 12mA | — | 0.8 | |

NOTE:

1. V_{IH} and V_{IL} must be within the min. or max. range shown in the DC ELECTRICAL CHARACTERISTICS OVER OPERATING RANGE table for the appropriate V_{CC} range. $T_A = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$.

OPERATING CHARACTERISTICS, $V_{CC} = 3.3V \pm 0.3V$, $T_A = 25^\circ C$

| Symbol | Parameter | Test Conditions | Typical | Unit |
|--------|--|------------------------|---------|------|
| CPD | Power Dissipation Capacitance per Transceiver Outputs enabled | $C_L = 0pF, f = 10Mhz$ | 39 | pF |
| CPD | Power Dissipation Capacitance per Transceiver Outputs disabled | | 4 | pF |

SWITCHING CHARACTERISTICS (1)

| Symbol | Parameter | $V_{CC} = 2.7V$ | | $V_{CC} = 3.3V \pm 0.3V$ | | Unit |
|-------------|--|-----------------|------|--------------------------|------|------|
| | | Min. | Max. | Min. | Max. | |
| t_{PLH} | Propagation Delay xAx to xBx , xBx to xAx | — | 5.7 | 1.5 | 4.8 | ns |
| t_{PHL} | Output Enable Time $x\bar{OE}$ to xAx or xBx | — | 7.9 | 1.5 | 6.3 | ns |
| t_{PHZ} | Output Disable Time $x\bar{OE}$ to xAx or xBx | — | 8.3 | 2.2 | 7.4 | ns |
| t_{PLZ} | | — | — | — | — | ps |
| $t_{SK(0)}$ | Output Skew ⁽²⁾ | — | — | — | 500 | ps |


NOTES:

1. See test circuits and waveforms. $T_A = -40^\circ C$ to $+85^\circ C$.
2. Skew between any two outputs of the same package and switching in the same direction.

TEST CIRCUITS AND WAVEFORMS:**TEST CONDITIONS**

| Symbol | $V_{CC(1)} = 3.3V \pm 0.3V$ | $V_{CC(1)} = 2.7V$ | $V_{CC(2)} = 2.5V \pm 0.2V$ | Unit |
|------------|-----------------------------|--------------------|-----------------------------|------|
| V_{LOAD} | 6 | 6 | $2 \times V_{CC}$ | V |
| V_{IH} | 2.7 | 2.7 | V_{CC} | V |
| V_T | 1.5 | 1.5 | $V_{CC}/2$ | V |
| V_{LZ} | 300 | 300 | 150 | mV |
| V_{HZ} | 300 | 300 | 150 | mV |
| CL | 50 | 50 | 30 | pF |

LVC Link

TEST CIRCUITS FOR ALL OUTPUTS**DEFINITIONS:**

CL = Load capacitance: includes jig and probe capacitance.

RT = Termination resistance: should be equal to Zout of the Pulse Generator.


NOTES:

1. Pulse Generator for All Pulses: Rate $\leq 10MHz$; $t_F \leq 2.5ns$; $t_R \leq 2.5ns$.
2. Pulse Generator for All Pulses: Rate $\leq 10MHz$; $t_F \leq 2ns$; $t_R \leq 2ns$.

SWITCH POSITION

| Test | Switch |
|-----------------|------------|
| Open Drain | V_{LOAD} |
| Disable Low | |
| Enable Low | |
| Disable High | GND |
| Enable High | |
| All Other tests | Open |

LVC Link



OUTPUT SKEW - $t_{SK}(x)$ 

$$tsk(x) = |tPLH2 - tPLH1| \text{ or } |tPHL2 - tPHL1|$$



LVC Link

NOTES:

1. For $tsk(o)$ OUTPUT1 and OUTPUT2 are any two outputs.
2. For $tsk(b)$ OUTPUT1 and OUTPUT2 are in the same bank.


PROPAGATION DELAY**ENABLE AND DISABLE TIMES****NOTE:**

1. Diagram shown for input Control Enable-LOW and input Control Disable-HIGH.

SET-UP, HOLD, AND RELEASE TIMES**PULSE WIDTH**

ORDERING INFORMATION

IDT XX LVC X XX XXXX XX
 Temp. Range Bus-Hold Family Device Type Package



CORPORATE HEADQUARTERS

2975 Stender Way
 Santa Clara, CA 95054

for SALES:

800-345-7015 or 408-727-6116
 fax: 408-492-8674
www.idt.com*

*To search for sales office near you, please click the sales button found on our home page or dial the 800# above and press 2.
 The IDT logo is a registered trademark of Integrated Device Technology, Inc.