



# STD7NS20 STD7NS20-1

N-CHANNEL 200V - 0.35Ω - 7A DPAK / IPAK  
MESH OVERLAY™ MOSFET

PRELIMINARY DATA

| TYPE       | V <sub>DSS</sub> | R <sub>DS(on)</sub> | I <sub>D</sub> |
|------------|------------------|---------------------|----------------|
| STD7NS20   | 200 V            | < 0.40 Ω            | 7 A            |
| STD7NS20-1 | 200 V            | < 0.40 Ω            | 7 A            |



- TYPICAL R<sub>DS(on)</sub> = 0.35 Ω
- EXTREMELY HIGH dv/dt CAPABILITY
- 100% AVALANCHE TESTED
- VERY LOW INTRINSIC CAPACITANCES
- ADD SUFFIX "T4" FOR ORDERING IN TAPE & REEL

## DESCRIPTION

Using the latest high voltage MESH OVERLAY™ process, STMicroelectronics has designed an advanced family of power MOSFETs with outstanding performance. The new patented STrip layout coupled with the Company's proprietary edge termination structure, makes it suitable in converters for lighting applications.

## APPLICATIONS

- HIGH CURRENT, HIGH SPEED SWITCHING
- SWITCH MODE POWER SUPPLIES (SMPS)
- DC-DC CONVERTERS FOR TELECOM, INDUSTRIAL, AND LIGHTING EQUIPMENT



## ABSOLUTE MAXIMUM RATINGS

| Symbol              | Parameter                                            | Value      | Unit |
|---------------------|------------------------------------------------------|------------|------|
| V <sub>DS</sub>     | Drain-source Voltage (V <sub>GS</sub> = 0)           | 200        | V    |
| V <sub>DGR</sub>    | Drain-gate Voltage (R <sub>GS</sub> = 20 kΩ)         | 200        | V    |
| V <sub>GS</sub>     | Gate- source Voltage                                 | ± 20       | V    |
| I <sub>D</sub>      | Drain Current (continuous) at T <sub>C</sub> = 25°C  | 7          | A    |
| I <sub>D</sub>      | Drain Current (continuous) at T <sub>C</sub> = 100°C | 4.4        | A    |
| I <sub>DM</sub> (•) | Drain Current (pulsed)                               | 28         | A    |
| P <sub>TOT</sub>    | Total Dissipation at T <sub>C</sub> = 25°C           | 45         | W    |
|                     | Derating Factor                                      | 0.37       | W/°C |
| dv/dt (1)           | Peak Diode Recovery voltage slope                    | 5          | V/ns |
| T <sub>stg</sub>    | Storage Temperature                                  | -65 to 150 | °C   |
| T <sub>j</sub>      | Max. Operating Junction Temperature                  | 150        | °C   |

(•) Pulse width limited by safe operating area

(1) I<sub>SD</sub> ≤ 7A, di/dt ≤ 300 A/μs, V<sub>DD</sub> ≤ V<sub>(BR)DSS</sub>, T<sub>j</sub> ≤ T<sub>jMAX</sub>

## STD7NS20 / STD7NS20-1

### THERMAL DATA

|                |                                                |     |      |
|----------------|------------------------------------------------|-----|------|
| Rthj-case      | Thermal Resistance Junction-case Max           | 2.7 | °C/W |
| Rthj-amb       | Thermal Resistance Junction-ambient Max        | 100 | °C/W |
| T <sub>I</sub> | Maximum Lead Temperature For Soldering Purpose | 275 | °C   |

### AVALANCHE CHARACTERISTICS

| Symbol          | Parameter                                                                                                                  | Max Value | Unit |
|-----------------|----------------------------------------------------------------------------------------------------------------------------|-----------|------|
| I <sub>AR</sub> | Avalanche Current, Repetitive or Not-Repetitive (pulse width limited by T <sub>j</sub> max)                                | 7         | A    |
| E <sub>AS</sub> | Single Pulse Avalanche Energy (starting T <sub>j</sub> = 25 °C, I <sub>D</sub> = I <sub>AR</sub> , V <sub>DD</sub> = 50 V) | 60        | mJ   |

### ELECTRICAL CHARACTERISTICS (TCASE = 25 °C UNLESS OTHERWISE SPECIFIED)

#### OFF

| Symbol               | Parameter                                             | Test Conditions                                                                       | Min. | Typ. | Max.    | Unit     |
|----------------------|-------------------------------------------------------|---------------------------------------------------------------------------------------|------|------|---------|----------|
| V <sub>(BR)DSS</sub> | Drain-source Breakdown Voltage                        | I <sub>D</sub> = 250 µA, V <sub>GS</sub> = 0                                          | 200  |      |         | V        |
| I <sub>DSS</sub>     | Zero Gate Voltage Drain Current (V <sub>GS</sub> = 0) | V <sub>DS</sub> = Max Rating<br>V <sub>DS</sub> = Max Rating, T <sub>C</sub> = 125 °C |      |      | 1<br>10 | µA<br>µA |
| I <sub>GSS</sub>     | Gate-body Leakage Current (V <sub>DS</sub> = 0)       | V <sub>GS</sub> = ±20V                                                                |      |      | ±100    | nA       |

#### ON (1)

| Symbol              | Parameter                         | Test Conditions                                            | Min. | Typ. | Max. | Unit |
|---------------------|-----------------------------------|------------------------------------------------------------|------|------|------|------|
| V <sub>GS(th)</sub> | Gate Threshold Voltage            | V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250µA | 2    | 3    | 4    | V    |
| R <sub>DS(on)</sub> | Static Drain-source On Resistance | V <sub>GS</sub> = 10V, I <sub>D</sub> = 3.5 A              |      | 0.35 | 0.40 | Ω    |

### DYNAMIC

| Symbol              | Parameter                    | Test Conditions                                                                           | Min. | Typ. | Max. | Unit |
|---------------------|------------------------------|-------------------------------------------------------------------------------------------|------|------|------|------|
| g <sub>fs</sub> (1) | Forward Transconductance     | V <sub>DS</sub> > I <sub>D(on)</sub> × R <sub>DS(on)</sub> max,<br>I <sub>D</sub> = 3.5 A |      | 4    |      | S    |
| C <sub>iss</sub>    | Input Capacitance            | V <sub>DS</sub> = 25V, f = 1 MHz, V <sub>GS</sub> = 0                                     |      | 540  |      | pF   |
| C <sub>oss</sub>    | Output Capacitance           |                                                                                           |      | 90   |      | pF   |
| C <sub>rss</sub>    | Reverse Transfer Capacitance |                                                                                           |      | 35   |      | pF   |

## ELECTRICAL CHARACTERISTICS (CONTINUED)

## SWITCHING ON

| Symbol      | Parameter          | Test Conditions                                                                                                              | Min. | Typ. | Max. | Unit |
|-------------|--------------------|------------------------------------------------------------------------------------------------------------------------------|------|------|------|------|
| $t_{d(on)}$ | Turn-on Delay Time | $V_{DD} = 100\text{ V}$ , $I_D = 3.5\text{ A}$<br>$R_G = 4.7\Omega$ , $V_{GS} = 10\text{ V}$<br>(see test circuit, Figure 3) |      | 10   |      | ns   |
| $t_r$       | Rise Time          |                                                                                                                              |      | 15   |      | ns   |
| $Q_g$       | Total Gate Charge  | $V_{DD} = 160\text{ V}$ , $I_D = 18\text{ A}$ ,<br>$V_{GS} = 10\text{ V}$                                                    |      | 31   | 45   | nC   |
| $Q_{gs}$    | Gate-Source Charge |                                                                                                                              |      | 7.5  |      | nC   |
| $Q_{gd}$    | Gate-Drain Charge  |                                                                                                                              |      | 9    |      | nC   |

## SWITCHING OFF


| Symbol        | Parameter             | Test Conditions                                                                                                                 | Min. | Typ. | Max. | Unit |
|---------------|-----------------------|---------------------------------------------------------------------------------------------------------------------------------|------|------|------|------|
| $t_{r(voff)}$ | Off-voltage Rise Time | $V_{clamp} = 160\text{ V}$ , $I_D = 7\text{ A}$ ,<br>$R_G = 4.7\Omega$ , $V_{GS} = 10\text{ V}$<br>(see test circuit, Figure 5) |      | 12   |      | ns   |
| $t_f$         | Fall Time             |                                                                                                                                 |      | 12   |      | ns   |
| $t_c$         | Cross-over Time       |                                                                                                                                 |      | 25   |      | ns   |

## SOURCE DRAIN DIODE


| Symbol       | Parameter                     | Test Conditions                                                                                                                                  | Min. | Typ. | Max. | Unit          |
|--------------|-------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|------|------|------|---------------|
| $I_{SD}$     | Source-drain Current          |                                                                                                                                                  |      |      | 7    | A             |
| $I_{SDM(2)}$ | Source-drain Current (pulsed) |                                                                                                                                                  |      |      | 28   | A             |
| $V_{SD(1)}$  | Forward On Voltage            | $I_{SD} = 7\text{ A}$ , $V_{GS} = 0$                                                                                                             |      |      | 1.5  | V             |
| $t_{rr}$     | Reverse Recovery Time         | $I_{SD} = 7\text{ A}$ , $di/dt = 100\text{ A}/\mu\text{s}$<br>$V_{DD} = 50\text{ V}$ , $T_J = 150^\circ\text{C}$<br>(see test circuit, Figure 5) |      | 170  |      | ns            |
| $Q_{rr}$     | Reverse Recovery Charge       |                                                                                                                                                  |      | 0.95 |      | $\mu\text{C}$ |
| $I_{RRM}$    | Reverse Recovery Current      |                                                                                                                                                  |      | 11   |      | A             |

Note: 1. Pulsed: Pulse duration = 300  $\mu\text{s}$ , duty cycle 1.5 %.  
2. Pulse width limited by safe operating area.


**Fig. 1: Unclamped Inductive Load Test Circuit**




**Fig. 2: Unclamped Inductive Waveform**




**Fig. 3: Switching Times Test Circuit For Resistive Load**



**Fig. 4: Gate Charge test Circuit**




**Fig. 5: Test Circuit For Inductive Load Switching And Diode Recovery Times**




## TO-252 (DPAK) MECHANICAL DATA

| DIM. | mm   |      |       | inch  |       |       |
|------|------|------|-------|-------|-------|-------|
|      | MIN. | TYP. | MAX.  | MIN.  | TYP.  | MAX.  |
| A    | 2.20 |      | 2.40  | 0.087 |       | 0.094 |
| A1   | 0.90 |      | 1.10  | 0.035 |       | 0.043 |
| A2   | 0.03 |      | 0.23  | 0.001 |       | 0.009 |
| B    | 0.64 |      | 0.90  | 0.025 |       | 0.035 |
| B2   | 5.20 |      | 5.40  | 0.204 |       | 0.213 |
| C    | 0.45 |      | 0.60  | 0.018 |       | 0.024 |
| C2   | 0.48 |      | 0.60  | 0.019 |       | 0.024 |
| D    | 6.00 |      | 6.20  | 0.236 |       | 0.244 |
| E    | 6.40 |      | 6.60  | 0.252 |       | 0.260 |
| G    | 4.40 |      | 4.60  | 0.173 |       | 0.181 |
| H    | 9.35 |      | 10.10 | 0.368 |       | 0.398 |
| L2   |      | 0.8  |       |       | 0.031 |       |
| L4   | 0.60 |      | 1.00  | 0.024 |       | 0.039 |
| V2   | 0°   |      | 8°    | 0°    |       | 0°    |




TO-251 (IPAK) MECHANICAL DATA

| DIM. | mm   |      |      | inch  |       |       |
|------|------|------|------|-------|-------|-------|
|      | MIN. | TYP. | MAX. | MIN.  | TYP.  | MAX.  |
| A    | 2.2  |      | 2.4  | 0.086 |       | 0.094 |
| A1   | 0.9  |      | 1.1  | 0.035 |       | 0.043 |
| A3   | 0.7  |      | 1.3  | 0.027 |       | 0.051 |
| B    | 0.64 |      | 0.9  | 0.025 |       | 0.031 |
| B2   | 5.2  |      | 5.4  | 0.204 |       | 0.212 |
| B3   |      |      | 0.85 |       |       | 0.033 |
| B5   |      | 0.3  |      |       | 0.012 |       |
| B6   |      |      | 0.95 |       |       | 0.037 |
| C    | 0.45 |      | 0.6  | 0.017 |       | 0.023 |
| C2   | 0.48 |      | 0.6  | 0.019 |       | 0.023 |
| D    | 6    |      | 6.2  | 0.236 |       | 0.244 |
| E    | 6.4  |      | 6.6  | 0.252 |       | 0.260 |
| G    | 4.4  |      | 4.6  | 0.173 |       | 0.181 |
| H    | 15.9 |      | 16.3 | 0.626 |       | 0.641 |
| L    | 9    |      | 9.4  | 0.354 |       | 0.370 |
| L1   | 0.8  |      | 1.2  | 0.031 |       | 0.047 |
| L2   |      | 0.8  | 1    |       | 0.031 | 0.039 |




0068771-E


## DPAK FOOTPRINT



## TUBE SHIPMENT (no suffix)\*



## TAPE AND REEL SHIPMENT (suffix "T4")\*



\* on sales type



Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

© The ST logo is a registered trademark of STMicroelectronics

© 2003 STMicroelectronics - Printed in Italy - All Rights Reserved  
STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - Canada - China - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco  
Singapore - Spain - Sweden - Switzerland - United Kingdom - United States.

© <http://www.st.com>