






LOC	DIST	REVISIONS				
		REV	DATE	BY	CHK	APP'D
CM	54	H2	23SEP14	MGM	CO	



RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THICK P.C. BOARD



- 1. POST TO WITHSTAND 13 NEWTONS (3 LBS) MIN. AXIAL FORCE IN BOTH DIRECTIONS SHOWN WITHOUT DISLODGING.
- 2. TOLERANCES APPLY TO SOLDER SIDE OF BOARD.
- 3. MEASURED AT SURFACE -A-
- 4. PLASTIC FLASH PERMITTED IN THIS AREA.
- 5. PARTS COMPLY WITH AMP SOLDERABILITY SPEC. NO. 109-11-2.
- 6. ONE HOLE MAY BE UNDERSIZED(.032-.035 DIA) FOR ASSEMBLY RETENTION DURING WAVE SOLDERING.
- 7. MATERIAL: HEADER-THERMOPLASTIC POLYESTER
UL94V-0(NATURAL)
POST-COPPER ALLOY (TIN-PLATED)
- 8. COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
- 9. PLASTIC BURRS CAUSED BY CUT-OFF TOOLING ARE PERMITTED WITHIN THE MAXIMUM TOLERANCE ENVELOPE.
- 10. POSTS TO BE MEASURED WHEN STRIP IS HELD FLAT.
- 11. POSTS MUSTS WITHSTAND TWO 90° BENDS AGAINST EXTRUSION WITHOUT BREAKING.
- 12. DIMENSION SHOULD BE .130 MIN WHEN MATING WITH A MTA 100 CONNECTOR ASSEMBLY OR A CST 100 CONNECTOR.
- 13. PIN BURR OF .005 MAX. VERTICAL AND .003 MAX. HORIZONTAL PERMITTED AT POST TIPS ON BOTH ENDS.

644225-1 SHOWN

OBSOLETE	8	644225-6
	3	644225-5
OBSOLETE	6	644225-3
	2	644225-2
OBSOLETE	7	644225-1

POST NUMBER OMITTED
PART NUMBER

		1.200	30.48
.035	0.89	.535	13.59
.032	0.81	.310	7.87
.025	0.64	.295	7.49
.020	0.51	.225	5.72
.015	0.38	.200	5.08
.012	0.30	.140	3.56
.010	0.25	.130	3.30
.008	0.20	.125	3.18
.005	0.13	.100	2.54
.003	0.08	.063	1.60
.001	0.03	.050	1.27
.000	0.00	.040	1.02
IN	MM	IN	MM

CONVERSION TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. SMITH 4-5-93	TE Connectivity	
DIMENSIONS: INCHES		CHK R. SWING 4-5-93	NAME MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .025 SQUARE STRAIGHT POST, TIN PLATED,	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROV R. SPEER PRODUCT SPEC	SIZE A1	
0.003 ± .003		APPLICATION SPEC	CAGE CODE 00779	
0.001 ± .001		WEIGHT	DRAWING NO 644225	
0.000 ± .000		RESTRICTED TO	CUSTOMER DRAWING	
MATERIAL 7		FINISH 7	SCALE 8:1	
		SHEET 1 of 1		REV H2