

- [Contact Us](#)
- |
- [TI Worldwide: United States](#)
- |
- [my.TI Login](#)
- **▶ Products**
 - Amplifiers & Linear
 - Clocks & Timers
 - Data Converters
 - Interface
 - Logic
 - Power Management
 - Processors
 - Digital
 - Signal Processing (DSP)
 -
 - Microcontrollers (MCU)
 - RFID
 - Systems
 - RF/IF & ZigBee® Solutions
 - Switches & Multiplexers
 - Standard Linear
 - Temperature Sensors & Monitoring
 - > [See All](#)
- **▶ Applications**
 - Audio
 - Automotive
 - Broadband
 - Communications & Telecom
 - Computers & Peripherals
 - Consumer Electronics
 - Industrial
 - Medical
 - Space, Avionics, & Defense
 - Security
 - Video & Imaging
 - Wireless
 - > [See All](#)
- **▶ Design Support**
 - Technical Documents
 - Contact Technical Support
 - TI E2E Support Community
 - Quality & Lead-free Data
 - KnowledgeBase
 - Training
 - Technology Days
 - Developer & Design House Network
 - Analog eLab™
 - Design Center
 - > [See All](#)
- **▶ Sample & Buy**
 - Pricing & Availability
 - Samples
 - TI eStore
 - Semiconductor Distributors
 - Sales Representatives
 - > [See All](#)

[All Searches](#) [TI Home](#) > [Semiconductors](#) > [Logic](#) > [Buffers, Drivers and Transceivers](#) > [Registered Transceivers](#) >

SN74ALS646

Status: OBSOLETE

Octal Registered Bus Transceivers with 3-State Outputs



View RoHS Compliant Devices

 Alert me about changes to this product



This Product is no longer available

Replaced By:

- [SN74ALS646A](#) The device has the SAME FUNCTIONALITY and PINOUT as the compared device but is NOT an exact equivalent.Minimum tpd limit changes only, December 1994

Most Popular Links

 [Samples](#)

 [Pricing/Packaging](#)

 [Technical Documents](#)

 [Features](#)

 [Related Products](#)

 [Tools & Software](#)

 [Inventory](#)

 [Symbols/Footprints](#)

 [Quality & Pb-Free Data](#)

 [Application Notes](#)

 [Reference Designs](#)

 [Support & Community](#)

	SN54ALS646
Voltage Nodes(V)	5
Technology Family	ALS
Rating	Military
	Samples
	Inventory

Other qualified versions of SN74ALS646		
Version	Part Number	Definition
Military	SN54ALS646	QML certified for Military and Defense Applications

Pricing / Packaging / CAD Design Tools / Samples

			Packaging		CAD Design Tools	Samples
Device	Status	Temp (°C)	Package Pins	Top Side Marking	Footprints	Samples
SN74ALS646-1DW	OBSOLETE	0 to 70	SOIC (DW) 24	View	View	Not Available
SN74ALS646-1DWR	OBSOLETE	0 to 70	SOIC (DW) 24	View	View	Not Available
SN74ALS646-1NT	OBSOLETE	0 to 70	PDIP (NT) 24		View	Not Available
SN74ALS646DW	OBSOLETE	0 to 70	SOIC (DW) 24	View	View	Not Available
SN74ALS646DWR	OBSOLETE	0 to 70	SOIC (DW) 24	View	View	Not Available
SN74ALS646FN	OBSOLETE	0 to 70	PLCC (FN) 28	View	View	Not Available
SN74ALS646NT	OBSOLETE	0 to 70	PDIP (NT) 24		View	Not Available

Inventory

	TI Inventory Status				Reported Distributor Inventory			
SN74ALS646DW	As of 8:50 AM GMT, 31 Mar 2009				As of 8:50 AM GMT, 31 Mar 2009			
	In Stock	In Progress QTY Date		Lead Time	Region	Company	In Stock	Purchase
	0*			Call**	Americas	Rochester Electronics	20	Buy Now
SN74ALS646FN	As of 8:50 AM GMT, 31 Mar 2009				As of 8:50 AM GMT, 31 Mar 2009			
	In Stock	In Progress QTY Date		Lead Time	Region	Company	In Stock	Purchase
	0*			Call**	Americas	Rochester Electronics	867	Buy Now
SN74ALS646NT	As of 8:50 AM GMT, 31 Mar 2009				As of 8:50 AM GMT, 31 Mar 2009			
	In Stock	In Progress QTY Date		Lead Time	Region	Company	In Stock	Purchase
	0*			Call**	Americas	Rochester Electronics	680	Buy Now

[View all Distributors](#)

Choose a Region

[Go](#)

* Our information is updated daily, so please check back with us soon if this does not meet your needs. You may also contact your [TI Authorized Distributor](#) , including those listed above, for real time stock information.

** Lead time information is not available at this time. However, our information is updated daily so please check back with us soon. Please contact your preferred [TI Authorized Distributor](#) for additional information.

Quality & Lead (Pb)-Free Data

If the information you are requesting is not available online at this time, contact one of our [Product Information Centers](#) regarding the availability of this information.

Technical Documents

Application Notes

- [Shelf-Life Evaluation of Lead-Free Component Finishes](#) (szza046.htm, 8 KB)
24 May 2004 [Abstract](#)
- [Understanding and Interpreting Standard-Logic Data Sheets \(Rev. B\)](#) (szza036b.htm, 8 KB)
28 May 2003 [Abstract](#)
- [TI IBIS File Creation, Validation, and Distribution Processes](#) (szza034.htm, 9 KB)
29 Aug 2002 [Abstract](#)
- [Bus-Interface Devices With Output-Damping Resistors Or Reduced-Drive Outputs \(Rev. A\)](#) (scba012a.htm, 8 KB)
01 Aug 1997 [Abstract](#)
- [Designing With Logic \(Rev. C\)](#) (sdya009c.htm, 8 KB)
01 Jun 1997 [Abstract](#)
- [Live Insertion](#) (sdya012.htm, 8 KB)
01 Oct 1996 [Abstract](#)
- [Input and Output Characteristics of Digital Integrated Circuits](#) (sdya010.htm, 9 KB)
01 Oct 1996 [Abstract](#)
- [Advanced Schottky \(ALS and AS\) Logic Families](#) (sdaa010.htm, 8 KB)
01 Aug 1995 [Abstract](#)

[View Application Notes for Registered Transceivers](#) ⓘ

User Guides

-  [LOGIC Pocket Data Book \(Rev. B\)](#) (scyd013b.pdf, 6001 KB)
16 Jan 2007 [Download](#)

More Literature

-  [Logic Selection Guide 2007 \(Rev. Z\)](#) (sdyu001z.pdf, 2862 KB)
24 Apr 2007 [Download](#)
-  [Logic Cross-Reference \(Rev. A\)](#) (scyb017a.pdf, 2938 KB)
07 Oct 2003 [Download](#)

Support and Community

Customer Tags ⓘ

No Tags are Available for this Part Number

[Create a Tag](#)

Other Support

- [KnowledgeBase](#)
- [Contact Technical Support](#)
- [Product Training](#)
- [Competitor Cross Reference](#)
- [Part Marketing Lookup](#)

Products | **Applications** | **Design Support** | **Sample & Buy** 

[TI Worldwide](#) | [About TI](#) | [Contact Us](#) | [Investor Relations](#) | [Press Center](#) | [Corporate Social Responsibility](#) | [Careers](#) | [Tags](#) | [my.TI Login](#) | [All Searches](#) | [Site Map](#)

© Copyright 1995-2008 Texas Instruments Incorporated. All rights reserved. [Trademarks](#) | [Privacy Policy](#) | [Terms of Use](#)