


SWITCHING APPLICATION.
INTERFACE CIRCUIT AND DRIVER CIRCUIT APPLICATION.



FEATURES

- With Built-in Bias Resistors.
- Simplify Circuit Design.
- Reduce a Quantity of Parts and Manufacturing Process.
- High Packing Density.

EQUIVALENT CIRCUIT



EQUIVALENT CIRCUIT (TOP VIEW)



MAXIMUM RATING (Ta=25℃)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Collector-Base Voltage	V_{CBO}	50	V
Collector-Emitter Voltage	V_{CEO}	50	V
Emitter-Base Voltage	V_{EBO}	5	V
Collector Current	I_C	100	mA

CHARACTERISTIC	SYMBOL	RATING	UNIT
Collector Power Dissipation	P_C *	200	mW
Junction Temperature	T_j	150	℃
Storage Temperature Range	T_{stg}	-55 ~ 150	℃

* Total Rating.


ELECTRICAL CHARACTERISTICS (Ta=25℃)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Collector Cut-off Current	I_{CBO}	$V_{CB}=50V, I_E=0$	-	-	100	nA
Emitter Cut-off Current	I_{EBO}	$V_{EB}=5V, I_C=0$	-	-	100	nA
DC Current Gain	h_{FE}	$V_{CE}=5V, I_C=1mA$	120	-	-	
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C=10mA, I_B=0.5mA$	-	0.1	0.3	V
Transition Frequency	f_T *	$V_{CE}=10V, I_C=5mA$	-	250	-	MHz
Input Resistor	KRC860E	R_1	-	4.7	-	kΩ
	KRC861E		-	10	-	
	KRC862E		-	100	-	
	KRC863E		-	22	-	
	KRC864E		-	47	-	

MARK SPEC

TYPE	KRC860E	KRC861E	KRC862E	KRC863E	KRC864E
MARK	NK	NM	NN	NO	NP

Marking Type Name









KRC860E~KRC864E

ELECTRICAL CHARACTERISTICS (Ta=25 °C)

CHARACTERISTIC			SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Switching Time	Rise Time	KRC860E	t_r	$V_O=5V$ $V_{IN}=5V$ $R_L=1k\ \Omega$	-	0.025	-	μS
		KRC861E			-	0.03	-	
		KRC862E			-	0.3	-	
		KRC863E			-	0.06	-	
		KRC864E			-	0.11	-	
	Storage Time	KRC860E	t_{stg}		-	3.0	-	
		KRC861E			-	2.0	-	
		KRC862E			-	6.0	-	
		KRC863E			-	4.0	-	
		KRC864E			-	5.0	-	
	Fall Time	KRC860E	t_f		-	0.2	-	
		KRC861E			-	0.12	-	
		KRC862E			-	2.0	-	
		KRC863E			-	0.9	-	
		KRC864E			-	1.4	-	

KRC860E~KRC864E



KRC860E~KRC864E

