


Automotive P-Channel 60 V (D-S) 175 °C MOSFET

PRODUCT SUMMARY	
V _{DS} (V)	- 60
R _{DS(on)} (Ω) at V _{GS} = - 10 V	0.065
R _{DS(on)} (Ω) at V _{GS} = - 4.5 V	0.110
I _D (A)	- 5.7
Configuration	Single



Part Marking Code: Q002

FEATURES

- TrenchFET® Power MOSFET
- PowerPAK® Package
 - Low Thermal Resistance, R_{thJC}
 - Low 1.07 mm Profile
- Fast Switching
- AEC-Q101 Qualified
- 100 % R_g Tested
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912

AUTOMOTIVE GRADE


RoHS
COMPLIANT

ORDERING INFORMATION

Package	PowerPAK 1212-8
Lead (Pb)-free	SQ7415EN-T1-E3

ABSOLUTE MAXIMUM RATINGS (T_A = 25 °C, unless otherwise noted)

PARAMETER		SYMBOL	10 s	STEADY STATE	UNIT
Drain-Source Voltage		V _{DS}	- 60	- 60	V
Gate-Source Voltage		V _{GS}	± 20	± 20	
Continuous Drain Current ^a	T _A = 25 °C	I _D	- 5.7	- 3.6	A
	T _A = 70 °C		- 4.6	- 2.9	
Continuous Source Current (Diode Conduction) ^a		I _S	- 3.2	- 1.3	
Pulsed Drain Current ^b		I _{DM}	- 30	- 30	
Maximum Power Dissipation ^b	T _A = 25 °C	P _D	3.8	1.5	W
	T _A = 70 °C		2	0.8	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to + 175	- 55 to + 175	°C
Soldering Recommendations (Peak Temperature) ^{d, e}			260	260	

THERMAL RESISTANCE RATINGS

PARAMETER		SYMBOL	TYPICAL	MAXIMUM	UNIT
Junction-to-Ambient		R _{thJA}	26	33	°C/W
	PCB Mount ^c		65	81	
Junction-to-Case (Drain)		R _{thJC}	1.9	2.4	

Notes







- Package limited.
- Pulse test; pulse width ≤ 300 µs, duty cycle ≤ 2 %.
- When mounted on 1" square PCB (FR-4 material).
- See solder profile (www.vishay.com/doc?73257). The PowerPAK 1212-8 is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection.
- Rework conditions: manual soldering with a soldering iron is not recommended for leadless components.





SPECIFICATIONS ($T_C = 25^\circ\text{C}$, unless otherwise noted)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT
Static						
Drain-Source Breakdown Voltage	V_{DS}	$V_{GS} = 0\text{ V}$, $I_D = -250\text{ }\mu\text{A}$	- 60	-	-	V
Gate-Source Threshold Voltage	$V_{GS(\text{th})}$	$V_{DS} = V_{GS}$, $I_D = -250\text{ }\mu\text{A}$	- 1.5	-	- 3	
Gate-Source Leakage	I_{GSS}	$V_{DS} = 0\text{ V}$, $V_{GS} = \pm 20\text{ V}$	-	-	± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{GS} = 0\text{ V}$, $V_{DS} = -60\text{ V}$	-	-	- 1	μA
		$V_{GS} = 0\text{ V}$, $V_{DS} = -60\text{ V}$, $T_j = 125^\circ\text{C}$	-	-	- 5	
		$V_{GS} = 0\text{ V}$, $V_{DS} = -60\text{ V}$, $T_j = 175^\circ\text{C}$	-	-	- 150	
On-State Drain Current ^a	$I_{D(\text{on})}$	$V_{GS} = -10\text{ V}$, $V_{DS} \leq -5\text{ V}$	- 20	-	-	A
Drain-Source On-State Resistance ^a	$R_{DS(\text{on})}$	$V_{GS} = -10\text{ V}$, $I_D = -5.7\text{ A}$	-	0.054	0.065	Ω
		$V_{GS} = -4.5\text{ V}$, $I_D = -4.4\text{ A}$	-	0.090	0.110	
		$V_{GS} = -10\text{ V}$, $I_D = -5.7\text{ A}$, $T_j = 125^\circ\text{C}$	-	-	0.104	
		$V_{GS} = -10\text{ V}$, $I_D = -5.7\text{ A}$, $T_j = 175^\circ\text{C}$	-	-	0.127	
Forward Transconductance ^a	g_{fs}	$V_{DS} = -15\text{ V}$, $I_D = -5.7\text{ A}$	11	-	-	S
Dynamic^b						
Input Capacitance	C_{iss}	$V_{GS} = 0\text{ V}$, $V_{DS} = 25\text{ V}$, $f = 1\text{ MHz}$	-	940	1175	pF
Output Capacitance	C_{oss}		-	151	189	
Reverse Transfer Capacitance	C_{rss}		-	54	68	
Total Gate Charge ^c	Q_g	$V_{GS} = -10\text{ V}$, $V_{DS} = -30\text{ V}$, $I_D = -5.7\text{ A}$	-	15	25	nC
Gate-Source Charge ^c	Q_{gs}		-	4	-	
Gate-Drain Charge ^c	Q_{gd}		-	3.2	-	
Gate Resistance	R_g	$f = 1\text{ MHz}$	0.8	1.8	2.8	Ω
Turn-On Delay Time ^c	$t_{d(\text{on})}$	$V_{DD} = -30\text{ V}$, $R_L = 30\text{ }\Omega$	-	12	20	ns
Rise Time ^c	t_r		-	12	20	
Turn-Off Delay Time ^c	$t_{d(\text{off})}$		-	22	35	
Fall Time ^c	t_f		-	16	25	
Source-Drain Diode Ratings and Characteristics $T_C = 25^\circ\text{C}^b$						
Pulsed Current ^a	I_{SM}		-	-	- 30	A
Forward Voltage	V_{SD}	$I_F = 85\text{ A}$, $V_{GS} = 0\text{ V}$	-	-	- 1.2	V
Reverse Recovery Time	t_{rr}	$I_F = 3.2\text{ A}$, $dI/dt = 100\text{ A}/\mu\text{s}$	-	45	90	ns



Notes

- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\text{ \%}$.
- b. Guaranteed by design, not subject to production testing.
- c. Independent of operating temperature.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$, unless otherwise noted)


TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$, unless otherwise noted)

Source Drain Diode Forward Voltage

Threshold Voltage

Single Pulse Power, Junction-to-Ambient

On-Resistance vs. Gate-to-Source Voltage

THERMAL RATINGS ($T_A = 25^\circ\text{C}$, unless otherwise noted)

Note

- The characteristics shown in the two graphs
 - Normalized Transient Thermal Impedance Junction-to-Ambient (25°C)
 - Normalized Transient Thermal Impedance Junction-to-Case (25°C)

are given for general guidelines only to enable the user to get a "ball park" indication of part capabilities. The data are extracted from single pulse transient thermal impedance characteristics which are developed from empirical measurements. The latter is valid for the part mounted on printed circuit board - FR4, size 1" x 1" x 0.062", double sided with 2 oz. copper, 100 % on both sides. The part capabilities can widely vary depending on actual application parameters and operating conditions.

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?74488.

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.