





LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
CM	52	E	REV & REDWN PER EC 0L30-0096-97		4-24-97	TB	RS

1. WIRE RANGE: 0.3 - 1.4 MM² (22 -16 AWG)



RECOMMENDED CUT OUT
FOR 1.57 THICK P.C. BOARD



SECTION A-A

1.02	.040	2.84	.112	8.38	.330	—	—
0.76	.030	2.79	.110	5.08	.200	—	—
0.30	.012	2.54	.100	4.45	.175	—	—
0.25	.010	1.57	.062	4.06	.160	—	—
0.13	.005	1.32	.052	3.81	.150	11.05	.435
0.05	.002	1.22	.048	3.56	.140	10.80	.425
0.00	.000	1.07	.042	2.92	.115	9.65	.380
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

MINI	61782-2
STANDARD	61782-1
APPLICATOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL

0.30 BRASS

FINISH

TIN

DWN
T. BECK
4-24-97

CHK
R. SWING
4-24-97

APVD
A. BEDDICK
4-28-97

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

NAME
AMP Incorporated
Harrisburg, PA 17105-3608

SIZE
A2

CAGE CODE
00779

DRAWING NO
61782

RESTRICTED TO
—

SCALE
10:1

SHEET
1

OF
1

REV
E