





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			R1	REVISED PER 0G3B-0209-04	04-MAR-04	KW	JE


1. WIRE RANGE: 0.2 – 0.6 MM² (24 – 20 AWG)
2. INSULATION RANGE: 1.52 – 2.29



SECTION A-A




SECTION B-B



SECTION C-C

PRE-TIN	0.25 PH BRZ	60986-1
FINISH	MATERIAL	PART NUMBER

1.359	.0535	1.96	.077	2.82	.111	—	—
1.14	.045	1.91	.075	2.79	.110	—	—
0.51	.020	1.52	.060	2.41	.095	10.03	.395
0.25	.010	1.486	.0585	2.29	.090	3.94	.155
0.13	.005	1.47	.058	2.16	.085	3.18	.125
MM	IN	MM	IN	MM	IN	MM	IN
CONVERSION TABLE							



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± 0°30'
FINISH SEE TABLE

DWN
K. WHITAKER
04-MAR-04

CHK
J. ELLIS
04-MAR-04

APVD
J. ELLIS
04-MAR-04

PRODUCT SPEC
108-1025

APPLICATION SPEC
114-1008

WEIGHT
—

CUSTOMER DRAWING

NAME
RECEPTACLE, .058 DIAMETER,
24-20 AWG, .060-.090 INSULATION,
LOOSE PIECE, P.C. CONTACT

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=60986

RESTRICTED TO
—

SCALE
10:1

SHEET
1 OF 1

REV
R1

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

AMP 1471-9 REV 31MAR2000