

C2012X5R0J475K125AA (TDK item description : C2012X5R0J475KT****)

Applications



Commercial Grade


Feature

General

General (Up to 50V)

Series

C2012 [EIA CC0805]




Size	
Length(L)	2.00mm +/-0.20mm
Width(W)	1.25mm +/-0.20mm
Thickness(T)	1.25mm +/-0.20mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	0.50mm Min.
Recommended Land Pattern(PA)	1.00 to 1.30mm (Flow Soldering) 0.90 to 1.20mm (Reflow Soldering)
Recommended Land Pattern(PB)	1.00 to 1.20mm (Flow Soldering) 0.70 to 0.90mm (Reflow Soldering)
Recommended Land Pattern(PC)	0.80 to 1.10mm (Flow Soldering) 0.90 to 1.20mm (Reflow Soldering)
Recommended Slit Pattern(SD)	

Electrical Characteristics	
Capacitance	4.7uF +/-10%
Rated Voltage	6.3Vdc
Temperature Characteristic	X5R(+/-15%)
Dissipation Factor	5% Max.
Insulation Resistance	21MΩ Min.


Other	
Soldering Method	Reflow, Flow
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000Pcs Min.

C2012X5R0J475K125AA


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




C2012X5R0J475K125AA




C2012X5R0J475K125AA




C2012X5R0J475K125AA



C2012X5R0J475K125AA



C2012X5R0J475K125AA(DC Bias = 0V) C2012X5R0J475K125AA(DC Bias = 3.15V)



C2012X5R0J475K125AA(100kHz) C2012X5R0J475K125AA(500kHz)
C2012X5R0J475K125AA(1MHz)