



Search by part # or keyword



Products

Industries & Solutions

Resources

TE Store


Sign In



[Harnessing](#) > [Heat Shrink Components](#) > [Heat Shrink Boots](#)

202K153-3-01/42-0

202K153-3-01/42-0



Raychem

TE Internal #: **879386-000**

TE Internal Description: **202K153-3-01/42-0**

Alias #: **3-1196846-6**

Molded Part Shape : **Straight**

Molded Part Shape Code : **202**

Lipped : **Yes**

Material Code : **3**

Material Systems Code : **10**

[Similar Products](#)

Compatible Parts & Tooling

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Feedback

Documents

Features

Product Compliance

Datasheets & Catalog Pages

1654025_Sec4_-3

[ENG_CS_1654025_Sec4_-3_0313.pdf](#) English

Product Specifications

Product Specification

[ENG_SS_RT-301_12.pdf](#) English

Product Environmental Compliance

Safety Datasheet

[DUT_MSDS_RAY3143-EC-DUT_2014-06-11_3143ECN.pdf](#) Dutch

[ENG_MSDS_RAY3143-EC-ENG_2014-06-11_3143ECE.pdf](#) English

Safety Datasheet

[FRE_MSDS_RAY3143-EC-FRE_2014-06-11_3143ECF.pdf](#) French

Safety Datasheet

[GER_MSDS_RAY3143-EC-GER_2014-06-11_3143ECD.pdf](#) German

Safety Datasheet

[ITA_MSDS_RAY3143-EC-ITA_2014-06-11_3143ECL.pdf](#) Italian

Safety Datasheet

[SPA_MSDS_RAY3143-EC-SPA_2014-06-11_3143ECS.pdf](#) Spanish

Safety Datasheet

[SWE_MSDS_RAY3143-EC-SWE_2014-06-11_3143ECW.pdf](#) Swedish

Safety Datasheet

[ENG_MSDS_SDS0190-EC-ENG_2014-04-10.pdf](#)

English

Safety Datasheet

[FRE_MSDS_SDS0190-EC-FRE_2014-04-10.pdf](#)

French

Safety Datasheet

[GER_MSDS_SDS0190-EC-GER_2014-04-10.pdf](#)

German

Safety Datasheet

[ITA_MSDS_SDS0190-EC-ITA_2014-04-10.pdf](#)

Italian

Safety Datasheet

[NOR_MSDS_SDS0190-EC-NOR_2014-04-10.pdf](#)

Norwegian

Safety Datasheet

[SPA_MSDS_SDS0190-EC-SPA_2014-04-10.pdf](#)

Spanish

Safety Datasheet

[SWE_MSDS_SDS0190-EC-SWE_2014-02-21_SDS190ECW.pdf](#)

Swedish

Safety Datasheet

[DUT_MSDS_SDS0190-EC-DUT_2014-04-10.pdf](#)

Dutch

Safety Datasheet

[DAN_MSDS_SDS0190-EC-DAN_2014-04-10.pdf](#)

Danish

Safety Datasheet

[ENG_MSDS_RAY3143-US-ENG_B.pdf](#)

English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type
Features

Molded Part Shape : **Straight**

Configuration
Features

Lipped : **Yes**

Body Features

Material Code : **3**

Material Systems Code : **10**

Adhesive Pre-Coat : **Yes**

Material : **Semi-Rigid Modified Polyolefin**

Dimensions

Cable Diameter Range : **8.4 – 19 mm [8.4 – 20 in]**

Wire/Cable Outside Diameter :

.35 in, .39 in, .43 in, .433 in, .47 in, .55 in, .63 in, 10 mm, 11 mm, 12 mm, 14 mm, 16 mm, 9 mm

Usage Conditions

Operating Temperature Range : **-55 – 135 °C [-67 – 275 °F]**

Operation/Application Power Cable Accessory : **No**

Industry Standards	Approved Standards : BS-G-198-5-DA, DEF Std 59-97 Issue 3 Type DA, SAE AS I 81765/1, Type I, UL 224, File E85381 Government Qualified : No
Other	Molded Part Shape Code : 202 Fluid/Chemical Resistance : Occasional exposure to fluids Adhesive Type : General Purpose Pre-Coat Adhesive
EU RoHS Directive 2011/65/EU <i>This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU. The restrictions under 2015/863/EU apply as of 22 July 2021 for EEE categories 8 (medical devices) and 9 (monitoring and control equipment).</i>	
EU ELV Directive 2000/53/EC	
China RoHS 2 Directive MIIT Order No 32, 2016	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	
Solder Process Capability	Not applicable for solder process capability
Statement of Compliance	Statement of Compliance pdf
Compliance Documents	There may be Environmental Compliance related documents on the DOCUMENTATION Tab
Disclaimer	This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU.

Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

TOP RESULTS ?


HEAT SHRINK BOOTS
202K153-3-01/42-0
202K153-3-01/42-0



Non-Stocked

Molded Part Shape : **Straight**
Molded Part Shape Code : **202**
Lipped : **Yes**
Material Code : **3**
Material Systems Code : **10**

HEAT SHRINK BOOTS
202K153-3/42-0
202K153-3/42-0



From **In-Stock**

Molded Part Shape : **Straight**
Molded Part Shape Code : **202**
Lipped : **Yes**
Material Code : **3**
Material Systems Code : **10**


HEAT SHRINK BOOTS
222K152-3/42-0
222K152-3/42-0



In-Stock

Molded Part Shape : **90°**
Molded Part Shape Code : **222**
Lipped : **Yes**
Material Code : **3**
Material Systems Code : **10**

HEAT SHRINK BOOTS
222D242-4-61/42-0
222D242-4-61/42-0



Non-Stocked

Molded Part Shape : **90°**
Molded Part Shape Code : **222**
Lipped : **Yes**
Material Code : **4**
Material Systems Code : **10**