




NOTES:

- MATERIALS AND FINISHES:  
 BAYONET SLEEVE - BRASS, NICKEL PLATING (.000100/.000250) THICK  
 BODIES - BRASS, NICKEL PLATING (.000100/.000250) THICK  
 WASHER - BRASS, NICKEL PLATING (.000100/.000250) THICK  
 CLAMP - BRASS, NICKEL PLATING (.000100/.000250) THICK  
 CONTACT - BeCu, GOLD PLATING (.00005/.0001 THICK) OVER NICKEL  
 OUTER CONTACT - BeCu, GOLD PLATING (.00005/.0001 THICK) OVER NICKEL  
 REAR OUTER CONTACT - BRASS, NICKEL PLATING (.000100/.000250) THICK  
 REAR GASKET - FLOUROSILICONE, COLOR: BLUE  
 FRONT GASKET - SILICONE RUBBER  
 INSULATORS - PTFE  
 SPACER - BRASS, NICKEL PLATING(.000100/.000250) THICK  
 RETAINING RING - BRASS, NICKEL PLATING (.000100/.000250) THICK  
 SPRING WASHER - BeCu, GOLD PLATING (.0005/.0001 THICK) OVER NICKEL  
 FERRULE - COPPER TUBING, NICKEL PLATING (.000100/.000250) THICK
- ELECTRICAL:  
 A. IMPEDANCE: NON-CONSTANT CAN BE USED WITH 50, 75 AND 93 OHM TRIAXIAL CABLES  
 B. FREQUENCY RANGE: DC - 500 MHz
- ENVIRONMENTAL:  
 A. TEMPERATURE RANGE: -65° C TO 165° C
- FOR ASSEMBLY AND STRIPPING INSTRUCTIONS SEE 9-9950-433
- FERRULE TO BE CRIMPED WITH A .178 HEX DIE  
 CONTACT TO BE SOLDERED
- ASTERISK (\*) INDICATES CABLE ENTRY DIMENSIONS

31-33485-7		REVISIONS			
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	--	RELEASE TO MFG.	--	--	--
	Y	REDRAW IN PRO-E; ADDED PARENTHESIS TO STAMP	9/13/11	48728	MJS



POLARITY



**CUSTOMER OUTLINE DRAWING**  
 ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL      3 PLACE DECIMAL      ANGLES ±.015 (0,381 mm)      ±.005 (0,127 mm)      ± 1°	MATERIAL	DRAWN	DATE	TITLE BNC R/A TRIAX PLUG FOR BOEING ST5M1323	Amphenol Amphenol Corporation Communication and Network Products Division Danbury, CT U.S.A. 06810
		M. SANCA	13-Sep-11		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE	ENGINEER	DATE	SCALE: 3.0:1      SHEET      2 OF 2	
	McDONNELL-DOUGLAS SPEC. ST5M1344RS5B	K. CAPOZZI	13-Sep-11		
			APPROVED	DATE	
		K. CAPOZZI	9/9/11		
		CAD FILE	CODE ID	DWG SIZE	DRAWING NO.
		31-33485-7	74868	B	31-33485-7
					REV
					Y

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[31-33485-7](#)