

APPROVAL SHEET

MULTILAYER CERAMIC CAPACITORS

High Capacitance Series

0402 to 1812 Sizes

X7R, X5R & Y5V Dielectrics

RoHS Compliance

CUSTOMER:

PRODUCTION_PN:

ISSUE DATE:

APPROVED BY: Derak Peng

*Contents in this sheet are subject to change without prior notice.

1. DESCRIPTION

MLCC consists of a conducting material and electrodes. To manufacture a chip-type SMT and achieve miniaturization, high density and high efficiency, ceramic condensers are used.

WTC high capacitance MLCC offers low ESR and excellent frequency characteristics to be suited for coupling and decoupling applications in circuit. The high dielectric constant material X7R, X5R and Y5V are used for this series product.

2. FEATURES

- Small size with high capacitance.
- Capacitor with lead-free termination (pure Tin).

3. APPLICATIONS


- Digital circuit coupling or decoupling applications.
- For high frequency and high-density type power suppliers.
- For bypassing.

4. HOW TO ORDER

<u>1206</u>	<u>E</u>	<u>106</u>	<u>Z</u>	<u>100</u>	<u>C</u>	<u>I</u>
<u>Size</u>	<u>Dielectric</u>	<u>Capacitance</u>	<u>Tolerance</u>	<u>Rated voltage</u>	<u>Termination</u>	<u>Packaging</u>
Inch (mm) 0402 (1005) 0603 (1608) 0805 (2012) 1206 (3216) 1210 (3225) 1812 (4532)	B =X7R X =X5R F =Y5V	Two significant digits followed by no. of zeros. And R is in place of decimal point. eg.: 106=10x10 ⁶ =10μF	K =±10% M =±20% Z =-20/+80%	Two significant digits followed by no. of zeros. And R is in place of decimal point. 6R3 =6.3 VDC 100 =10 VDC 160 =16 VDC 250 =25 VDC 500 =50 VDC 101 =100 VDC	C =Cu/Ni/Sn	T =7" reeled G =13" reeled

5. EXTERNAL DIMENSIONS

Size Inch (mm)	L (mm)	W (mm)	T (mm)/Symbol	Remark	M _B (mm)
0402 (1005)	1.00±0.05	0.50±0.05	0.50±0.05	N #	0.25 +0.05/-0.10
0603 (1608)	1.60±0.10	0.80±0.10	0.80±0.07	S	0.40±0.15
	1.60+0.15/-0.10	0.80+0.15/-0.10	0.80+0.15/-0.10	X	
0805 (2012)	2.00±0.15	1.25±0.10	0.80±0.10	B	0.50±0.20
			1.25±0.10	D #	
	2.00±0.20	1.25±0.20	1.25±0.20	I #	
1206 (3216)	3.20±0.15	1.60±0.15	0.95±0.10	C #	0.60±0.20
			1.25±0.10	D #	
	3.20±0.20	1.60±0.20	1.60±0.20	G #	
			1.15±0.15	J #	
	3.20+0.30/-0.10	1.60+0.30/-0.10	1.60+0.30/-0.10	P #	
1210 (3225)	3.20±0.30	2.50±0.20	0.95±0.10	C #	0.75±0.25
			1.25±0.10	D #	
	3.20±0.40	2.50±0.30	1.60±0.20	G #	
			2.00±0.20	K #	
			2.50±0.30	M #	
1812 (4532)	4.50±0.40	3.20±0.30	1.25±0.10	D #	0.75±0.25
			2.00±0.20	K #	
	4.50±0.40	3.20±0.40	2.50±0.30	M #	



Reflow soldering only is recommended.

6. GENERAL ELECTRICAL DATA

Dielectric	X7R	X5R	Y5V
Size	0402, 0603, 0805, 1206, 1210, 1812		
Capacitance range*	0.56μF to 10μF	0.027μF to 22μF	1μF to 100μF
Capacitance tolerance**	K (±10%), M (±20%)		Z (-20/+80%)
Rated voltage (WVDC)	6.3V, 10V, 16V, 25V, 50V, 100V		
Tan δ*	Note 1		
Insulation resistance at U _r	R _x C≥500ΩxF		
Operating temperature	-55 to +125°C	-55 to +85°C	-25 to +85°C
Capacitance characteristic	±15%		+30/-80%
Termination	Ni/Sn (lead-free termination)		

* Measured at 1.0±0.2Vrms, 1.0kHz±10% for C≤10μF; 0.5±0.2Vrms, 120Hz±20% for C>10μF, 30~70% related humidity, 25°C ambient temperature for X7R, X5R and at 20°C for Y5V.

** Preconditioning for Class II MLCC: Perform a heat treatment at 150±10°C for 1 hour, then leave in ambient condition for 24±2 hours before measurement.

Note 1:

X7R/X5R

Rated vol.	D.F. ≤	Exception of D.F. ≤
≥50V	2.5%	3% 0603 ≥ 0.047μF; 0805 ≥ 0.18μF; 1206 ≥ 0.47μF
25V	3.5%	5% 0805 ≥ 1μF; 1210 ≥ 10μF
		7% 0603 ≥ 0.33μF; 1206 ≥ 4.7μF
		10% 0402 ≥ 0.10μF; 0603 ≥ 0.47μF; 0805 ≥ 2.2μF; 1206 ≥ 6.8μF
16V	3.5%	5% 0402 ≥ 0.033μF; 0603 ≥ 0.15μF; 0805 ≥ 0.68μF; 1206 ≥ 2.2μF; 1210 ≥ 4.7μF
		10% 0603 ≥ 0.68μF; 0805 ≥ 2.2μF; 1206 ≥ 4.7μF; 1210 ≥ 22μF
10V	5%	10% 0402 ≥ 0.33μF; 0603 ≥ 0.33μF; 0805 ≥ 2.2μF; 1206 ≥ 2.2μF; 1210 ≥ 22μF;
		15% 0201 ≥ 0.1μF; 0402 ≥ 1μF
6.3V	10%	15% 0603 ≥ 10μF; 0805 ≥ 4.7μF; 1206 ≥ 47μF; 1210 ≥ 100μF;
		20% 0402 ≥ 2.2μF

Y5V

Rated vol.	D.F. ≤	Exception of D.F. ≤
≥50V	5%	7% 0603 ≥ 0.1μF; 0805 ≥ 0.47μF; 1206 ≥ 4.7μF
35V	7%	---
25V	5%	7% 0402 ≥ 0.047μF; 0603 ≥ 0.1μF; 0805 ≥ 0.33μF; 1206 ≥ 1μF; 1210 ≥ 4.7μF
		9% 0402 ≥ 0.068μF; 0603 ≥ 0.47μF; 1206 ≥ 4.7μF; 1210 ≥ 22μF
16V (C<1.0μF)	7%	9% 0402 ≥ 0.068μF; 0603 ≥ 0.68μF
16V (C≥1.0μF)	9%	12.5% 0603 ≥ 2.2μF; 0805 ≥ 3.3μF; 1206 ≥ 10μF; 1210 ≥ 22μF; 1812 ≥ 47μF
10V	12.5%	20% 0402 ≥ 0.47μF
6.3V	20%	---

7. CAPACITANCE RANGE

7-1 X7R Dielectric

DIELECTRIC		X7R																					
SIZE		0603			0805				1206					1210					1812				
RATED VOLTAGE		6.3	10	16	6.3	10	16	25	6.3	10	16	25	50	10	16	25	50	100	10	16	25	50	100
Capacitance	0.56μF (564)		X	X																			
	0.68μF (684)		X	X																			
	0.82μF (824)		X	X																			
	1.0μF (105)	X	X	X		D	D	D		J	J	J	P	D	D	D	D	K	D	D	D	K	K
	1.5μF (155)					I			J	J	J	P											K
	2.2μF (225)		X		I	I	I	I	J	J	J	P			K	G							M
	3.3μF (335)									P	P	P				G							
	4.7μF (475)				I	I			P	P	P	P		K	K	K							
	6.8μF (685)																						
10μF (106)								P	P	P			K	K	K			M	M	M			

1. The letter in cell is expressed the symbol of product thickness.

7-2 X5R Dielectric

Dielectric		X5R																					
Size		0402				0603				0805				1206				1210				1812	
Rated Voltage (VDC)		6.3	10	16	25	6.3	10	16	25	6.3	10	16	25	6.3	10	16	25	6.3	10	16	25	6.3	
Capacitance	0.027μF (273)			N																			
	0.033μF (333)			N																			
	0.039μF (393)			N																			
	0.047μF (473)			N																			
	0.056μF (563)		N	N																			
	0.068μF (683)		N	N																			
	0.082μF (823)	N	N	N																			
	0.10μF (104)	N	N	N	N																		
	0.15μF (154)																						
	0.22μF (224)	N	N	N				X	X														
	0.27uF (274)						X	X															
	0.33μF (334)	N	N			X	X	X	X														
	0.39μF (394)						X	X															
	0.47μF (474)	N	N				X	X	X														
	0.68μF (684)	N	N				X	X	X														
	0.82uF (824)					X	X	X															
	1.0μF (105)	N	N			X	X	X	X														
	1.5μF (155)					X				I	I				J	J			K	K			
	2.2μF (225)	N				X	X	X		I	I	I	I		J	J	P		K	K			
	3.3μF (335)									I	I	I	I		P	P	P						
	4.7μF (475)	N				X	X			I	I	I	I	P	P	P	P		K	K	K		
	6.8uF (685)													P	P								
	10μF (106)					X				I	I	I		P	P	P	P	K	K	K	K		
	22μF (226)									I	I			P	P			M	M	M			
	47μF (476)									I				P				M	M				
	100μF (107)																	M				U	

1. The letter in cell is expressed the symbol of product thickness.

7-3 Y5V Dielectric

DIELECTRIC		Y5V										
SIZE		0402		0603				0805				
RATED VOLTAGE (VDC)		63	10	63	10	16	25	6.3	10	16	25	50
Capacitance	1.0μF (105)	N	N		S	X	X		B	B	D	D
	1.5μF (155)				S				D	D		
	2.2μF (225)			S	S	X			D	D	I	I
	3.3μF (335)								D	D		
	4.7μF (475)			X	X				D	D	I	
	6.8μF (685)								I			
	10μF (106)							I	I	I		
	22μF (226)							I				

DIELECTRIC		Y5V																
SIZE		1206					1210						1812					
RATED VOLTAGE (VDC)		10	16	25	35	50	6.3	10	16	25	35	50	63	10	16	25	50	100
Capacitance	1.0μF (105)	C	C	C		C		C	C	C		C		D	D	D	D	D
	1.5μF (155)	C	C	C				C	C	C				D	D	D	D	
	2.2μF (225)	C	C	C		J		C	C	C		G		D	D	D	D	
	3.3μF (335)	J	J	J				C	C	C				D	D	D	D	
	4.7μF (475)	J	J	J	J	P		C	C	D		G		D	D	D	D	
	6.8μF (685)	J	J					C	C	D				D	D	D	D	
	10μF (106)	J	J	P				D	D	G	K	G		D	D	D	K	
	22μF (226)	P	P					K	K	K								
	47μF (476)		P				K	K							M			
	100μF (107)						M											

1. The letter in cell is expressed the symbol of product thickness.





8. PACKAGING STYLE AND QUANTITY

Size	Thickness (mm)/Symbol		Paper tape		Plastic tape	
			7" reel	13" reel	7" reel	13" reel
0402 (1005)	0.50±0.05	N	10k	50k	-	-
0603 (1608)	0.80±0.07	S	4k	15k	-	-
	0.80+0.15/-0.10	X	4k	15k	-	-
0805 (2012)	0.80±0.10	B	4k	15k	-	-
	1.25±0.10	D	-	-	3k	10k
	1.25±0.20	I	-	-	3k	10k
1206 (3216)	0.95±0.10	C	-	-	3k	10k
	1.15±0.15	J	-	-	3K	10K
	1.25±0.10	D	-	-	3k	10k
	1.60±0.20	G	-	-	2k	-
	1.60+0.30/-0.10	P	-	-	2k	-
1210 (3225)	0.95±0.10	C	-	-	3k	10k
	1.25±0.10	D	-	-	3k	10k
	1.60±0.20	G	-	-	2k	-
	2.00±0.20	K	-	-	1k	-
	2.50±0.30	M	-	-	1k	-
1812 (4532)	1.25±0.10	D	-	-	1k	-
	2.00±0.20	K	-	-	1k	-
	2.50±0.30	M	-	-	0.5k	-

Unit: pieces

9. ELECTRICAL CHARACTERISTICS

Typical Impedance/ESR vs. Frequency



10. RELIABILITY TEST CONDITIONS AND REQUIREMENTS

No.	Item	Test Condition	Requirements																																																																								
1.	Visual and Mechanical	---	* No remarkable defect. * Dimensions to conform to individual specification sheet.																																																																								
2.	Capacitance	Class I:NP0	* Shall not exceed the limits given in the detailed spec.																																																																								
3.	Q/ D.F. (Dissipation Factor)	Cap≤1000pF 1.0±0.2Vrms, 1MHz±10%	NP0: Cap≥30pF, Q≥1000; Cap<30pF,Q≥400+20C X7R, X5R: <table><tr><th>Rated vol.</th><th>D.F. ≤</th><th colspan="2">Exception of D.F. ≤</th></tr><tr><td>≥ 50V</td><td>2.5%</td><td>3%</td><td>0603≥ 0.047μF; 0805≥ 0.18μF;1206≥ 0.47μF</td></tr><tr><td rowspan="3">25V</td><td rowspan="3">3.5%</td><td>5%</td><td>0805≥ 1μF; 1210≥ 10μF</td></tr><tr><td>7%</td><td>0603≥ 0.33μF; 1206≥ 4.7μF</td></tr><tr><td>10%</td><td>0402≥ 0.10μF;0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF</td></tr><tr><td rowspan="2">16V</td><td rowspan="2">3.5%</td><td>5%</td><td>0402≥ 0.033μF; 0603≥ 0.15μF; 0805≥ 0.68μF;1206≥ 2.2μF;1210≥ 4.7μF</td></tr><tr><td>10%</td><td>0603≥ 0.68μF;0805≥ 2.2μF; 1206≥ 4.7μF;1210≥ 22μF</td></tr><tr><td rowspan="2">10V</td><td rowspan="2">5%</td><td>10%</td><td>0402≥ 0.33μF;0603≥ 0.33μF; 0805≥ 2.2μF;1206≥ 2.2μF;1210≥ 22μF;</td></tr><tr><td>15%</td><td>0201≥ 0.1μF; 0402≥ 1μF</td></tr><tr><td rowspan="2">6.3V</td><td rowspan="2">10%</td><td>15%</td><td>0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF;</td></tr><tr><td>20%</td><td>0402≥ 2.2μF</td></tr></table> Y5V: <table><tr><th>Rated vol.</th><th>D.F.≤</th><th colspan="2">Exception of D.F.≤</th></tr><tr><td>≥ 50V</td><td>5%</td><td>7%</td><td>0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF</td></tr><tr><td>35V</td><td>7%</td><td>---</td><td>---</td></tr><tr><td rowspan="2">25V</td><td rowspan="2">5%</td><td>7%</td><td>0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF</td></tr><tr><td>9%</td><td>0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF</td></tr><tr><td>16V (C<1.0μF)</td><td>7%</td><td>9%</td><td>0402≥ 0.068μF; 0603≥ 0.68μF</td></tr><tr><td></td><td></td><td>12.5%</td><td>0402≥ 0.22μF</td></tr><tr><td>16V (C≥ 1.0μF)</td><td>9%</td><td>12.5%</td><td>0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF</td></tr><tr><td>10V</td><td>12.5%</td><td>20%</td><td>0402≥ 0.47μF</td></tr><tr><td>6.3V</td><td>20%</td><td>---</td><td>---</td></tr></table>	Rated vol.	D.F. ≤	Exception of D.F. ≤		≥ 50V	2.5%	3%	0603≥ 0.047μF; 0805≥ 0.18μF;1206≥ 0.47μF	25V	3.5%	5%	0805≥ 1μF; 1210≥ 10μF	7%	0603≥ 0.33μF; 1206≥ 4.7μF	10%	0402≥ 0.10μF;0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF	16V	3.5%	5%	0402≥ 0.033μF; 0603≥ 0.15μF; 0805≥ 0.68μF;1206≥ 2.2μF;1210≥ 4.7μF	10%	0603≥ 0.68μF;0805≥ 2.2μF; 1206≥ 4.7μF;1210≥ 22μF	10V	5%	10%	0402≥ 0.33μF;0603≥ 0.33μF; 0805≥ 2.2μF;1206≥ 2.2μF;1210≥ 22μF;	15%	0201≥ 0.1μF; 0402≥ 1μF	6.3V	10%	15%	0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF;	20%	0402≥ 2.2μF	Rated vol.	D.F.≤	Exception of D.F.≤		≥ 50V	5%	7%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF	35V	7%	---	---	25V	5%	7%	0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF	9%	0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF	16V (C<1.0μF)	7%	9%	0402≥ 0.068μF; 0603≥ 0.68μF			12.5%	0402≥ 0.22μF	16V (C≥ 1.0μF)	9%	12.5%	0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF	10V	12.5%	20%	0402≥ 0.47μF	6.3V	20%	---	---
		Rated vol.		D.F. ≤	Exception of D.F. ≤																																																																						
		≥ 50V		2.5%	3%	0603≥ 0.047μF; 0805≥ 0.18μF;1206≥ 0.47μF																																																																					
		25V		3.5%	5%	0805≥ 1μF; 1210≥ 10μF																																																																					
					7%	0603≥ 0.33μF; 1206≥ 4.7μF																																																																					
					10%	0402≥ 0.10μF;0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF																																																																					
		16V		3.5%	5%	0402≥ 0.033μF; 0603≥ 0.15μF; 0805≥ 0.68μF;1206≥ 2.2μF;1210≥ 4.7μF																																																																					
					10%	0603≥ 0.68μF;0805≥ 2.2μF; 1206≥ 4.7μF;1210≥ 22μF																																																																					
		10V		5%	10%	0402≥ 0.33μF;0603≥ 0.33μF; 0805≥ 2.2μF;1206≥ 2.2μF;1210≥ 22μF;																																																																					
					15%	0201≥ 0.1μF; 0402≥ 1μF																																																																					
6.3V	10%	15%	0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF;																																																																								
		20%	0402≥ 2.2μF																																																																								
Rated vol.	D.F.≤	Exception of D.F.≤																																																																									
≥ 50V	5%	7%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF																																																																								
35V	7%	---	---																																																																								
25V	5%	7%	0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF																																																																								
		9%	0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF																																																																								
16V (C<1.0μF)	7%	9%	0402≥ 0.068μF; 0603≥ 0.68μF																																																																								
		12.5%	0402≥ 0.22μF																																																																								
16V (C≥ 1.0μF)	9%	12.5%	0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF																																																																								
10V	12.5%	20%	0402≥ 0.47μF																																																																								
6.3V	20%	---	---																																																																								
4.	Dielectric Strength	* To apply voltage (≤100V) 250%. * Duration: 1 to 5 sec. * Charge and discharge current less than 50mA.	* No evidence of damage or flash over during test.																																																																								
5.	Insulation Resistance	To apply rated voltage for max. 120 sec.	10GΩ or RxC≥ 500Ω-F whichever is smaller. Class II (X7R, X5R, Y5V) <table><tr><th>Rated voltage</th><th>Insulation Resistance</th></tr><tr><td>100V: X7R</td><td rowspan="4">10GΩ or RxC≥ 100 Ω-F whichever is smaller.</td></tr><tr><td>16V:0402≥0.22μF</td></tr><tr><td>10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF</td></tr><tr><td>6.3V</td></tr></table>	Rated voltage	Insulation Resistance	100V: X7R	10GΩ or RxC≥ 100 Ω-F whichever is smaller.	16V:0402≥0.22μF	10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF	6.3V																																																																	
Rated voltage	Insulation Resistance																																																																										
100V: X7R	10GΩ or RxC≥ 100 Ω-F whichever is smaller.																																																																										
16V:0402≥0.22μF																																																																											
10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF																																																																											
6.3V																																																																											
6.	Temperature Coefficient	With no electrical load. <table><tr><th>T.C.</th><th>Operating Temp</th></tr><tr><td>NPO</td><td>-55~125°C at 25°C</td></tr><tr><td>X7R</td><td>-55~125°C at 25°C</td></tr><tr><td>X5R</td><td>-55~ 85°C at 25°C</td></tr><tr><td>Y5V</td><td>-25~ 85°C at 20°C</td></tr></table>	T.C.	Operating Temp	NPO	-55~125°C at 25°C	X7R	-55~125°C at 25°C	X5R	-55~ 85°C at 25°C	Y5V	-25~ 85°C at 20°C	<table><tr><th>T.C.</th><th>Capacitance Change</th></tr><tr><td>NPO</td><td>Within ±30ppm/°C</td></tr><tr><td>X7R</td><td>Within ±15%</td></tr><tr><td>X5R</td><td>Within ±15%</td></tr><tr><td>Y5V</td><td>Within +30%/-80%</td></tr></table>	T.C.	Capacitance Change	NPO	Within ±30ppm/°C	X7R	Within ±15%	X5R	Within ±15%	Y5V	Within +30%/-80%																																																				
T.C.	Operating Temp																																																																										
NPO	-55~125°C at 25°C																																																																										
X7R	-55~125°C at 25°C																																																																										
X5R	-55~ 85°C at 25°C																																																																										
Y5V	-25~ 85°C at 20°C																																																																										
T.C.	Capacitance Change																																																																										
NPO	Within ±30ppm/°C																																																																										
X7R	Within ±15%																																																																										
X5R	Within ±15%																																																																										
Y5V	Within +30%/-80%																																																																										
7.	Adhesive Strength of Termination	* Pressurizing force : 5N (≤0603) and 10N (>0603) * Test time: 10±1 sec.	* No remarkable damage or removal of the terminations.																																																																								

No.	Item	Test Condition	Requirements															
8.	Vibration Resistance	* Vibration frequency: 10~55 Hz/min. * Total amplitude: 1.5mm * Test time: 6 hrs. (Two hrs each in three mutually perpendicular directions.)	* No remarkable damage. * Cap change and Q/D.F.: To meet initial spec.															
9.	Solderability	* Solder temperature: 235±5°C * Dipping time: 2±0.5 sec.	95% min. coverage of all metalized area.															
10.	Bending Test	* The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1 mm per second until the deflection becomes 1 mm and then the pressure shall be maintained for 5±1 sec. * Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).	* No remarkable damage. * Cap change : NP0: within ±5% or 0.5pF whichever is larger X7R, X5R: within ±12.5% Y5V: within ±30% (This capacitance change means the change of capacitance under specified flexure of substrate from the capacitance measured before the test.)															
11.	Resistance to Soldering Heat	* Solder temperature: 260±5°C * Dipping time: 10±1 sec * Preheating: 120 to 150°C for 1 minute before immerse the capacitor in a eutectic solder. * Before initial measurement (Class II only): Perform 150+0/-10°C for 1 hr and then set for 48±4 hrs at room temp. * Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).	* No remarkable damage. * Cap change: NP0: within ±2.5% or 0.25pF whichever is larger X7R, X5R: within ±7.5% Y5V: within ±20% * Q/D.F., I.R. and dielectric strength: To meet initial requirements. * 25% max. leaching on each edge.															
12.	Temperature Cycle	* Conduct the five cycles according to the temperatures and time. <table><tr><th>Step</th><th>Temp. (°C)</th><th>Time (min.)</th></tr><tr><td>1</td><td>Min. operating temp. +0/-3</td><td>30±3</td></tr><tr><td>2</td><td>Room temp.</td><td>2~3</td></tr><tr><td>3</td><td>Max. operating temp. +3/-0</td><td>30±3</td></tr><tr><td>4</td><td>Room temp.</td><td>2~3</td></tr></table> * Before initial measurement (Class II only): Perform 150+0/-10°C for 1 hr and then set for 48±4 hrs at room temp. * Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).	Step	Temp. (°C)	Time (min.)	1	Min. operating temp. +0/-3	30±3	2	Room temp.	2~3	3	Max. operating temp. +3/-0	30±3	4	Room temp.	2~3	* No remarkable damage. * Cap change : NP0: within ±2.5% or 0.25pF whichever is larger X7R, X5R: within ±7.5% Y5V: within ±20% * Q/D.F., I.R. and dielectric strength: To meet initial requirements.
Step	Temp. (°C)	Time (min.)																
1	Min. operating temp. +0/-3	30±3																
2	Room temp.	2~3																
3	Max. operating temp. +3/-0	30±3																
4	Room temp.	2~3																

No.	Item	Test Condition	Requirements																																		
13.	Humidity (Damp Heat) Steady State	* Test temp.: 40±2°C	* No remarkable damage.																																		
		* Humidity: 90–95% RH	* Cap change:																																		
		* Test time: 500+24/-0hrs.	NP0: within ±5% or 0.5pF whichever is larger																																		
		* Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).	X7R, X5R: ≥10V, within ±12.5%; 6.3V, within ±25%																																		
			Y5V: ≥10V, within ±30%; 6.3V, within +30/-40%																																		
			* Q/D.F. value:																																		
			NP0: More than 30pF Q≥350, 10pF≤C≤30pF, Q≥275+2.5C																																		
			Less than 10pF Q≥200+10C																																		
			X7R, X5R:																																		
			<table><tr><th>Rated vol.</th><th>D.F.≤</th><th colspan="2">Exception of D.F.≤</th></tr><tr><td>≥ 50V</td><td>3%</td><td>6%</td><td>0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF</td></tr><tr><td rowspan="3">25V</td><td rowspan="3">5%</td><td>10%</td><td>0805≥ 1μF; 1210≥ 10μF</td></tr><tr><td>14%</td><td>0603≥ 0.33μF; 1206≥ 4.7μF</td></tr><tr><td>15%</td><td>0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF</td></tr><tr><td rowspan="2">16V</td><td rowspan="2">5%</td><td>10%</td><td>0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF</td></tr><tr><td>15%</td><td>0402≥ 0.033μF; 0603≥ 0.68μF; 0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF</td></tr><tr><td rowspan="2">10V</td><td rowspan="2">7.5%</td><td>15%</td><td>0402≥ 0.33μF; 0603≥ 0.33μF; 0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF</td></tr><tr><td>20%</td><td>0201≥ 0.1μF ;0402≥ 1μF</td></tr><tr><td>6.3V</td><td>15%</td><td>30%</td><td>0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF</td></tr></table>	Rated vol.	D.F.≤	Exception of D.F.≤		≥ 50V	3%	6%	0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF	25V	5%	10%	0805≥ 1μF; 1210≥ 10μF	14%	0603≥ 0.33μF; 1206≥ 4.7μF	15%	0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF	16V	5%	10%	0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF	15%	0402≥ 0.033μF; 0603≥ 0.68μF; 0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF	10V	7.5%	15%	0402≥ 0.33μF; 0603≥ 0.33μF; 0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF	20%	0201≥ 0.1μF ;0402≥ 1μF	6.3V	15%	30%	0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF		
		Rated vol.	D.F.≤	Exception of D.F.≤																																	
		≥ 50V	3%	6%	0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF																																
		25V	5%	10%	0805≥ 1μF; 1210≥ 10μF																																
				14%	0603≥ 0.33μF; 1206≥ 4.7μF																																
				15%	0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF																																
16V	5%	10%	0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF																																		
		15%	0402≥ 0.033μF; 0603≥ 0.68μF; 0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF																																		
10V	7.5%	15%	0402≥ 0.33μF; 0603≥ 0.33μF; 0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF																																		
		20%	0201≥ 0.1μF ;0402≥ 1μF																																		
6.3V	15%	30%	0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF																																		
	Y5V:																																				
	<table><tr><th>Rated vol.</th><th>D.F.≤</th><th colspan="2">Exception of D.F.≤</th></tr><tr><td>≥ 50V</td><td>7.5%</td><td>10%</td><td>0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF</td></tr><tr><td>35V</td><td>10%</td><td>---</td><td>---</td></tr><tr><td rowspan="2">25V</td><td rowspan="2">7.5%</td><td>10%</td><td>0402≥ 0.047μF; 0603≥ 0.1μF; 0805≥ 0.33μF; 1206≥ 1μF; 1210≥ 4.7μF</td></tr><tr><td>15%</td><td>0402≥ 0.068μF; 0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF</td></tr><tr><td>16V (C<1.0μF)</td><td>10%</td><td>12.5%</td><td>0402≥ 0.068μF; 0603≥ 0.68μF</td></tr><tr><td rowspan="2">16V (C≥ 1.0μF)</td><td rowspan="2">12.5%</td><td>20%</td><td>0402≥ 0.22μF</td></tr><tr><td></td><td>0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF;</td></tr><tr><td>10V</td><td>20%</td><td>30%</td><td>0402≥ 0.47μF</td></tr><tr><td>6.3V</td><td>30%</td><td>---</td><td>---</td></tr></table>	Rated vol.	D.F.≤	Exception of D.F.≤		≥ 50V	7.5%	10%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF	35V	10%	---	---	25V	7.5%	10%	0402≥ 0.047μF; 0603≥ 0.1μF; 0805≥ 0.33μF; 1206≥ 1μF; 1210≥ 4.7μF	15%	0402≥ 0.068μF; 0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF	16V (C<1.0μF)	10%	12.5%	0402≥ 0.068μF; 0603≥ 0.68μF	16V (C≥ 1.0μF)	12.5%	20%	0402≥ 0.22μF		0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF;	10V	20%	30%	0402≥ 0.47μF	6.3V	30%	---	---
Rated vol.	D.F.≤	Exception of D.F.≤																																			
≥ 50V	7.5%	10%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF																																		
35V	10%	---	---																																		
25V	7.5%	10%	0402≥ 0.047μF; 0603≥ 0.1μF; 0805≥ 0.33μF; 1206≥ 1μF; 1210≥ 4.7μF																																		
		15%	0402≥ 0.068μF; 0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF																																		
16V (C<1.0μF)	10%	12.5%	0402≥ 0.068μF; 0603≥ 0.68μF																																		
16V (C≥ 1.0μF)	12.5%	20%	0402≥ 0.22μF																																		
			0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF;																																		
10V	20%	30%	0402≥ 0.47μF																																		
6.3V	30%	---	---																																		
	*I.R.: ≥10V, 1GΩ or 50 Ω-F whichever is smaller.																																				
	Class II (X7R, X5R, Y5V)																																				
	<table><tr><th>Rated voltage</th><th>Insulation Resistance</th></tr><tr><td>100V: X7R</td><td rowspan="4">1GΩ or RxC≥ 10 Ω-F whichever is smaller.</td></tr><tr><td>16V:0402≥0.22μF</td></tr><tr><td>10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF; 1206≥4.7μF; 1210≥47μF</td></tr><tr><td>6.3V</td></tr></table>	Rated voltage	Insulation Resistance	100V: X7R	1GΩ or RxC≥ 10 Ω-F whichever is smaller.	16V:0402≥0.22μF	10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF; 1206≥4.7μF; 1210≥47μF	6.3V																													
Rated voltage	Insulation Resistance																																				
100V: X7R	1GΩ or RxC≥ 10 Ω-F whichever is smaller.																																				
16V:0402≥0.22μF																																					
10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF; 1206≥4.7μF; 1210≥47μF																																					
6.3V																																					

No	Item	Test Condition	Requirements																																				
14	Humidity (Damp Heat) Load	* Test temp.: 40±2°C	* No remarkable damage.																																				
		* Humidity: 90~95%RH	Cap change:																																				
		* Test time: 500+24/-0 hrs.	NP0: ±7.5% or 0.75pF whichever is larger.																																				
		* To apply voltage : rated voltage.	X7R, X5R: ≥10V, within ±12.5%; 6.3V, within ±25%																																				
		* Measurement to be made after keeping at room temp.	Y5V: ≥10V, within ±30%; 6.3V, within +30/-40%																																				
		for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).	Q/D.F. value:																																				
			NP0: C≥30pF,Q≥200;C<30pF, Q≥100+10/3C																																				
			X7R, X5R:																																				
			<table><tr><th>Rated vol.</th><th>D.F.≤</th><th colspan="2">Exception of D.F.≤</th></tr><tr><td>≥ 50V</td><td>3%</td><td>6%</td><td>0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF</td></tr><tr><td rowspan="3">25V</td><td rowspan="3">5%</td><td>10%</td><td>0805≥ 1μF; 1210≥ 10μF</td></tr><tr><td>14%</td><td>0603≥ 0.33μF;1206≥ 4.7μF</td></tr><tr><td>15%</td><td>0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF</td></tr><tr><td rowspan="2">16V</td><td rowspan="2">5%</td><td>10%</td><td>0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF</td></tr><tr><td>15%</td><td>0402≥ 0.033μF; 0603≥ 0.68μF;0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF</td></tr><tr><td rowspan="2">10V</td><td rowspan="2">7.5%</td><td>15%</td><td>0402≥ 0.33μF; 0603≥ 0.33μF;0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF</td></tr><tr><td>20%</td><td>0201≥ 0.1μF ;0402≥ 1μF</td></tr><tr><td>6.3V</td><td>15%</td><td>30%</td><td>0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF;1210≥ 100μF</td></tr></table>	Rated vol.	D.F.≤	Exception of D.F.≤		≥ 50V	3%	6%	0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF	25V	5%	10%	0805≥ 1μF; 1210≥ 10μF	14%	0603≥ 0.33μF;1206≥ 4.7μF	15%	0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF	16V	5%	10%	0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF	15%	0402≥ 0.033μF; 0603≥ 0.68μF;0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF	10V	7.5%	15%	0402≥ 0.33μF; 0603≥ 0.33μF;0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF	20%	0201≥ 0.1μF ;0402≥ 1μF	6.3V	15%	30%	0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF;1210≥ 100μF				
		Rated vol.	D.F.≤	Exception of D.F.≤																																			
		≥ 50V	3%	6%	0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF																																		
		25V	5%	10%	0805≥ 1μF; 1210≥ 10μF																																		
				14%	0603≥ 0.33μF;1206≥ 4.7μF																																		
				15%	0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF																																		
16V	5%	10%	0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF																																				
		15%	0402≥ 0.033μF; 0603≥ 0.68μF;0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF																																				
10V	7.5%	15%	0402≥ 0.33μF; 0603≥ 0.33μF;0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF																																				
		20%	0201≥ 0.1μF ;0402≥ 1μF																																				
6.3V	15%	30%	0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF;1210≥ 100μF																																				
	Y5V:																																						
	<table><tr><th>Rated vol.</th><th>D.F.≤</th><th colspan="2">Exception of D.F.≤</th></tr><tr><td>≥ 50V</td><td>7.5%</td><td>10%</td><td>0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF</td></tr><tr><td>35V</td><td>10%</td><td>---</td><td>---</td></tr><tr><td rowspan="2">25V</td><td rowspan="2">7.5%</td><td>10%</td><td>0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF</td></tr><tr><td>15%</td><td>0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF</td></tr><tr><td>16V (C<1.0μF)</td><td>10%</td><td>12.5%</td><td>0402≥ 0.068μF; 0603≥ 0.68μF</td></tr><tr><td></td><td></td><td>20%</td><td>0402≥ 0.22μF</td></tr><tr><td>16V (C≥ 1.0μF)</td><td>12.5%</td><td>20%</td><td>0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF;1210≥ 22μF; 1812≥ 47μF;</td></tr><tr><td>10V</td><td>20%</td><td>30%</td><td>0402≥ 0.47μF</td></tr><tr><td>6.3V</td><td>30%</td><td>---</td><td>---</td></tr></table>	Rated vol.	D.F.≤	Exception of D.F.≤		≥ 50V	7.5%	10%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF	35V	10%	---	---	25V	7.5%	10%	0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF	15%	0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF	16V (C<1.0μF)	10%	12.5%	0402≥ 0.068μF; 0603≥ 0.68μF			20%	0402≥ 0.22μF	16V (C≥ 1.0μF)	12.5%	20%	0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF;1210≥ 22μF; 1812≥ 47μF;	10V	20%	30%	0402≥ 0.47μF	6.3V	30%	---	---
Rated vol.	D.F.≤	Exception of D.F.≤																																					
≥ 50V	7.5%	10%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF																																				
35V	10%	---	---																																				
25V	7.5%	10%	0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF																																				
		15%	0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF																																				
16V (C<1.0μF)	10%	12.5%	0402≥ 0.068μF; 0603≥ 0.68μF																																				
		20%	0402≥ 0.22μF																																				
16V (C≥ 1.0μF)	12.5%	20%	0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF;1210≥ 22μF; 1812≥ 47μF;																																				
10V	20%	30%	0402≥ 0.47μF																																				
6.3V	30%	---	---																																				
	*I.R.: ≥10V, 500MΩ or 25 Ω-F whichever is smaller.																																						
	Class II (X7R, X5R, Y5V)																																						
	<table><tr><th>Rated voltage</th><th>Insulation Resistance</th></tr><tr><td>100V: X7R</td><td rowspan="4">500MΩ or RxC≥ 5 Ω-F whichever is smaller.</td></tr><tr><td>16V:0402≥0.22μF</td></tr><tr><td>10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF</td></tr><tr><td>6.3V</td></tr></table>	Rated voltage	Insulation Resistance	100V: X7R	500MΩ or RxC≥ 5 Ω-F whichever is smaller.	16V:0402≥0.22μF	10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF	6.3V																															
Rated voltage	Insulation Resistance																																						
100V: X7R	500MΩ or RxC≥ 5 Ω-F whichever is smaller.																																						
16V:0402≥0.22μF																																							
10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF																																							
6.3V																																							

No	Item	Test Condition	Requirements																																																																												
15.	High Temperature Load (Endurance)	Test temp. : NP0, X7R/X7E: 125±3°C X5R, Y5V: 85±3°C Test time: 1000+24/-0 hrs. To apply voltage: (1) 6.3V or C≥ 10μF or TT series: 150% of rated voltage. (2) 10V≤ Ur<500V: 200% of rated voltage. (3) 500V: 150% of rated voltage. (4) Ur≥ 630V: 120% of rated voltage. (5) 100% of rated voltage for below range.	* No remarkable damage. Cap change: NP0: ±3.0% or ±0.3pF whichever is larger X7R, X5R: ≥10V, within ±12.5%; 6.3V, within ±25% Y5V: ≥10V, within ±30%; 6.3V, within +30/-40% Q/D.F. value: NP0: More than 30pF, Q≥350 10pF≤C<30pF, Q≥275+2.5C Less than 10pF, Q≥200+10C X7R, X5R:																																																																												
		<table><tr><th>Size</th><th>Dielectric</th><th>Rated voltage</th><th>Capacitance range</th></tr><tr><td>0201</td><td>X5R</td><td>6.3V,10V</td><td>C≥ 0.1μF</td></tr><tr><td>0402</td><td>X5R, Y5V</td><td>6.3V,10V</td><td>C≥ 1.0μF</td></tr><tr><td>0603</td><td>X5R</td><td>6.3V,10V</td><td>C≥ 4.7μF</td></tr><tr><td></td><td>Y5V</td><td></td><td>TT≥ 2.2μF</td></tr><tr><td>0805</td><td>X5R</td><td>6.3V</td><td>C≥ 22μF</td></tr><tr><td></td><td>Y5V</td><td></td><td>TT≥ 10μF</td></tr><tr><td>1206</td><td>X5R</td><td>6.3V</td><td>C≥ 47μF</td></tr><tr><td></td><td>Y5V</td><td></td><td>TT≥ 22μF</td></tr></table>	Size	Dielectric	Rated voltage	Capacitance range	0201	X5R	6.3V,10V	C≥ 0.1μF	0402	X5R, Y5V	6.3V,10V	C≥ 1.0μF	0603	X5R	6.3V,10V	C≥ 4.7μF		Y5V		TT≥ 2.2μF	0805	X5R	6.3V	C≥ 22μF		Y5V		TT≥ 10μF	1206	X5R	6.3V	C≥ 47μF		Y5V		TT≥ 22μF	<table><tr><th>Rated vol.</th><th>D.F.≤</th><th colspan="2">Exception of D.F.≤</th></tr><tr><td>≥ 50V</td><td>3%</td><td>6%</td><td>0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF</td></tr><tr><td></td><td></td><td>10%</td><td>0805≥ 1μF; 1210≥ 10μF</td></tr><tr><td>25V</td><td>5%</td><td>14%</td><td>0603≥ 0.33μF;1206≥ 4.7μF</td></tr><tr><td></td><td></td><td>15%</td><td>0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF</td></tr><tr><td>16V</td><td>5%</td><td>10%</td><td>0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF</td></tr><tr><td></td><td></td><td>15%</td><td>0402≥ 0.033μF; 0603≥ 0.68μF;0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF</td></tr><tr><td>10V</td><td>7.5%</td><td>15%</td><td>0402≥ 0.33μF; 0603≥ 0.33μF;0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF</td></tr><tr><td></td><td></td><td>20%</td><td>0201≥ 0.1μF ;0402≥ 1μF</td></tr><tr><td>6.3V</td><td>15%</td><td>30%</td><td>0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF;1210≥ 100μF</td></tr></table>	Rated vol.	D.F.≤	Exception of D.F.≤		≥ 50V	3%	6%	0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF			10%	0805≥ 1μF; 1210≥ 10μF	25V	5%	14%	0603≥ 0.33μF;1206≥ 4.7μF			15%	0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF	16V	5%	10%	0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF			15%	0402≥ 0.033μF; 0603≥ 0.68μF;0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF	10V	7.5%	15%	0402≥ 0.33μF; 0603≥ 0.33μF;0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF			20%	0201≥ 0.1μF ;0402≥ 1μF	6.3V	15%	30%	0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF;1210≥ 100μF
		Size	Dielectric	Rated voltage	Capacitance range																																																																										
		0201	X5R	6.3V,10V	C≥ 0.1μF																																																																										
		0402	X5R, Y5V	6.3V,10V	C≥ 1.0μF																																																																										
		0603	X5R	6.3V,10V	C≥ 4.7μF																																																																										
			Y5V		TT≥ 2.2μF																																																																										
		0805	X5R	6.3V	C≥ 22μF																																																																										
			Y5V		TT≥ 10μF																																																																										
		1206	X5R	6.3V	C≥ 47μF																																																																										
	Y5V		TT≥ 22μF																																																																												
Rated vol.	D.F.≤	Exception of D.F.≤																																																																													
≥ 50V	3%	6%	0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF																																																																												
		10%	0805≥ 1μF; 1210≥ 10μF																																																																												
25V	5%	14%	0603≥ 0.33μF;1206≥ 4.7μF																																																																												
		15%	0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF																																																																												
16V	5%	10%	0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF																																																																												
		15%	0402≥ 0.033μF; 0603≥ 0.68μF;0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF																																																																												
10V	7.5%	15%	0402≥ 0.33μF; 0603≥ 0.33μF;0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF																																																																												
		20%	0201≥ 0.1μF ;0402≥ 1μF																																																																												
6.3V	15%	30%	0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF;1210≥ 100μF																																																																												
(6)150% of rated voltage for below range.	<table><tr><th>Size</th><th>Dielectric</th><th>Rated voltage</th><th>Capacitance range</th></tr><tr><td>0402</td><td>X5R</td><td>10V,16V</td><td>C≥ 0.22μF</td></tr><tr><td></td><td>Y5V</td><td>16V</td><td>C≥ 0.47μF</td></tr><tr><td>0603</td><td>X5R</td><td>10V,16V</td><td>C≥ 1.0μF</td></tr><tr><td></td><td>Y5V</td><td>16V</td><td>C≥ 2.2μF</td></tr><tr><td>0805</td><td>X5R</td><td>10V</td><td>C≥ 4.7μF</td></tr><tr><td></td><td>Y5V</td><td>16V</td><td>C≥ 4.7μF</td></tr></table>	Size	Dielectric	Rated voltage	Capacitance range	0402	X5R	10V,16V	C≥ 0.22μF		Y5V	16V	C≥ 0.47μF	0603	X5R	10V,16V	C≥ 1.0μF		Y5V	16V	C≥ 2.2μF	0805	X5R	10V	C≥ 4.7μF		Y5V	16V	C≥ 4.7μF																																																		
Size	Dielectric	Rated voltage	Capacitance range																																																																												
0402	X5R	10V,16V	C≥ 0.22μF																																																																												
	Y5V	16V	C≥ 0.47μF																																																																												
0603	X5R	10V,16V	C≥ 1.0μF																																																																												
	Y5V	16V	C≥ 2.2μF																																																																												
0805	X5R	10V	C≥ 4.7μF																																																																												
	Y5V	16V	C≥ 4.7μF																																																																												
* Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).																																																																															
			Y5V:																																																																												
			<table><tr><th>Rated vol.</th><th>D.F.≤</th><th colspan="2">Exception of D.F.≤</th></tr><tr><td>≥ 50V</td><td>7.5%</td><td>10%</td><td>0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF</td></tr><tr><td>35V</td><td>10%</td><td>---</td><td>---</td></tr><tr><td>25V</td><td>7.5%</td><td>10%</td><td>0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF</td></tr><tr><td></td><td></td><td>15%</td><td>0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF</td></tr><tr><td>16V (C<1.0μF)</td><td>10%</td><td>12.5%</td><td>0402≥ 0.068μF; 0603≥ 0.68μF</td></tr><tr><td></td><td></td><td>20%</td><td>0402≥ 0.22μF</td></tr><tr><td>16V (C≥ 1.0μF)</td><td>12.5%</td><td>20%</td><td>0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF;1210≥ 22μF; 1812≥ 47μF;</td></tr><tr><td>10V</td><td>20%</td><td>30%</td><td>0402≥ 0.47μF</td></tr><tr><td>6.3V</td><td>30%</td><td>---</td><td>---</td></tr></table>	Rated vol.	D.F.≤	Exception of D.F.≤		≥ 50V	7.5%	10%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF	35V	10%	---	---	25V	7.5%	10%	0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF			15%	0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF	16V (C<1.0μF)	10%	12.5%	0402≥ 0.068μF; 0603≥ 0.68μF			20%	0402≥ 0.22μF	16V (C≥ 1.0μF)	12.5%	20%	0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF;1210≥ 22μF; 1812≥ 47μF;	10V	20%	30%	0402≥ 0.47μF	6.3V	30%	---	---																																				
Rated vol.	D.F.≤	Exception of D.F.≤																																																																													
≥ 50V	7.5%	10%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF																																																																												
35V	10%	---	---																																																																												
25V	7.5%	10%	0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF																																																																												
		15%	0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF																																																																												
16V (C<1.0μF)	10%	12.5%	0402≥ 0.068μF; 0603≥ 0.68μF																																																																												
		20%	0402≥ 0.22μF																																																																												
16V (C≥ 1.0μF)	12.5%	20%	0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF;1210≥ 22μF; 1812≥ 47μF;																																																																												
10V	20%	30%	0402≥ 0.47μF																																																																												
6.3V	30%	---	---																																																																												
			*I.R.: ≥10V, 1GΩ or 50 Ω-F whichever is smaller.																																																																												
			Class II (X7R, X5R, Y5V)																																																																												
			<table><tr><th>Rated voltage</th><th>Insulation Resistance</th></tr><tr><td>100V: X7R</td><td rowspan="4">1GΩ or RxC≥ 10 Ω-F whichever is smaller.</td></tr><tr><td>16V:0402≥0.22μF</td></tr><tr><td>10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF</td></tr><tr><td>6.3V</td></tr></table>	Rated voltage	Insulation Resistance	100V: X7R	1GΩ or RxC≥ 10 Ω-F whichever is smaller.	16V:0402≥0.22μF	10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF	6.3V																																																																					
Rated voltage	Insulation Resistance																																																																														
100V: X7R	1GΩ or RxC≥ 10 Ω-F whichever is smaller.																																																																														
16V:0402≥0.22μF																																																																															
10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF																																																																															
6.3V																																																																															

APPENDIXES

■ Tape & reel dimensions




Fig. 6 The dimension of paper tape




Fig. 7 The dimension of plastic tape

Size	0402	0603	0805			1206			1210			1812	
Thickness	N	S, X	A	B	C, D, I	B	C, J, D	G, P	C, D	G, K	M	D, K	M
A ₀	0.62±0.05	1.02±0.05	1.50±0.10	1.50±0.10	<1.57	2.00±0.10	<1.85	<1.95	<2.97	<2.97	<2.97	<3.81	<3.81
B ₀	1.12±0.05	1.80±0.05	2.30±0.10	2.30±0.10	<2.40	3.50±0.10	<3.46	<3.67	<3.73	<3.73	<3.73	<5.30	<5.30
T	0.60±0.05	0.95±0.05	0.75±0.05	0.95±0.05	0.23±0.05	0.95±0.05	0.23±0.05	0.23±0.05	0.23±0.05	0.23±0.05	0.23±0.05	0.25±0.05	0.25±0.05
K ₀	-	-	-	-	<2.50	-	<2.50	<2.50	<2.50	<2.50	<3.00	<2.50	<3.00
W	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	12.0±0.20	12.0±0.20
P ₀	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10
10xP ₀	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10
P ₁	2.00±0.05	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	8.00±0.10	8.00±0.10
P ₂	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05
D ₀	1.55±0.05	1.55±0.05	1.55±0.05	1.55±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05
D ₁	-	-	-	-	1.00±0.10	-	1.00±0.10	1.00±0.10	1.00±0.10	1.00±0.10	1.00±0.10	1.50±0.10	1.50±0.10
E	1.75±0.05	1.75±0.05	1.75±0.05	1.75±0.05	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10
F	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	5.50±0.05	5.50±0.05





Fig. 8 The dimension of reel

Size	0402, 0603, 0805, 1206, 1210			1812
Reel size	7"	10"	13"	7"
C	13.0+0.5/-0.2	13.0+0.5/-0.2	13.0+0.5/-0.2	13.0+0.5/-0.2
W ₁	8.4+1.5/-0	8.4+1.5/-0	8.4+1.5/-0	12.4+2.0/-0
A	178.0±0.10	250.0±1.0	330.0±1.0	178.0±0.10
N	60.0+1.0/-0	100.0±1.0	100±1.0	60.0+1.0/-0


■ Description of customer label



- a. Customer name
- b. WTC order series and item number
- c. Customer P/O
- d. Customer P/N
- e. Description of product
- f. Quantity
- g. Bar code including quantity & WTC P/N or customer
- h. WTC P/N
- i. Shipping date
- j. Order bar code including series and item numbers
- k. Serial number of label

■ Constructions

No.	Name	X7R, X5R, Y5V
①	Ceramic material	BaTiO ₃ based
②	Inner electrode	Ni
③	Termination	Inner layer
④		Middle layer
⑤		Outer layer
		Sn (Matt)



■ Storage and handling conditions

- (1) To store products at 5 to 40°C ambient temperature and 20 to 70% related humidity conditions.
- (2) The product is recommended to be used within one year after shipment. Check solderability in case of shelf life extension is needed.

Cautions:

- a. Don't store products in a corrosive environment such as sulfide, chloride gas, or acid. It may cause oxidization of electrode, which easily be resulted in poor soldering.
- b. To store products on the shelf and avoid exposure to moisture.
- c. Don't expose products to excessive shock, vibration, direct sunlight and so on.

■ Recommended soldering conditions

The lead-free termination MLCCs are not only to be used on SMT against lead-free solder paste, but also suitable against lead-containing solder paste. If the optimized solder joint is requested, increasing soldering time, temperature and concentration of N_2 within oven are recommended.




Fig. 10 Recommended IR reflow soldering profile for SMT process with SnAgCu series solder paste.




Fig. 11 Recommended wave soldering profile for SMT process with SnAgCu series solder.