

4		3		2		1																																																																																											
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION ,19 .																																																																																													
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.																																																																																																	
LOC		DIST		REVISIONS																																																																																													
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD																																																																																								
				E		REV PER 0G3A-0541-00	25SEP00	JR	TM																																																																																								
1 WIRE INSULATION DIA IS 0.91-1.09 [.036-.043].																																																																																																	
RING "A" COLOR: RED RING "B" COLOR: GREEN SLEEVE 3.05 [.120] 7.87 [.310] 2.54 [.100] REF 2 PLC 13.34 [.525] MAX <table><tr><td colspan="4">TEFLON ASTM D-1710</td><td colspan="2">SLEEVE</td></tr><tr><td colspan="4">COPPER PER ASTM B152 / NICKEL PL PER QQ-N-290</td><td colspan="2">RING "B"</td></tr><tr><td colspan="4">COPPER PER ASTM B152 / NICKEL PL PER QQ-N-290</td><td colspan="2">RING "A"</td></tr><tr><td colspan="4">MATERIAL / FINISH</td><td colspan="2">DESCRIPTION</td></tr><tr><td colspan="2">THIS DRAWING IS A CONTROLLED DOCUMENT.</td><td colspan="2">DWN JR RUTH 31MAY00</td><td colspan="2" rowspan="2"> AMP AMP Incorporated Harrisburg, PA 17105-3608</td></tr><tr><td colspan="2"></td><td colspan="2">CHK R HERSEY 31MAY00</td></tr><tr><td colspan="2">DIMENSIONS: MM [INCHES]</td><td colspan="2">TOLERANCES UNLESS OTHERWISE SPECIFIED:</td><td colspan="2">NAME</td></tr><tr><td colspan="2" rowspan="4"></td><td colspan="2">0 PLC ±-</td><td colspan="2">PRODUCT SPEC</td></tr><tr><td colspan="2">1 PLC ±-</td><td colspan="2">APPLICATION SPEC</td></tr><tr><td colspan="2">2 PLC ±0.40 [.015]</td><td colspan="2">SIZE</td></tr><tr><td colspan="2">3 PLC ±-</td><td colspan="2">CAGE CODE</td></tr><tr><td colspan="2">4 PLC ±-</td><td colspan="2">4 PLC ANGLES ±-</td><td colspan="2">DRAWING NO</td></tr><tr><td colspan="2">MATERIAL SEE TABLE</td><td colspan="2">FINISH SEE TABLE</td><td colspan="2">RESTRICTED TO</td></tr><tr><td colspan="4">CUSTOMER DRAWING</td><td colspan="2">SCALE 10:1</td></tr><tr><td colspan="4"></td><td colspan="2">SHEET 1 OF 1</td></tr><tr><td colspan="4"></td><td colspan="2">REV E</td></tr></table>										TEFLON ASTM D-1710				SLEEVE		COPPER PER ASTM B152 / NICKEL PL PER QQ-N-290				RING "B"		COPPER PER ASTM B152 / NICKEL PL PER QQ-N-290				RING "A"		MATERIAL / FINISH				DESCRIPTION		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 31MAY00		AMP AMP Incorporated Harrisburg, PA 17105-3608				CHK R HERSEY 31MAY00		DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME				0 PLC ±-		PRODUCT SPEC		1 PLC ±-		APPLICATION SPEC		2 PLC ±0.40 [.015]		SIZE		3 PLC ±-		CAGE CODE		4 PLC ±-		4 PLC ANGLES ±-		DRAWING NO		MATERIAL SEE TABLE		FINISH SEE TABLE		RESTRICTED TO		CUSTOMER DRAWING				SCALE 10:1						SHEET 1 OF 1						REV E	
TEFLON ASTM D-1710				SLEEVE																																																																																													
COPPER PER ASTM B152 / NICKEL PL PER QQ-N-290				RING "B"																																																																																													
COPPER PER ASTM B152 / NICKEL PL PER QQ-N-290				RING "A"																																																																																													
MATERIAL / FINISH				DESCRIPTION																																																																																													
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 31MAY00		AMP AMP Incorporated Harrisburg, PA 17105-3608																																																																																													
		CHK R HERSEY 31MAY00																																																																																															
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME																																																																																													
		0 PLC ±-		PRODUCT SPEC																																																																																													
		1 PLC ±-		APPLICATION SPEC																																																																																													
		2 PLC ±0.40 [.015]		SIZE																																																																																													
		3 PLC ±-		CAGE CODE																																																																																													
4 PLC ±-		4 PLC ANGLES ±-		DRAWING NO																																																																																													
MATERIAL SEE TABLE		FINISH SEE TABLE		RESTRICTED TO																																																																																													
CUSTOMER DRAWING				SCALE 10:1																																																																																													
				SHEET 1 OF 1																																																																																													
				REV E																																																																																													