



REGION +


Search Enter a keyword[About Nuvoton](#)[Products & Sales](#)[News & Events](#)[Investor](#)

**Accountability
Innovation
Teamwork**


[Home](#) \ [Product & Sales](#) \ [Product Lines](#) \ [Consumer Electronics IC](#) \ [Telecom](#) \ [Pro-X CODEC/SLCC](#)

Pro-X CODEC/SLCC

Part No.	W682388
Datasheet	 Request PDF
Description	<p>The W682388 implements a dual channel FXS telephone line interface optimized for short loop applications. It features dual SLCC (Subscriber Line Control Circuit) functionality with a dual channel programmable CODEC. The device supports internal ringing up to 90V_{PK} (5REN at 4kft) ideal for customer premise equipment (CPE). The CODEC is configured for μ-law/A-law or 16-bit linear PCM encoding and supports a comprehensive set of signaling options required to supervise and control both telephone lines. These include tone generation, including ring tone generation and detection as well as FSK and metering pulse generation. An on-chip dual pulse width modulator allows the control of DCDC conversion for each line. Programmable impedance and transhybrid balanced output buffers are provided for worldwide deployment.</p> <p>For additional technical documentation please Contact Sales.</p>
Diagram	 Block Diagram



Application Diagram



Features	<p>Performs complete BORSCHT functions for two channels on a single device Internal balanced ringing up to 90 V_{PK} (5 REN up to 4 kft)</p> <p>Integrated Power Management Integrated PWM controls line voltage to minimize power dissipation in all operating modes</p> <p>Programmable linefeed characteristics Ringing frequency, amplitude, cadence Trapezoidal and Sinusoidal waveforms Two-wire AC impedance, transhybrid balance Constant Current feed (20 to 41 mA) Ring trip and loop closure threshold</p> <p>Loop test and diagnostics support Integrated loopback modes Real-time linefeed monitor</p> <p>Programmable signal generation DTMF generation and detection Metering pulse generation (12/16 kHz) Caller ID (FSK) generation Tone generation (up to four simultaneous)</p>
----------	---

	G.711 µ-Law/A-Law / 16-bit linear PCM audio Programmable audio path gains PCM and SPI bus digital interfaces On-chip PLL for flexible clocking options 3.3V operation Small Footprint Packages:LQFP-64, QFN-64						
Package	LQFP-64, QFN-64						
Other Files	N/A						
Development Tools	Evaluation System:						
Others	Parametric <table border="1"><thead><tr><th>PART NUMBER</th><th>DESCRIPTION</th></tr></thead><tbody><tr><td>W682388DG</td><td>Pb-free, dual channel FXS telephone line interface, µ-law/A-law or 16-bit linear PCM</td></tr><tr><td>W682388YG</td><td>Pb-free, dual channel FXS telephone line interface, µ-law/A-law or 16-bit linear PCM</td></tr></tbody></table>	PART NUMBER	DESCRIPTION	W682388DG	Pb-free, dual channel FXS telephone line interface, µ-law/A-law or 16-bit linear PCM	W682388YG	Pb-free, dual channel FXS telephone line interface, µ-law/A-law or 16-bit linear PCM
PART NUMBER	DESCRIPTION						
W682388DG	Pb-free, dual channel FXS telephone line interface, µ-law/A-law or 16-bit linear PCM						
W682388YG	Pb-free, dual channel FXS telephone line interface, µ-law/A-law or 16-bit linear PCM						

Contact us: CODEC@nuvoton.com

[Terms of Use](#) | [Privacy Policy](#) | [Site map](#)
©2008 Nuvoton Technology Corporation. All Rights Reserved. Best Viewed at 1