






PERFORMANCE CHARACTERISTICS

CURRENT RATING
1.5 A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE 500V AC (CONT / CONT)

OPERATING TEMPERATURE -55°C TO 125°C

CONTACT RESISTANCE 20 MΩ MAX

INSERTION FORCE :0.75 N MAX /CONT


EXTRACTION FORCE: 0.15 N MIN /CONT

INSULATION RESISTANCE :10⁴ MΩ MIN

NOTES

- LEAD FREE INDICATOR : LF- LEAD FREE
- PERFORMANCE LEVEL INDICATOR
(REF DWG No. BS,C,201844,003)
- THIS PRODUCT IS CSA APPROVED
THIS PRODUCT IS UL RECOGNISED
- FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING: BSA,201,572001
THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVE
AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

LAY OUT
P.C.B.-HOLE



PDM: Rev.9D

STATUS: Released

Printed: Mar 15, 2011

Material				Spec ref			
Mat code				tolerance			
Heat treat				projection			
Plating/Finish				MM			
rev	ecn no	dr	date	Dr	30 03 99	W.Panis	
A	CONNECTION	KN	14-9-98	Eng			
B	3005-0256	Guo.M	03/08/95	Chr			
C	3007-0362	Keson	05/09/97	Appr			
D	0010-0010	NZ	10/13/99				
-	-	-	-				
-	-	-	-				
07	0000000000	RW	09/08/01				
Title				Product family			
Title				Model Name			
Title				Model Revision			
Title				REL Level			
Title				size			
Title				Scale			
Title				Rev.			
Title				D			
Title				sheet 1 of 1			