





注記 NOTES

- △1 MX J側を基準に奇数番目の極におけるソルダーテール。
SOLDER TAIL OF ODD CKTS,MXJ MARK AS BASIC.
- △2 MX J側を基準に偶数番目の極におけるソルダーテール。
SOLDER TAIL OF EVEN CKTS,MXJ MARK AS BASIC.
- △3 3極~10極に適用。APPLY FOR 3-10 CKTS.
- △4 3極~19極に適用。APPLY FOR 3-19 CKTS.
5. () 内寸法は、参考値。
() DIMENSION IS FOR REFERENCE.
6. ソルダーテールは、先端が取付推奨穴にガイドされること。
ガイドされること。
SOLDER TAILS MAY BE CHECKEDBY INSERTION
FOR RECOMMENDED PCB BOARD HOLES.

48.25	43.95	39-51-3343	5597-34APB	34
47.00	42.70	-3333	-33APB	33
45.75	41.45	-3323	-32APB	32
44.50	40.20	-3313	-31APB	31
43.25	38.95	-3303	-30APB	30
42.00	37.70	-3293	-29APB	29
40.75	36.45	-3283	-28APB	28
39.50	35.20	-3273	-27APB	27
38.25	33.95	-3263	-26APB	26
37.00	32.70	-3253	-25APB	25
35.75	31.45	-3243	-24APB	24
34.50	30.20	-3233	-23APB	23
33.25	28.95	-3223	-22APB	22
32.00	27.70	-3213	-21APB	21
30.75	26.45	-3203	-20APB	20
29.50	25.20	-3193	-19APB	19
28.25	23.95	-3183	-18APB	18
27.00	22.70	-3173	-17APB	17
25.75	21.45	-3163	-16APB	16
24.50	20.20	-3153	-15APB	15
23.25	18.95	-3143	-14APB	14
22.00	17.70	-3133	-13APB	13
20.75	16.45	-3123	-12APB	12
19.50	15.20	-3113	-11APB	11
18.25	13.95	-3103	-10APB	10
17.00	12.70	-3093	-09APB	9
15.75	11.45	-3083	-08APB	8
14.50	10.20	-3073	-07APB	7
13.25	8.95	-3063	-06APB	6
12.00	7.70	-3053	-05APB	5
10.75	6.45	-3043	-04APB	4
9.50	5.20	39-51-3033	5597-03APB	3
B	A	MATERIAL NO.	ENG. NO.	極数 CKT.

DO NOT SCALE DRAWING		164NO. DRWN: CH'K: APPR:		163NO. DRWN: CH'K: APPR:		162NO. DRWN: CH'K: APPR:		161NO. DRWN: CH'K: APPR:		再作図及び変更 REDRAWN & REVISED 160NO. J2003-2624 DRWN: K.TOJO '03/04/17 CH'K: H. Sasaki '03/04/17 APPR: H. Sasaki '03/04/17		DESCRIPTION F REV		MATERIAL HOUSING, ACTUATOR : 材料 PBTP, UL94V-0 TERMINAL : PHOSPHOR-BRONZE THK : 0.3+ FINISH TIN-LEAD(9:1)3~5MICRON 仕上りMETER OVER COPPER 1~2.5 MICRON METER PLATING. WIRE RANGE 適用電線範囲 INS. RANGE 被覆外径		GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差 10 UNDER 未満 ±0.2 10 OVER 以上 30 UNDER 未満 ±0.25 30 OVER 以上 ±0.3 ANGLE 角度 ±3°		SCALE 1/1 DESIGN UNITS mm mm INCH		DRAWN BY & DATE K.TOJO '03/04/15 CHECKED BY & DATE H. Sasaki '03/04/17 APPROVED BY & DATE H. Sasaki '03/04/17 CAD FILENAME SD-5597-004.S01		TITLE: 1.25 FPC Conn Assy ZIF MATERIAL NO. 39-51-3**3 DRAWING NO. SD-5597-004 SHEET NO. 1 OF 2		DIMENSIONS: 2RD ANGLE PROJECTION mm mm INCH INCH mm ONLY SHT REV IN CAD ONLY		MOLEX INCORPORATED SD-5597-004.S01 39-51-3**3 SD-5597-004 1 OF 2 SIZE B		EN-02J(097) MXJ-54	
----------------------	--	-----------------------------	--	-----------------------------	--	-----------------------------	--	-----------------------------	--	---	--	-------------------------	--	--	--	--	--	--	--	---	--	---	--	--	--	---	--	--------------------	--



164NO. DRWN: CHK: APPR:	163NO. DRWN: CHK: APPR:	162NO. DRWN: CHK: APPR:	161NO. DRWN: CHK: APPR:	再作図及び変更 REDRAWN & REVISED 160NO.J2003-2624 DRWN: K.TOJO '03/04/17 CHK: H. Saito '03/04/17 APPR: H. Saito '03/04/17	DESCRIPTION MATERIAL 材料 SEE SHEET I FINISH 仕上り SEE SHEET I WIRE RANGE 適用電線範囲 INS. RANGE 被覆外径	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差 10 UNDER 未満 ±0.2 10 OVER 以上 30 UNDER 未満 ±0.25 30 OVER 以上 ±0.3 ANGLE 角度 ±3°	SCALE 1/1 DRAWN BY & DATE K.TOJO '03/04/15 CHECKED BY & DATE H. Saito '03/04/17 APPROVED BY & DATE H. Saito '03/04/17 CAD FILENAME SD-5597-004.S02	DESIGN UNITS ☒ mm ☐ INCH 2ND ANGLE PROJECTION TITLE: 1.25 FPC Conn Assy ZIF MOLEX INCORPORATED MATERIAL NO. 39-51-3**3 DRAWING NO. SD-5597-004 SHEET NO. 2 OF 2	2 B
----------------------------------	----------------------------------	----------------------------------	----------------------------------	---	--	---	---	--	--------