



Thomas Research Products

SSL Solutions Faster Than The Speed Of Light®

TR-SS1 LED Core™

**Integrated LED Performance Canopy Module
Patented Design,
with 0-10V Dimming**

- Die-cast single piece aluminum body
- DLC Compliant optics
- UV stabilized polycarbonate lens with injection-molded frame
- Universal voltage (100-277Vac)
- Patented design is robust, for superb durability
- Modular: Key components can be refurbished
- Type V short lens

TR-SS1 Integrated LED Canopy Module is designed to seamlessly integrate into just about any canopy fixture. We have taken the tedious engineering task out of designing an LED solution.

Combining cutting-edge optical characteristics and integrated LED driver, it's simpler than ever. This module includes DLC Compliant optics, so any luminaire utilizing the LED Core will meet DLC requirements. We can provide your engineering staff a full set of CAD files to speed along the integration process.

Includes 0-10V Dimming-capable driver as standard.

Electrical:

Class 1 and 2 power supplies accommodate an input voltage range of 100-277V 50/60Hz. All power supplies provide Class A EMI rating with high power factor of 90% typical.

Mounting:

Custom fixture mount only. CAD and Step files available to streamline integration. Fixture cut out pattern show on next page.

Exterior Surface Finish:

Powder coated die-cast aluminum.

Testing and Compliance:

The TR-SS1 meets UL8750 specifications. Contact our engineering staff for assistance in certifying your fixture.

Lumen Maintenance:

Lumen maintenance will vary substantially based upon fixture in which the TR-SS1 is mounted. Additional heat dissipating capacity from fixture is highly recommended to maximize lumen maintenance. Lumen maintenance to be determined by using LM80, in situ thermal data in accordance with DOE/EPA standards and reliability data supplied by LED Manufacturer.

- Maintains a tolerance of $\pm 7\%$ on flux measurements.
- Published output measurements using 4500-5000K.
- Minimum CRI is 70.
- Output lumens will vary depending on factors involved with fixture integration.
- 5 year limited warranty with validation of fixture.

Environmental Impact

- RoHS Compliant
- No mercury
- Reduction in Kw load by as much as 60%



SS1 Series LED Canopy Module

Model Number	System Power	Initial Delivered Lumens	Lumens Per Watt	Replaces HID lamp	Energy Savings [†]
TR-SS1-E36P	41W	4115	101	70W HPS	50W
TR-SS1-E48P	55W	5593	102	100W HPS	75W
TR-SS1-E64P	75W	7435	99	150W MH	135W

† Compares LED Core™ system wattage to avg. HID ballast input wattage



Specifications subject to change without notice.

10-04-13




Thomas Research Products

SSL Solutions Faster Than The Speed Of Light®


TR-SS1-P

Pg 2 of 2

Photometrics




Dimensions




Application Notes:

- 1) The LED Core™ is intended to be mounted to a flange of the fixture, situated between the LED Core™ module's lens frame/lens/gasket and aluminum body in order to qualify for IP rating. (See detail.)
- 2) The LED Core™ module can be mounted to the fixture flange on the backside of the module's body. Mounting holes are not provided. This is not recommended as it will not achieve an IP rating.



Mounting



Mounting Example:
Canopy Luminaire

