


Darlington Transistor

2SD1024

(T8L10)

8A NPN

OUTLINE DIMENSIONS



RATINGS

● Absolute Maximum Ratings


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T _{stg}		-55~+150	°C
Junction Temperature	T _j		+150	°C
Collector to Base Voltage	V _{CBO}		100	V
Collector to Emitter Voltage	V _{CEO}		100	V
Emitter to Base Voltage	V _{EBO}		7	V
Collector Current DC	I _C		8	A
Collector Current Peak	I _{CP}		12	A
Base Current DC	I _B		0.5	A
Base Current Peak	I _{BP}		1	A
Total Transistor Dissipation	P _T	T _c = 25°C	50	W
Mounting Torque	TOR	(Recommended torque : 0.3N·m)	0.5	N·m

● Electrical Characteristics (T_c=25°C)


Item	Symbol	Conditions	Ratings	Unit
Collector Cutoff Current	I _{CBO}	V _{CB} = 100V	Max 0.1	mA
	I _{CEO}	V _{CE} = 100V	Max 0.1	
Emitter Cutoff Current	I _{EBO}	V _{EB} = 7V	Max 5	mA
DC Current Gain	h _{FE}	V _{CE} = 3V, I _C = 5A	Min 1,500	
			Max 30,000	
Collector to Emitter Saturation Voltage	V _{CE(sat)}	I _C = 5A	Max 1.5	V
Base to Emitter Saturation Voltage	V _{BE(sat)}	I _B = 6mA	Max 2.0	V
Thermal Resistance	θ _{jc}	Junction to case	Max 2.5	°C/W
Transition Frequency	f _T	V _{CE} = 10V, I _C = 0.8A	TYP 20	MHz
Turn on Time	ton	I _C = 8A I _{B1} = I _{B2} = 8mA R _L = 3Ω V _{BB2} = 4V	Max 2	μs
Storage Time	ts		Max 5	
Fall Time	tf		Max 3	

2SD1024

$h_{FE} - I_C$




2SD1024 Saturation Voltage




2SD1024


Switching Time - I_C




2SD1024 Switching Time - Tc



2SD1024 Transient Thermal Impedance



2SD1024 Forward Bias SOA



2SD1024 Collector Current Derating

