




LOC		DIST		REVISIONS			
F	LTR	DESCRIPTION		DATE	DWN	APVD	
B		ECR-12-008098		08MAY2012	WC	AC	

D





- △ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.
- △ CONTACT MATERIAL: PHOSPHOR BRONZE PER UNS
ALLOY NO. C51100, TEMPER: H04.
- △ CONTACT FINISH:(C)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.0005 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- Ⓐ △ PART MARKING PER TE SPEC 115-9009 LOCATED APPROXIMATELY
AS SHOWN BETWEEN RIBS/SLOTS ON EITHER SIDE OF HOUSING AT
MANUFACTURER'S DISCRETION.
- △ PART TO BE MARKED WITH DATE CODE ONLY.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI


C



B



A



RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)

△ 6 OBSOLETE	58	29	59.88	△ 3	120	5223514-6
	70	35	71.88	△ 3	144	5223514-5
	94	47	95.88	△ 3	192	5223514-4
	46	23	47.88	△ 3	96	5223514-3
	22	11	23.88	△ 3	48	5223514-2
△ 5	10	5	11.88	△ 3	24	5223514-1
	C	B	A	FINISH	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.MCMMASTER	14DEC04	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK R.WERTZ	14DEC04	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.WERTZ	14DEC04	PRODUCT SPEC	
APPLICATION SPEC		SIZE		CAGE CODE	
MATERIAL		WEIGHT		DRAWING NO	
FINISH		A1		00779	
CUSTOMER DRAWING		SCALE		SHEET	
4:1		1		REV	