

# NC6MSXX

6 pole male cable connector with Nickel housing and silver contacts. Equivalent to Switchcraft pin layout.

The next generation of the worldwide accepted standard of XLR cable connectors. The successor of the X series offers several new features which make it more reliable, easier to assemble and improves contact integrity as well cable strain relief.



## Features & Benefits

- Male connector with improved locking recess without "window", more stringent housing increases durability
- Improved chuck type strain relief provides higher pull-out force and makes assembly easier and faster
- Boot with polyurethane gland gives high protection to cable bending stresses
- Colored rings and boots available for coding or identification
- Sleek and ergonomic design - valuable and handy
- Rugged zinc diecast shell, longlasting and dependable
- Internal thread on shell is well protected against any damage
- Branded with unique hologram - guarantees genuine and authentic Neutrik product

## Technical Information ▼ hide

### Product

Title NC6MSXX

Connection Type XLR

Gender male

### Electrical

Capacitance between contacts  $\leq 7 \text{ pF}$

Contact resistance  $\leq 3 \text{ m}\Omega$  (inner)

Dielectric strength 1,5 kVdc

Insulation resistance  $> 2 \text{ G}\Omega$  (initial)

Rated current per contact 7,5 A

Rated voltage 50 V

### Mechanical

Cable O.D. 3.5 - 8.0 mm

Insertion force  $\leq 20 \text{ N}$

Available insertion force

$\leq 20 \text{ N}$

## Withdrawal force

Lifetime	> 1000 mating cycles
Wiresize	max. 1.0 mm <sup>2</sup>
Wiresize	max. 18 AWG
Wiring	Solder contacts
Locking device	Latch lock
Equivalent	Switchcraft pin arrangement

## Material

Boot	Polyurethan
Contact plating	2 µm Ag over 2 µm Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Zinc diecast (ZnAl4Cu1)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Strain relief	Polyacetal (POM)

## Environmental

Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

## Accessories

		
<b>BTXX</b>	<b>BXX-*</b>	<b>BXX-CR</b>

		
<b>DYY 11</b>	<b>HTYD</b>	<b>VVD *</b>