

OptiMOS™ -P Power-Transistor
Features


- P-Channel
- Enhancement mode
- Logic level
- 150°C operating temperature
- Avalanche rated; RoHS compliant
- V_{GS}=25V, specially suited for notebook applications
- Halogen-free according to IEC61249-2-21
- Pb-free lead plating; RoHS compliant



Halogen-Free

Product Summary

V_{DS}	-30	V
$R_{DS(on),max}$	13	mΩ
I_D	-22.5	A



PG-TDSON-8



Type	Package	Marking	Lead free	Packing
BSC130P03LS G	PG-TDSON-8	130P03LS	Yes	Dry

Maximum ratings, at $T_J=25\text{ °C}$, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current	I_D	$T_C=25\text{ °C}$	-22,5	A
		$T_C=70\text{ °C}$	-22,5	
		$T_A=25\text{ °C}^{(1)}$	-12	
Pulsed drain current	$I_{D,pulse}$	$T_C=25\text{ °C}^{(2)}$	-90	
Avalanche energy, single pulse	E_{AS}	$I_D=-22.5\text{ A}$, $R_{GS}=25\text{ Ω}$	148	mJ
Gate source voltage	V_{GS}		±25	V
Power dissipation	P_{tot}	$T_C=25\text{ °C}$	69	W
		$T_A=25\text{ °C}^{(1)}$	2,5	
Operating and storage temperature	T_J, T_{stg}		-55 ... 150	°C
ESD class		JESD22-A114-HBM	1C (1kV-2kV)	
Soldering temperature			260 °C	
IEC climatic category; DIN IEC 68-1			55/150/56	

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Thermal characteristics

Thermal resistance, junction - case	R_{thJC}		-	-	1,8	K/W
Thermal resistance, junction - ambient	R_{thJA}	6 cm ² cooling area ¹⁾	-	-	50	

Electrical characteristics, at $T_j=25\text{ °C}$, unless otherwise specified

Static characteristics

Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS}=0\text{ V}$, $I_D=-250\mu\text{A}$	-30	-	-	V
Gate threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}$, $I_D=-150\mu\text{A}$	-2,2	-1,5	-1	
Zero gate voltage drain current	I_{DSS}	$V_{DS}=-30\text{ V}$, $V_{GS}=0\text{ V}$, $T_j=25\text{ °C}$	-	-0,1	-1	μA
		$V_{DS}=-30\text{ V}$, $V_{GS}=0\text{ V}$, $T_j=125\text{ °C}$	-	-10	-100	
Gate-source leakage current	I_{GSS}	$V_{GS}=-25\text{ V}$, $V_{DS}=0\text{ V}$	-	-10	-100	nA
Drain-source on-state resistance	$R_{DS(on)}$	$V_{GS}=-10\text{ V}$, $I_D=-22.5\text{ A}$	-	9,4	13,0	m Ω
Gate resistance	R_G		-	3,8	-	Ω
Transconductance	g_{fs}	$ V_{DS} >2 I_D R_{DS(on)max}$, $I_D=-22.5\text{ A}$	20	39	-	S

¹⁾ Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 μm thick) copper area for drain connection. PCB is vertical in still air.

²⁾ See Figure 3.

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Dynamic characteristics

Input capacitance	C_{iss}	$V_{GS}=0\text{ V}, V_{DS}=-15\text{ V},$ $f=1\text{ MHz}$	-	2760	3670	pF
Output capacitance	C_{oss}		-	857	1140	
Reverse transfer capacitance	C_{rss}		-	690	1000	
Turn-on delay time	$t_{d(on)}$	$V_{DD}=-15\text{ V}, V_{GS}=-10\text{ V}, I_D=22.5\text{ A},$ $R_G=6\ \Omega$	-	11,4	17,1	ns
Rise time	t_r		-	65,6	98,4	
Turn-off delay time	$t_{d(off)}$		-	43,5	65,3	
Fall time	t_f		-	35,1	52,7	

Gate Charge Characteristics³⁾


Gate to source charge	Q_{gs}	$V_{DD}=-24\text{ V}, I_D=22.5\text{ A},$ $V_{GS}=0\text{ to }-10\text{ V}$	-	-7,7	-10,3	nC
Gate charge at threshold	$Q_{g(th)}$		-	-4,3	-5,7	
Gate to drain charge	Q_{gd}		-	-20,5	-30,8	
Switching charge	Q_{sw}		-	-24,0	-35,4	
Gate charge total	Q_g		-	-54,9	-73,1	
Gate plateau voltage	$V_{plateau}$		-	-2,9	-	V
Output charge	Q_{oss}	$V_{DD}=-15\text{ V}, V_{GS}=0\text{ V}$	-	-14,8	-	

Reverse Diode

Diode continuous forward current	I_S	$T_C=25\text{ °C}$	-	-	22,5	A
Diode pulse current	$I_{S,pulse}$		-	-	-90	
Diode forward voltage	V_{SD}	$V_{GS}=0\text{ V}, I_F=-22.5\text{ A},$ $T_J=25\text{ °C}$	-	-0,9	-1,2	V
Reverse recovery time	t_{rr}	$V_R=15\text{ V}, I_F= I_S ,$ $di_F/dt=100\text{ A}/\mu\text{s}$	-	33	-	ns
Reverse recovery charge	Q_{rr}		-	24	-	nC


1 Power dissipation

$$P_{\text{tot}} = f(T_C); t_p \leq 10 \text{ s}$$



2 Drain current


$$I_D = f(T_C); |V_{GS}| \geq 10 \text{ V}; t_p \leq 10 \text{ s}$$



3 Safe operating area

$$I_D = f(V_{DS}); T_C = 25^\circ\text{C}^{(1)}; D = 0$$


parameter: t_p



4 Max. transient thermal impedance


$$Z_{\text{thJS}} = f(t_p)$$

parameter: $D = t_p/T$




5 Typ. output characteristics

 $I_D = f(V_{DS}); T_j = 25^\circ\text{C}$

parameter: V_{GS}



6 Typ. drain-source on resistance

 $R_{DS(on)} = f(I_D); T_j = 25^\circ\text{C}$


parameter: V_{GS}


7 Typ. transfer characteristics

 $I_D = f(V_{GS}); |V_{DS}| > 2|I_D|R_{DS(on)max}$


parameter: T_j


8 Typ. forward transconductance

 $g_{fs} = f(I_D); T_j = 25^\circ\text{C}$



9 Drain-source on-state resistance

$$R_{DS(on)} = f(T_j); I_D = -22.5 \text{ A}; V_{GS} = -10 \text{ V}$$




10 Typ. gate threshold voltage

$$V_{GS(th)} = f(T_j); V_{GS} = V_{DS}; I_D = -150 \mu\text{A}$$



11 Typ. capacitances


$$C = f(V_{DS}); V_{GS} = 0 \text{ V}; f = 1 \text{ MHz}$$



12 Forward characteristics of reverse diode

$$I_F = f(V_{SD})$$


parameter: T_j



13 Avalanche characteristics

$$I_{AS}=f(t_{AV}); R_{GS}=25\ \Omega$$


parameter: $T_{j(\text{start})}$



14 Typ. gate charge


$$V_{GS}=f(Q_{\text{gate}}); I_D=-22.5\ \text{A pulsed}$$

parameter: V_{DD}




15 Drain-source breakdown voltage


$$V_{BR(DSS)}=f(T_j); I_D=-250\ \mu\text{A}$$




16 Gate charge waveforms



Package Outline



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	0.90	1.10	0.035	0.043
b	0.34	0.54	0.013	0.021
b1	0.02	0.22	0.001	0.008
c	0.15	0.35	0.006	0.014
D=D1	4.95	5.35	0.195	0.211
D2	4.20	4.40	0.165	0.173
E	5.95	6.35	0.234	0.250
E1	5.70	6.10	0.224	0.240
E2	3.40	3.80	0.134	0.150
e	1.27		0.050	
N	8		8	
L	0.45	0.65	0.018	0.026
□	8.5°	11.5°	8.5°	11.5°
aaa	0.25		0.010	
eee	0.05		0.002	
F1	6.75	6.95	0.266	0.274
F2	4.60	4.80	0.181	0.189
F3	4.36	4.56	0.172	0.180
F4	0.55	0.75	0.022	0.030
F5	0.52	0.72	0.020	0.028
F6	1.10	1.30	0.043	0.051
F7	0.40	0.60	0.016	0.024
F8	0.60	0.80	0.024	0.031
F9	0.53	0.73	0.021	0.029
F10	4.90	5.10	0.193	0.201
F11	0.53	0.73	0.021	0.029

DOCUMENT NO. Z8B00003332
SCALE 0 2.5 5mm
EUROPEAN PROJECTION 
ISSUE DATE 08-03-2007
REVISION 03

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2008 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please [contact the nearest Infineon Technologies Office \(www.infineon.com\)](http://www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.